

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP. 2005

© COPYRIGHT 2005

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	Released as per ECR-08-022292	4-Sep-08	SP	JC
	V	ECR-16-003733	12MAR2016	KR	TN


LASER MARKING: TE LOGO PN VALUE
TOLERANCE & DATE CODE

M6 ST/STEEL TERMINAL STUDS.
EACH SUPPLIED WITH:-
2 OFF M6 ST/STEEL FULL NUTS
2 OFF M6/STEEL PLAN WASHERS

- 1 FOR FURTHER INFORMATION SEE DATA SHEET FOR
HS SERIES-ALUMINIUM HOUSED RESISTORS
- 2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF

GOLD ANODISED
ALUMINIUM HOUSINGS

RoHS Compliant



SCALE 1:2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 28.SEP.05

CHK DAVE KENNEDY

29.SEP.05

J CATCHPOLE

APVD 29.SEP.05

J CATCHPOLE

PRODUCT SPEC

-

APPLICATION SPEC


-

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC

±0.5

1 PLC

±0.2

2 PLC

±0.1

3 PLC

±

4 PLC

±

ANGLES

±5°

MATERIAL

material_2

FINISH

finish_spec_2



TE Connectivity

NAME

HSC250 ALUMINIUM HOUSED
POWER RESISTOR

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-1630024

RESTRICTED TO

-

SCALE

1:1

SHEET

1

OF

1

REV

V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1630024-7](#)