


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z1	REVISED PER ECO-11-005150	21MAR2011	RK	HMR
	Z2	NEW DRAWING CREATED IN CREO	26JUNE2014	JBJH	BRUN
	Z3	NOTE 8 MODIFIED	18NOV2015	MAH.	BRUN
	Z4	TOLERANCES ADDED AT SECTION A-A AND B-B	21JAN2016	MAH.	BRUN




NOTES:

- 1 UNDERCOATING: 0.8 µm NICKEL OVERALL
CONTACT AREA: 0.8 µm GOLD
CRIMP AREA: GOLDFLASH
- 2 UNDERCOATING: 0.8 µm NICKEL OVERALL
CONTACT AREA: 1.25 µm GOLD
CRIMP AREA: GOLDFLASH
- 3 SUITABLE FOR 0.64x0.64 POST
- 6 UNDERCOATING: 0.8 µm NICKEL OVERALL
CONTACT AREA: 0.4 µm GOLD
CRIMP AREA: GOLDFLASH
- 7 ADVANCED PROD. NRS. FOR DIN 41612 PART 5 SPEC
- 8 PLATING: 2.0 µm TIN OVER MIN. 0.5 µm Ni OVERALL
- 9 REVERSE REELED FOR USE WITH MINI APPLICATOR.
- 10 STANDARD REELED FOR USE WITH STANDARD APPLICATOR.
- 11 TRADE MARK.

WIRE RANGE:
20-24 (26) AWG
INSULATION RANGE:
1.40 MAX DIA.

SUPERSEDED BY 166500-2

166722-1	1	PHOSPHORBRONZE	1-166500-2	10	Z
166722-6	8		1-166500-1	10	Z
166722-6	8		166500-9	9	Z
166722-4	6		166500-7	9	W
166722-2	2		166500-4	9	Z
166722-1	1		166500-2	9	Z
LOOSE PIECE NUMBER	PLATING	MATERIAL	STRIPNUMBER	REV	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M.Pfeilschifter	18JUL2000	 TE Connectivity	
		CHK	V.Huhn	18JUL2000		
DIMENSIONS:		APVD	-		NAME	
mm		PRODUCT SPEC	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	-		SIZE	
0 PLC ±0.2		WEIGHT	-			
1 PLC ±0.2		CUSTOMER DRAWING		SCALE	10:1	SHEET
2 PLC ±0.2				1 OF 1		REV
3 PLC ±0.2						Z4
4 PLC ±0.2						
ANGLES ±1°						
FINISH						
-						
-						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[166500-9](#)