




P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	REVISED PER ECO-19-005751	26SEP2019	RS	SG



SECTION C-C
SCALE 12:1



SECTION D-D
SCALE 12:1

1. THIS CONTACT IS USED ON EITHER PLUG AND CAP HOUSING
- 2 0.00076mm MIN THICK GOLD-PLATED IN THE CONTACT SECTION TO 3.2mm FROM TIP END, OVER NICKEL UNDERPLATE ALL OVER
3. WIRE RANGE: 22-18 AWG
INSULATION DIA: 1.5-2.4mm
4. APPLICABLE INSULATION DIA MAX FOR TWO WIRE CRIMP IS 3.4mm MAX

170361, 170362, 170365, 170366	TIN/PHOS BRONZ	170364-4	170360-4
	GOLD/BRASS 	170364-3	170360-3
	TIN/BRASS	170364-1	170360-1
MATING P/N	FINISH/MATERIAL	LOOSE PIECE P/N	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SMITH 26SEP2019	TE Connectivity	
		CHK S. WRIGHT 26SEP2019		
		APVD S. WRIGHT 26SEP2019		
		PRODUCT SPEC 108-5138		
DIMENSIONS: mm		APPLICATION SPEC 114-5050	NAME MINI UNIVERSAL MATE-N-LOK PIN CONTACT	
		WEIGHT -	SIZE A3 CAGE CODE 00779 DRAWING NO C-170360	
MATERIAL SEE TABLE		CUSTOMER DRAWING		RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED:		SCALE 4:1		SHEET 1 OF 1
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$		REV L		
FINISH SEE TABLE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[170360-3](#)