

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-





© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC
HBDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	CHANGE LOGO&ADD LINE IDENTIFICATION ECO-12-003498& ADD CQC SYMBOL P-11-003756	07Nov2012	YS.H	BH.Y



CONNECTION DIAGRAM (BOTTOM VIEW)




Diagram dimension	Tolerance
0.99mm max.	\pm 0.1mm
1 - 2.99mm	\pm 0.2mm
3mm min.	\pm 0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN KY.DU

CHK N.Fungyama


APVD C.H.HSU

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC \pm -
1 PLC \pm -
2 PLC \pm -
3 PLC \pm -
4 PLC \pm -
ANGLES \pm -

FINISH



TE Connectivity

NAME

PCH-D2(H)-WG CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

1721766

RESTRICTED TO

SCALE 5:1

SHEET 1 OF 2

REV C

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

1-1721766-4	PCH-148D2H-WG	48V	PCH-148D2H-WG	107-79019(TRAY)	n
1-1721766-3	PCH-124D2H-WG	24V	PCH-124D2H-WG	107-79019(TRAY)	m
1-1721766-2	PCH-112D2H-WG	12V	PCH-112D2H-WG	107-79019(TRAY)	l
1-1721766-1	PCH-109D2H-WG	9V	PCH-109D2H-WG	107-79019(TRAY)	k
1-1721766-0	PCH-106D2H-WG	6V	PCH-106D2H-WG	107-79019(TRAY)	j
1721766-9	PCH-105D2H-WG	5V	PCH-105D2H-WG	107-79019(TRAY)	i
1721766-8	PCH-103D2H-WG	3V	PCH-103D2H-WG	107-79019(TRAY)	h
1721766-7	PCH-148D2-WG	48V	PCH-148D2-WG	107-79019(TRAY)	g
1721766-6	PCH-124D2-WG	24V	PCH-124D2-WG	107-79019(TRAY)	f
1721766-5	PCH-112D2-WG	12V	PCH-112D2-WG	107-79019(TRAY)	e
1721766-4	PCH-109D2-WG	9V	PCH-109D2-WG	107-79019(TRAY)	d
1721766-3	PCH-106D2-WG	6V	PCH-106D2-WG	107-79019(TRAY)	c
1721766-2	PCH-105D2-WG	5V	PCH-105D2-WG	107-79019(TRAY)	b
1721766-1	PCH-103D2-WG	3V	PCH-103D2-WG	107-79019(TRAY)	a
TE PART NO	TE TYPE NAME	PART B	PART A	PACKAGE SPEC	TYPE

RELAY TYPE

NOTES:

1.LAST SUFFIX

NON : WASHABLE TYPE

② 2.LOT NO SYSTEM AS FOLLOWING:



WEEK

YEAR

⑥ 6.ADD LOT NO. SYSTEM AS FOLLOWING;



I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,....Z

③ 3.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

④ 4.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

⑤ 5.MARKING FROM INK TO LASER.

		UV RESIN	UV SEAL	17
		EPOXY RESIN	SEAL	16
		UEW	COIL WIRE	15
	SOLDER DIP	HCP WIRE	COIL TERMINAL	14
		Ag ALLOY	STATIONARY CONTACT	13
		Ag ALLOY	MOVBLE CONTACT	12
		Cu ALLOY	HINGE SPRING	11
	SOLDER DIP	Cu ALLOY	NC TERMINAL	10
	SOLDER DIP	Cu ALLOY	NC TERMINAL	9
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	8
UL94 V-0		LCP	CARD	7
UL94 V-0		PET	CASE	6
UL94 HB		PA NYLON	BOBBIN	5
UL94 V-0		PET	BASE	4
	Ni PLATED	STEEL	CORE	3
	Ni PLATED	STEEL	ARMATURE	2
	Ni PLATED	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

KY.DU

CHK

N.Funayama

APVD

C.H.HSU

PRODUCT SPEC

APPLICATION SPEC

WEIGHT


-

FINISH

-

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

-



TE Connectivity

NAME

PCH-D2(H)-WG CUSTOMER DRWING

SIZE

CAGE CODE

DRAWING NO

1721766

RESTRICTED TO

A3

00779

C=

1721766

SCALE 5:1

SHEET 2 OF 2

REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1721766-6](#)