







Technical drawing of the front view of a device. The drawing shows a rectangular frame with a central component and two side components. A dashed rectangle is in the upper center. Dimensions are 1.1 for the left side and 18.45 ± 0.25 for the total width.





W/O LED LIGHT



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
(DIMENSION TOLERANCE: 1 PLC: ± 0.1 2PLC: ± 0.05)

△6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	REEL	W/O	50μ"	3-1734719-8
			30μ"	3-1734719-7
			15μ"	3-1734719-6
			6μ"	3-1734719-5
		W/	50μ"	3-1734719-4
			30μ"	3-1734719-3
			15μ"	3-1734719-2
			6μ"	3-1734719-1
 OBSOLETE	TRAY	W/O	50μ"	1734719-8
30μ"			1734719-7	
15μ"			1734719-6	
6μ"			1734719-5	
OBSOLETE		W/	50μ"	1734719-4
OBSOLETE			30μ"	1734719-3
OBSOLETE			15μ"	1734719-2
			6μ"	1734719-1
	PACKAGE	LED LIGHT	MIN. GOLD THICKNESS	PART NUMBER

AS	00775	00775		
		SCALE	SHEET	REV

STE

TE Connectivity

MODULAR JACK, RJ45, SINGLE
ENTRY, DIP TYPE


AS	00775	00775		
		SCALE	SHEET	REV

SHEET	REV A
-------	-------

SHEET	1 OF 4	REV	A2
-------	--------	-----	----






4	REV A2
---	--------

1471-19 (3/11)




DETAIL W

TE LOGO &
DATE CODE





RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
(DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05)



W/O LED LIGHT

NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC HIGH TEMP., UL94V-0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.35mm.
SHELL: BRASS, THICKNESS: 0.20mm.
- FINISH:
CONTACT: GOLD PLATED (SEE TABLE) IN CONTACT AREA,
GOLD FLASH ON SOLDER TAILS,
50u" MIN. NICKEL UNDER PLATED ALL OVER.
SHELL: 20u" MIN. NICKEL PLATED.
- WAVE SOLDER CAPABLE TO 265°C PER TYCO SPEC 109-202,
CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —		 TE Connectivity		THICKNESS	
		CHK —					
		APVD —		NAME			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE			
		0 PLC ± 0.5 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.1 4 PLC ± — ANGLES ± 3°		PRODUCT SPEC — APPLICATION SPEC —			
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE		SEE NOTE		WEIGHT —	A300779	C=1734719	—
CUSTOMER DRAWING						SCALE —	SHEET 2 OF 4
						REV A2	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

ALL RIGHTS RESERVED.

© COPYRIGHT 2013 BY TE CONNECTIVITY.

LOC
DWDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

TOP TRAY

CLAPBOARD

INNER BOX

BOX

370mm(L)X255mm(W)X220mm(H)
11 TRAY/CARTON
TOTAL: 880 PCS
GROSS WEIGHT: 5Kg Ref.

TRAY

330mm(L)X225mm(W)X15mm(H)
80 PCS/TRAY

H

W

L

H

W

L

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	—
CHK	—
APVD	—
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—




TE Connectivity

NAME			
MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=1734719	—
CUSTOMER DRAWING		SCALE	SHEET
		—	3 of 4
		REV	A2

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2013 BY TE CONNECTIVITY.

LOC
DWDIST
—

REVISIONS

P

LTR





DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1




NOTES:

- THE DIRECTION OF JACKS PUT INTO CARRIER.
- 10 EMPTY CAVITIES FOR BOTH OF TOP AND BOTTOM OF THE CARRIER.
- 200 PCS PRODUCTS BE PACKAGED ONE REEL.
- BOX SIZE: 345(L)X345(W)X315(H)
6 REEL/BOX
TOTAL: 1200 PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1734719

TE Connectivity

MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE

RESTRICTED TO

—

SCALE

—

SHEET

4 of 4

REV

A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1734719-3](#)