

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DW

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECR-16-003830	14MAR16	FL	SY

8.7	GEN II & GEN III		2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	4-1734774-8			
5.45				38.35	37	40.15	56	38.65	98	WHITE		4-1734774-7			
3.85				21.35	20	23.15	39	21.65	64	BLACK		4-1734774-6			
2.55				7.35	6	9.15	25	7.65	36	WHITE		4-1734774-5			
										BLACK		4-1734774-4			
										WHITE		4-1734774-3			
8.7							71.35	70	73.15	89	71.65	164	BLACK	15u"	4-1734774-0
													G/F	3-1734774-9	
5.45							38.35	37	40.15	56	38.65	98	WHITE	15u"	3-1734774-8
													G/F	3-1734774-7	
3.85							21.35	20	23.15	39	21.65	64	BLACK	15u"	3-1734774-6
													G/F	3-1734774-5	
2.55							7.35	6	9.15	25	7.65	36	WHITE	15u"	3-1734774-4
													G/F	3-1734774-3	
8.7							71.35	70	73.15	89	71.65	164	BLACK	15u"	3-1734774-2
													G/F	3-1734774-1	
5.45				38.35	37	40.15	56	38.65	98	WHITE	15u"	3-1734774-0			
										G/F	2-1734774-9				
3.85				21.35	20	23.15	39	21.65	64	BLACK	15u"	2-1734774-8			
										G/F	2-1734774-7				
2.55				7.35	6	9.15	25	7.65	36	WHITE	15u"	2-1734774-6			
										G/F	2-1734774-5				
8.7			3.10	71.35	70	73.15	89	71.65	164	BLACK	30u"	2-1734774-4			
												WHITE	2-1734774-3		
5.45				38.35	37	40.15	56	38.65	98	BLACK		2-1734774-2			
												WHITE	2-1734774-1		
3.85				21.35	20	23.15	39	21.65	64	BLACK		2-1734774-0			
												WHITE	1-1734774-9		
2.55				7.35	6	9.15	25	7.65	36	BLACK	1-1734774-8				
											WHITE	1-1734774-7			
8.7					71.35	70	73.15	89	71.65	164	BLACK	15u"	1-1734774-6		
											G/F	1-1734774-5			
5.45					38.35	37	40.15	56	38.65	98	WHITE	15u"	1-1734774-4		
											G/F	1-1734774-3			
3.85					21.35	20	23.15	39	21.65	64	BLACK	15u"	1-1734774-2		
											G/F	1-1734774-1			
2.55					7.35	6	9.15	25	7.65	36	WHITE	15u"	1-1734774-0		
											G/F	1734774-9			
				38.35	37	40.15	56	38.65	98	BLACK	15u"	1734774-8			
										G/F	1734774-7				
				21.35	20	23.15	39	21.65	64	WHITE	15u"	1734774-6			
										G/F	1734774-5				
										15u"	1734774-4				
				7.35	6	9.15	25	7.65	36	BLACK	G/F	1734774-3			
										15u"	1734774-2				
										G/F	1734774-1				
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER			

8.8	GEN II	PA46	2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	9-1734774-7			
5.5				38.35	37	40.15	56	38.65	98	WHITE		9-1734774-6			
3.9				21.35	20	23.15	39	21.65	64	BLACK		9-1734774-5			
2.55				7.35	6	9.15	25	7.65	36	WHITE		9-1734774-4			
										BLACK		9-1734774-3			
										WHITE		9-1734774-2			
8.8							71.35	70	73.15	89	71.65	164	BLACK	15u"	8-1734774-9
													G/F	8-1734774-8	
5.5							38.35	37	40.15	56	38.65	98	WHITE	15u"	8-1734774-7
													G/F	8-1734774-6	
3.9							21.35	20	23.15	39	21.65	64	BLACK	15u"	8-1734774-5
													G/F	8-1734774-4	
2.55							7.35	6	9.15	25	7.65	36	WHITE	15u"	8-1734774-3
													G/F	8-1734774-2	
8.8							71.35	70	73.15	89	71.65	164	BLACK	15u"	8-1734774-1
													G/F	8-1734774-0	
5.5				38.35	37	40.15	56	38.65	98	WHITE	15u"	7-1734774-9			
										G/F	7-1734774-8				
3.9				21.35	20	23.15	39	21.65	64	BLACK	15u"	7-1734774-7			
										G/F	7-1734774-6				
2.55				7.35	6	9.15	25	7.65	36	WHITE	15u"	7-1734774-5			
										G/F	7-1734774-4				
8.8			3.10	71.35	70	73.15	89	71.65	164	BLACK	30u"	7-1734774-3			
												WHITE	7-1734774-2		
5.5				38.35	37	40.15	56	38.65	98	BLACK		7-1734774-1			
												WHITE	7-1734774-0		
3.9				21.35	20	23.15	39	21.65	64	BLACK		6-1734774-9			
												WHITE	6-1734774-8		
2.55				7.35	6	9.15	25	7.65	36	BLACK	6-1734774-7				
											WHITE	6-1734774-6			
8.8					71.35	70	73.15	89	71.65	164	BLACK	15u"	6-1734774-5		
											G/F	6-1734774-4			
5.5					38.35	37	40.15	56	38.65	98	WHITE	15u"	6-1734774-3		
											G/F	6-1734774-2			
3.9					21.35	20	23.15	39	21.65	64	BLACK	15u"	6-1734774-1		
											G/F	6-1734774-0			
2.55					7.35	6	9.15	25	7.65	36	WHITE	15u"	5-1734774-9		
											G/F	5-1734774-8			
				38.35	37	40.15	56	38.65	98	BLACK	15u"	5-1734774-7			
										G/F	5-1734774-6				
				21.35	20	23.15	39	21.65	64	WHITE	15u"	5-1734774-5			
										G/F	5-1734774-4				
										15u"	5-1734774-3				
				7.35	6	9.15	25	7.65	36	BLACK	G/F	5-1734774-2			
										15u"	5-1734774-1				
										G/F	5-1734774-0				
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.3

2 PLC ± 0.2

3 PLC ± 0.15

4 PLC ± -

ANGLES ± 3°

FINISH

MATERIAL

APVD

W. KODAMA

15JUL2009

PRODUCT SPEC

108-57871

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DWN

B. HSING

15JUL2009

CHK

S. CHIEN

15JUL2009

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-1734774

SCALE

SHEET

1 OF 5

REV

G

AMP 1470-19 REV 31MAR2000

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

NOTES:

1. MATERIAL:

1.1 HOUSING: 1.PA46 WITH 40% G.F, UL94 V-0, COLOR: SEE TABLE.

2.PA9T WITH 30% GF, UL94 V-0, COLOR: SEE TABLE.

1.2 CONTACT: PHOSPHOR BRONZE

2. FINISH:

CONTACT: (SEE TABLE) GOLD PLATING ON CONTACT AREA.

2.54um [100u"] MIN. MATTE-TIN PALTING ON SOLDER TAIL AREA.

1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.

3. CONNECTOR HAS MET THE REQUIREMENTS






PER PCI EXPRESS GEN 2 TECHNICAL DOCUMENT.

4. WEIGHT:


36 POS.: 2.55 GRAMS; 64 POS.: 3.90 GRAMS

98 POS.: 5.50 GRAMS; 164 POS.: 8.80 GRAMS

5. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC. 109-202 CONDITION B.

6. REFLOW SOLDER CAPABLE TO 260°C PER TEST SPEC. 109-201 CONDITION B.
(REFLOW SOLDERING PLEASE USE PN : 1734774-1 TO 4-1734774-8)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

SEE NOTE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.15
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734774


SCALE

SHEET

2 OF 5

REV

G



4

3

2

1

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	DWN
				SEE SHEET 1.		
						APVD

D

D

C


C

B

B

A

A




RECOMMENDED PCB LAYOUT


TOLERANCE: ±0.05
FOR DIM.L=3.1mm PCB THICKNESS: 2.4mm
FOR DIM.L=2.3mm PCB THICKNESS: 1.6mm

ADD-IN CARD EDGE-FINGER DIMENSIONS





NOTES:
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS



164	70.0	73.15	72.15	A1, B17, B31, B48, B81
98	37.0	40.15	39.15	A1, B17, B31, B48
64	20.0	23.15	22.15	A1, B17, B31
36	6.0	9.15	8.15	A1, B17
POS.	DIM. F	DIM. G	DIM. H	"K"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —		 TE Connectivity			
DIMENSIONS: MM		CHK —					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME			
		PRODUCT SPEC —		PCI EXPRESS CARD EDGE CONNECTOR VERTICAL, DIP TYPE, 3GIO			
		APPLICATION SPEC —					
		WEIGHT —					
		CUSTOMER DRAWING					
MATERIAL —		FINISH —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1734774	RESTRICTED TO —
				SCALE —	SHEET 4	OF 5	REV G

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1.		



NOTES :

- MATERIAL :
TRAY : PVC, COLOR: TRANSPARENT.
CARTON: CORRUGATED FIBER
BOX: CORRUGATED FIBER
- DIMENSION :
TRAY: SEE DRAWING
CARTON: SEE DRAWING
BOX : SEE DRAWING
- QUANTITY : SEE TABLE
- WEIGHT : SEE TABLE

10.2 Kg	8.2 Kg	30	10	3	900	164
9.0 Kg	7.0 Kg	40	10	3	1200	98
8.5 Kg	6.5 Kg	60	10	3	1800	64
7.6 Kg	5.6 Kg	70	10	3	2100	36
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ CARTON	CARTON/ BOX	PCS/ BOX	POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity PCI EXPRESS CARD EDGE CONNECTOR VERTICAL, DIP TYPE, 3GIO							
DIMENSIONS: MM		CHK					NAME			
		APVD					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		PRODUCT SPEC					A300779C-1734774			
MATERIAL		APPLICATION SPEC	CUSTOMER DRAWING							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT	SCALE							
0 PLC ± -			SHEET 5 OF 5							
1 PLC ± -			REV G							
2 PLC ± -										
3 PLC ± -										
4 PLC ± -										
ANGLES ± -										
FINISH										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1734774-7](#)