

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DW

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

G

REVISED PER ECR-16-003830

14MAR16

FL

SY

8.7	GEN II & GEN III		2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	4-1734774-8
5.45				38.35	37	40.15	56	38.65	98	WHITE		4-1734774-7
3.85				21.35	20	23.15	39	21.65	64	BLACK		4-1734774-6
2.55				7.35	6	9.15	25	7.65	36	WHITE		4-1734774-5
8.7				71.35	70	73.15	89	71.65	164	BLACK		4-1734774-4
										WHITE		4-1734774-3
5.45				38.35	37	40.15	56	38.65	98	BLACK	4-1734774-2	
										WHITE	4-1734774-1	
3.85				21.35	20	23.15	39	21.65	64	BLACK	15u"	
										WHITE	G/F	
2.55				7.35	6	9.15	25	7.65	36	BLACK	15u"	
										WHITE	G/F	
8.7				71.35	70	73.15	89	71.65	164	BLACK	15u"	
										WHITE	G/F	
5.45				38.35	37	40.15	56	38.65	98	BLACK	15u"	
										WHITE	G/F	
3.85	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
8.7	71.35	70	73.15	89	71.65	164	BLACK	15u"				
							WHITE	G/F				
5.45	38.35	37	40.15	56	38.65	98	BLACK	15u"				
							WHITE	G/F				
3.85	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

8.8	GEN II	PA46	2.30	71.35	70	73.15	89	71.65	164	BLACK	30u"	9-1734774-7
5.5				38.35	37	40.15	56	38.65	98	WHITE		9-1734774-6
3.9				21.35	20	23.15	39	21.65	64	BLACK		9-1734774-5
2.55				7.35	6	9.15	25	7.65	36	WHITE		9-1734774-4
8.8				71.35	70	73.15	89	71.65	164	BLACK		9-1734774-3
										WHITE		9-1734774-2
5.5				38.35	37	40.15	56	38.65	98	BLACK	9-1734774-1	
										WHITE	9-1734774-0	
3.9				21.35	20	23.15	39	21.65	64	BLACK	15u"	
										WHITE	G/F	
2.55				7.35	6	9.15	25	7.65	36	BLACK	15u"	
										WHITE	G/F	
8.8				71.35	70	73.15	89	71.65	164	BLACK	15u"	
										WHITE	G/F	
5.5				38.35	37	40.15	56	38.65	98	BLACK	15u"	
										WHITE	G/F	
3.9	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
8.8	71.35	70	73.15	89	71.65	164	BLACK	15u"				
							WHITE	G/F				
5.5	38.35	37	40.15	56	38.65	98	BLACK	15u"				
							WHITE	G/F				
3.9	21.35	20	23.15	39	21.65	64	BLACK	15u"				
							WHITE	G/F				
2.55	7.35	6	9.15	25	7.65	36	BLACK	15u"				
							WHITE	G/F				
WEIGHT(g)	PCI-E COMPLIANCE	HOUSING MATERIAL	DIM. L	DIM. E	DIM. D	DIM. C	DIM. B	DIM. A	POS.	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.3

2 PLC ± 0.2

3 PLC ± 0.15

4 PLC ± -

ANGLES ± 3°

FINISH

MATERIAL

DWN

B. HSING

15JUL2009

CHK

S. CHIEN

15JUL2009

APVD

W. KODAMA

15JUL2009

PRODUCT SPEC

108-57871

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-1734774

SCALE

SHEET

1 OF 5

REV

G

AMP 1470-19 REV 31MAR2000

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT

-

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

NOTES:

1. MATERIAL:

1.1 HOUSING: 1.PA46 WITH 40% G.F, UL94 V-0, COLOR: SEE TABLE.

2.PA9T WITH 30% GF, UL94 V-0, COLOR: SEE TABLE.

1.2 CONTACT: PHOSPHOR BRONZE

2. FINISH:

CONTACT: (SEE TABLE) GOLD PLATING ON CONTACT AREA.

2.54um [100u"] MIN. MATTE-TIN PALTING ON SOLDER TAIL AREA.

1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.

3. CONNECTOR HAS MET THE REQUIREMENTS






PER PCI EXPRESS GEN 2 TECHNICAL DOCUMENT.

4. WEIGHT:

36 POS.: 2.55 GRAMS; 64 POS.: 3.90 GRAMS

98 POS.: 5.50 GRAMS; 164 POS.: 8.80 GRAMS

5. WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC. 109-202 CONDITION B.

6. REFLOW SOLDER CAPABLE TO 260°C PER TEST SPEC. 109-201 CONDITION B.
(REFLOW SOLDERING PLEASE USE PN : 1734774-1 TO 4-1734774-8)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC


WEIGHT

SEE NOTE 4

CUSTOMER DRAWING

DIMENSIONS:

MM



MATERIAL

SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.3
2 PLC ± 0.2
3 PLC ± 0.15
4 PLC ± -
ANGLES ± 3°

FINISH

SEE NOTE



TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO


A300779C-1734774

SCALE

SHEET

2 OF 5

REV G




LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1.		

D

D


ADD-IN CARD EDGE-FINGER DIMENSIONS

NOTES:
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS




RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05
FOR DIM.L=3.1mm PCB THICKNESS: 2.4mm
FOR DIM.L=2.3mm PCB THICKNESS: 1.6mm



I/O PANEL DIRECTION
PRIMARY (COMPONENT) SIDE



SECONDARY (SOLDER) SIDE

164	70.0	73.15	72.15	A1, B17, B31, B48, B81
98	37.0	40.15	39.15	A1, B17, B31, B48
64	20.0	23.15	22.15	A1, B17, B31
36	6.0	9.15	8.15	A1, B17
POS.	DIM. F	DIM. G	DIM. H	"K"

C


C

B

B

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — CHK — APVD —		 TE Connectivity									
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME									
				PCI EXPRESS CARD EDGE CONNECTOR VERTICAL, DIP TYPE, 3GIO									
MATERIAL —		PRODUCT SPEC —		APPLICATION SPEC —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
FINISH —		WEIGHT —		CUSTOMER DRAWING		A3		00779		C-1734774		—	
						SCALE —		SHEET		4 OF 5		REV G	



TE Connectivity

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO


A300779C=1734774

SCALE SHEET 4 OF 5 REV G

LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1.		



- NOTES :
- MATERIAL :
TRAY : PVC, COLOR: TRANSPARENT.
CARTON: CORRUGATED FIBER
BOX: CORRUGATED FIBER
 - DIMENSION :
TRAY: SEE DRAWING
CARTON: SEE DRAWING
BOX : SEE DRAWING
 - QUANTITY : SEE TABLE
 - WEIGHT : SEE TABLE



10.2 Kg	8.2 Kg	30	10	3	900	164
9.0 Kg	7.0 Kg	40	10	3	1200	98
8.5 Kg	6.5 Kg	60	10	3	1800	64
7.6 Kg	5.6 Kg	70	10	3	2100	36
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ CARTON	CARTON/ BOX	PCS/ BOX	POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

PCI EXPRESS CARD EDGE CONNECTOR
VERTICAL, DIP TYPE, 3GIO

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734774

SCALE

SHEET 5 OF 5

REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1734774-9](#)