










2		1						
LOC	DIST	REVISIONS						
DY	-	P	LTR	DESCRIPTION		DATE	DWN	APVD
			-	SEE SHEET 1		-	-	-





P/N X- -1
(1.8V RVS)
SCALE 3:2



P/N X- -2
(1.5V RVS)
SCALE 3:2



P/N X- -3
(1.8V STD)
SCALE 3:2



P/N X- -4
(1.5V STD)
SCALE 3:2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	18MAY2007	TE TE CONNECTIVITY Singapore		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK YJ SEE	APVD SF LEONG	NAME ASSEMBLY, MINIDIMM, R/A, LF 0.60mm PITCH, 244 CKTS, DDR2/3		
	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ±0.10 4 PLC ± ANGLES ±1°	PRODUCT SPEC 108-51091				
MATERIAL 	FINISH SEE P/N TABLE	APPLICATION SPEC 114-51011	SIZE A3	CAGE CODE 00779	DRAWING NO C-1735438	
		WEIGHT -	SCALE 3:2 SHEET 2 OF 5 REV B5			
CUSTOMER DRAWING						

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DY

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

PIN 122 FOR P/N -3/-4 (STD)
PIN 123 FOR P/N -1/-2 (RVS)PIN 1 FOR P/N -3/-4 (STD)
PIN 244 FOR P/N -1/-2 (RVS)

1.57±0.10

Ø2.50±0.05

7.20 REF

1.50 REF

14.30
REF7.20
REFPIN 1 FOR P/N -1/-2 (RVS)
PIN 244 FOR P/N -3/-4 (STD)4.00 REF
2 PLC

SEE DETAIL A

Ø2.50±0.05
Ø0.10 G E-FPIN 122 FOR P/N -1/-2 (RVS)
PIN 123 FOR P/N -3/-4 (STD)

2.60±0.05

Ø0.10 G E-F
2 PLC

0.60 TYP

0.35±0.03

Ø0.10 G E-F

2.00±0.03

Ø0.10 G E-F

5.00

Ø0.10 G E-F

4.59

4.59


3.35

5.35




DETAIL A
SCALE 4:1


NOTES:

21 PCB THICKNESS IS NOT PART OF THE RECOMMENDED DIMENSIONS FOR THIS PRODUCT.
THE DESIGN OF THIS CONNECTOR IS NOT DEPENDENT ON THE PCB THICKNESS.RECOMMENDED PCB LAYOUT
(AS SHOWN FOR X- -1/-2 RVS)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE 18MAY2007	 TE CONNECTIVITY Singapore		
DIMENSIONS: mm		CHK YJ SEE			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ±0.10 4 PLC ± ANGLES ±1°	APVD SF LEONG	NAME ASSEMBLY, MINIDIMM, R/A, LF 0.60mm PITCH, 244 CKTS, DDR2/3		
		PRODUCT SPEC 108-51091			
			APPLICATION SPEC 114-51011	SIZE A3	CAGE CODE 00779
MATERIAL	FINISH	WEIGHT -			
CUSTOMER DRAWING			SCALE 2:1	SHEET 3 OF 5	REV B5

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DY	-		-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	18MAY2007		 TE CONNECTIVITY Singapore			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK YJ SEE	NAME ASSEMBLY, MINIDIMM, R/A, LF 0.60mm PITCH, 244 CKTS, DDR2/3					
		APVD SF LEONG						
	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ±0.10 4 PLC ± ANGLES ±1°	PRODUCT SPEC 108-51091	DRAWING NO C-1735438					
		APPLICATION SPEC 114-51011						
		MATERIAL	FINISH	WEIGHT -	SIZE A3	CAGE CODE 00779	SCALE 1:1	SHEET 5 OF 5
		CUSTOMER DRAWING						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1735438-3](#)