




8.70

2 PLC REF
(TO CONTACT
MID PLANE)

93.00 REF

75.60

E1

F1 X 0.6

E2

F2 X 0.6

1.8V
RVS
LCP-GF-MD45

DATE CODE

PART NUMBER

20.45

52.65 REF
LATCH OPEN

48.00 REF
LATCH CLOSED

9.79

5.30
2 PLC

0.60 TYP
(PITCH)

1.80

2.40 REF

0.150 TYP
0.10 X Y Z
(SOLDERTAIL WIDTH)

6.29 REF
(SEATING HEIGHT OF
THE MODULE CARD)

Ø2.40 REF
3 PLC

2.46
3 PLC

6.55
REF

CL OF HOUSING

CL OF THE MODULE CARD

1

2

3

4

5

6

MATERIAL: HOUSING: HIGH TEMP LCP, BLACK, UL94V-0
LATCHES: HIGH TEMP LCP, NATURAL, UL94V-0
CONTACTS: COPPER ALLOY
SOLDERPEGS: COPPER ALLOY

FINISH: ENGAGEMENT AREAS: 0.76µm MIN GOLD OVER
1.25µm MIN NICKEL
SOLDERTAILS: 0.02µm MIN GOLD OVER
1.25µm MIN NICKEL

FINISH: ENGAGEMENT AREAS: 0.38µm MIN GOLD OVER
1.25µm MIN NICKEL
SOLDERTAILS: 0.02µm MIN GOLD OVER
1.25µm MIN NICKEL

ACCEPTS 1.0mm THICK MEMORY MODULE, PER JEDEC MO-244,
WITH BEVELS (FOR INSERTION LEAD-IN) REQUIRED.

PRODUCT SHALL BE PACKED IN JEDEC HARD TRAY (BLACK).

PART NUMBER AND DATE CODE SHALL BE MARKED LEGIBLY
AS SHOWN. DATE CODE FORMAT: YYWWD.

64	56	38.4	33.6	45.5	40.7	DDR3 (AB/BB/CB) ; STD	1.5V	3	1- -4
64	56	38.4	33.6	45.5	40.7	DDR2 (AA/BA/CA) ; STD	1.8V	3	1- -3
56	64	33.6	38.4	40.7	45.5	DDR3 (AB/BB/CB) ; RVS	1.5V	3	1- -2
56	64	33.6	38.4	40.7	45.5	DDR2 (AA/BA/CA) ; RVS	1.8V	3	1- -1
64	56	38.4	33.6	45.5	40.7	DDR3 (AB/BB/CB) ; STD	1.5V	2	-4
64	56	38.4	33.6	45.5	40.7	DDR2 (AA/BA/CA) ; STD	1.8V	2	-3
56	64	33.6	38.4	40.7	45.5	DDR3 (AB/BB/CB) ; RVS	1.5V	2	-2
56	64	33.6	38.4	40.7	45.5	DDR2 (AA/BA/CA) ; RVS	1.8V	2	-1
F2	F1	E2	E1	B2	B1	variation ; ORIENTATION MODULE	VOLTAGE MARKING	CONTACT FINISH	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.25
2 PLC ±0.13
3 PLC ±0.10
4 PLC ±
ANGLES ±1°

FINISH
SEE
P/N TABLE

DWN
WYLEE

CHK
YJ SEE

APVD
SE LEONG

PRODUCT SPEC
108-51091

APPLICATION SPEC
114-51011

WEIGHT
-

CUSTOMER DRAWING

18MAY2007

TE CONNECTIVITY
Singapore

NAME
ASSEMBLY, MINIDIMM, R/A, LF
0.60mm PITCH, 244 CKTS,
DDR2/3

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1735438

SCALE
1:1

SHEET
1



OF
5

REV
B5



P/N -1 AS SHOWN

AMP 1470-19 REV 09MAY94



LOC		DIST		REVISIONS					
DY		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-





P/N X- -1
(1.8V RVS)
SCALE 3:2




P/N X- -2
(1.5V RVS)
SCALE 3:2



P/N X- -3
(1.8V STD)
SCALE 3:2



P/N X- -4
(1.5V STD)
SCALE 3:2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	18MAY2007	 TE CONNECTIVITY Singapore	
DIMENSIONS: mm		CHK YJ SEE			
	0 PLC	±		NAME ASSEMBLY, MINIDIMM, R/A, LF 0.60mm PITCH, 244 CKTS, DDR2/3	
	1 PLC	±0.25			
	2 PLC	±0.13			
	3 PLC	±0.10			
MATERIAL 	4 PLC	±		SIZE A3	
	ANGLES	±1°			
FINISH SEE P/N TABLE		PRODUCT SPEC 108-51091		CAGE CODE 00779	
		APPLICATION SPEC 114-51011		DRAWING NO C-1735438	
		WEIGHT -		SCALE 3:2	
		CUSTOMER DRAWING		SHEET 2 OF 5	
				REV B5	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DY

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

PIN 122 FOR P/N -3/-4 (STD)
PIN 123 FOR P/N -1/-2 (RVS)PIN 1 FOR P/N -3/-4 (STD)
PIN 244 FOR P/N -1/-2 (RVS)

1.57±0.10

Ø2.50±0.05

7.20 REF

1.50 REF

7.20 REF

14.30 REF

3.60
2 PLC

E1

1.80

E2

1.80

Ø2.50±0.05

Ø0.10 G E

4.59

5.00±0.05

Ø0.10 G E-F

4 PLC

4.59

PIN 1 FOR P/N -1/-2 (RVS)
PIN 244 FOR P/N -3/-4 (STD)4.00 REF
2 PLC

SEE DETAIL A

Ø2.50±0.05

Ø0.10 G E-F

PIN 122 FOR P/N -1/-2 (RVS)
PIN 123 FOR P/N -3/-4 (STD)

2.60±0.05

Ø0.10 G E-F

2 PLC

0.60 TYP

0.35±0.03

Ø0.10 G E-F

2.00±0.03

Ø0.10 G E-F

5.30

B1

B2

5.30

4.80±0.05

Ø0.10 G E-F

4 PLC

86.20

5.00
Ø0.10 G E-F

4.59

4.59


3.35


5.35

RECOMMENDED PCB LAYOUT
(AS SHOWN FOR X- -1/-2 RVS)DETAIL A
SCALE 4:1




NOTES:

21 PCB THICKNESS IS NOT PART OF THE RECOMMENDED DIMENSIONS FOR THIS PRODUCT.
THE DESIGN OF THIS CONNECTOR IS NOT DEPENDENT ON THE PCB THICKNESS.


THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	18MAY2007	 TE CONNECTIVITY Singapore	
		CHK YJ SEE			
DIMENSIONS: mm		APVD SF LEONG		NAME ASSEMBLY, MINIDIMM, R/A, LF 0.60mm PITCH, 244 CKTS, DDR2/3	
		PRODUCT SPEC 108-51091			
		APPLICATION SPEC 114-51011		SIZE A3	CAGE CODE 00779
MATERIAL		FINISH	WEIGHT -	DRAWING NO C-1735438	
		CUSTOMER DRAWING		SCALE 2:1	SHEET 3 OF 5
				REV B5	



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DY	-		-	SEE SHEET 1	-	-	-



DETAIL A
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	18MAY2007	 TE CONNECTIVITY Singapore			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK YJ SEE	APVD SF LEONG	NAME ASSEMBLY, MINIDIMM, R/A, LF 0.60mm PITCH, 244 CKTS, DDR2/3			
	0 PLC ±°	PRODUCT SPEC 108-51091	APPLICATION SPEC 114-51011	SIZE A3	CAGE CODE 00779	DRAWING NO C-1735438	
	1 PLC ±0.25	WEIGHT -		SCALE 1:1	SHEET 5	OF 5	REV B5
	2 PLC ±0.13						
	3 PLC ±0.10						
	4 PLC ±°						
MATERIAL	FINISH						
CUSTOMER DRAWING							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1735438-1](#)