




THIS DRAWING IS UNPUBLISHED.  
 RELEASED FOR PUBLICATION 20  
 BY -  
 ALL RIGHTS RESERVED.

© COPYRIGHT 20 BY -

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-16-004435	15APR2016	KG	EO



MATING FACE



REAR FACE

1) FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.  
 CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194  
 REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1

2) DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER GPRBE14SB  
 THIS INSERT CONTAINS: 14 CAVITIES FOR SIZE 16 SOCKET CONTACTS.

4. THIS PRODUCT IS SOLD BY TE CONNECTIVITY UNDER A LICENSE FROM RADIALL SA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN BH CHK JPM APVD IPM	29JUN2006 29JUN2006 29JUN2006 29JUN2006
	0 PLC $\pm 0.1$ 1 PLC $\pm 0.05$ 2 PLC $\pm 0.05$ 3 PLC $\pm 0.05$ 4 PLC $\pm 0.05$	PRODUCT SPEC - APPLICATION SPEC - MATERIAL	
	ANGLES $\pm 1^\circ$	FINISH	WEIGHT -
			CUSTOMER DRAWING
			SCALE 4:1 SHEET 1 OF 1 REV A
			RESTRICTED TO A 200779 C=1738124

617999252 1738124-1  
 RADIALL PART NUMBER

TE Connectivity

INSERT ASSEMBLY, SOCKET,  
 ENVIRONMENTAL,  
 ARRANGEMENT 14, KEY B, GPRB

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1738124-1](#)