




OBSOLETE	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	1-1761682-5
	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	1-1761682-3
	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	1-1761682-1
OBSOLETE	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	1761682-9
	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	1761682-7
	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	1761682-6
	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	1761682-5
	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	1761682-3
	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. <u>B.CRISAMORE/DTI</u> 23MAY05 CHK. <u>S.BOLASH</u> 23MAY05		 TE Connectivity		
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 23MAY05 <u>M.WALMSLEY</u> 23MAY05				
	0 PLC ± -	PRODUCT SPEC	NAME	HEADER ASSEMBLY, HIGH TEMP, RIGHT ANGLE, LOW PROFILE, IDC		
	1 PLC ± -	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	
	2 PLC ± -		RESTRICTED TO	A1	00779	C1761682
	4 PLC ± -					
ANGLES ± - MATERIAL 	FINISH	WEIGHT -	CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1	
				REV A1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1761682-3](#)