


|                                                                      |          |                                  |            |
|----------------------------------------------------------------------|----------|----------------------------------|------------|
| 8                                                                    |          | 7                                |            |
| THIS DRAWING IS UNPUBLISHED.                                         |          | RELEASED FOR PUBLICATION         |            |
| 20                                                                   |          | 20                               |            |
| © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED. |          |                                  |            |
| PART NUMBER                                                          | REVISION | DESCRIPTION                      | FEED TYPE  |
| 2836229-1                                                            | C        | FINE CRIMP HEIGHT ADJUST         | MECHANICAL |
| 2836229-2                                                            | C        | FINE CRIMP HEIGHT ADJUST         | PNEUMATIC  |
| 7-2836229-1                                                          | C        | MECHANICAL AND CRIMP TOOLING KIT | MECHANICAL |
| 7-2836229-2                                                          | C        | PNEUMATIC AND CRIMP TOOLING KIT  | PNEUMATIC  |
| 7-2836229-7                                                          | A        | CRIMP TOOLING KIT                | -          |

ATLANTIC VERSION TERMINATOR  
INTERFACE ADAPTER



|                                      |                |      |
|--------------------------------------|----------------|------|
| APPLICATOR DATA                      |                |      |
| CRIMP                                | SIZE           | TYPE |
| WIRE                                 | 1.60 mm [.063] | F    |
| INSUL                                | 1.83 mm [.072] | O    |
| APPLICATOR INSTRUCTIONS<br>408-35042 |                |      |

|                                    |  |                   |                                                                                   |                              |   |
|------------------------------------|--|-------------------|-----------------------------------------------------------------------------------|------------------------------|---|
| TERMINAL DATA: SUMITOMO TERMINAL   |  |                   |                                                                                   | VW CRIMP SPECIFICATION       |   |
| TERMINAL NAME: TERMINAL, FEMALE    |  |                   |                                                                                   |                              |   |
| WIRE STRIP LENGTH                  |  |                   |  | INSULATION DIAMETER RANGE    |   |
| 3.05-3.81 mm [.120-.150 IN]        |  |                   |                                                                                   | Ø1.40-1.70 mm [.055-.067 IN] |   |
| TERMINAL APPLICATION SPECIFICATION |  |                   |  | N .107.773.                  |   |
|                                    |  |                   | -                                                                                 | -                            | - |
| TERMINALS APPLIED                  |  |                   |                                                                                   |                              |   |
| TE TERMINAL                        |  | SUMITOMO TERMINAL |                                                                                   | TE TERMINAL                  |   |
| 2113483-1                          |  | 8240-0360         |                                                                                   | 2113483-2                    |   |
|                                    |  |                   |                                                                                   | 8240-0358                    |   |

|           |                            |                                |
|-----------|----------------------------|--------------------------------|
| WIRE SIZE | CRIMP HEIGHT mm [INCH]     | CRIMP HEIGHT REFERENCE SETTING |
| 0.50mm2   | 0.96+/-0.03 [.038+/- .001] | 7.6                            |
| 0.35mm2   | 0.94+/-0.03 [.037+/- .001] | 7.8                            |



- 1 RECOMMENDED SPARE PARTS
- 2 REFER TO SUPPLIED INSTRUCTION SHEET FOR CLEANING, LUBRICATION AND STORAGE OF APPLICATOR.
- 3 APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.
- 4 CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.
5. UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.

\*WARNING  
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING, REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

ATLANTIC VERSION  
Shown on sheets 1 of 4 & 2 of 4  
(Pacific version shown on sheets 3 of 4 & 4 of 4)

|     |      |           |     |               |           |     |      |
|-----|------|-----------|-----|---------------|-----------|-----|------|
| 2   |      | 1         |     |               |           |     |      |
| LOC | DIST | REVISIONS |     |               |           |     |      |
| A   | 66   | P         | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|     |      | A         |     | RELEASE       | 18MAR2016 | XZ  | UG   |
|     |      | B         |     | ECR-19-001216 | 24JAN2019 | FL  | CT   |
|     |      | C         |     | ECR-20-017075 | 07DEC2020 | FZ  | RK   |
|     |      |           |     |               |           |     |      |


|     |     |     |     |     |             |                                     |         |
|-----|-----|-----|-----|-----|-------------|-------------------------------------|---------|
| -   | 1   | -   | 1   | -   | 2119641-1   | FEED CAM, AIR FEED                  | 248     |
| -   | 1   | 1   | 1   | 1   | 2119082-4   | CAM, SNAIL, INSULATION ADJUSTMENT   | 244     |
| -   | 1   | 1   | 1   | 1   | 2079764-1   | WASHER, WAVE SPRING, CREST-TO-CREST | 243     |
| -   | 1   | 1   | 1   | 1   | 2119083-1   | RETAINER, INSULATION DIAL           | 242     |
| -   | 1   | 1   | 1   | 1   | 7-18023-7   | SCR, SKT HD CAP M3 X 4.0            | 241     |
| -   | -   | 1   | -   | 1   | 2119580-1   | MECHANICAL FEED ASSEMBLY            | 239     |
| -   | 1   | -   | 1   | -   | 2844940-1   | AIR FEED MODULE                     | 238     |
| -   | REF | REF | REF | REF | 994970-2    | COUNTER, MAGNETIC                   | 164     |
| -   | 1   | 1   | 1   | 1   | 2844908-1   | SCREW, LOCKING                      | 99      |
| -   | 1   | 1   | 1   | 1   | 2844907-1   | POST, LOCKING                       | 98      |
| -   | 1   | 1   | 1   | 1   | 455888-5    | SPACER, CRIMPER                     | 82      |
| -   | 1   | 1   | 1   | 1   | 1803607-3   | DOCUMENTATION PACKAGE               | 71      |
| -   | 1   | 1   | 1   | 1   | 2119791-9   | DEPRESSOR, WIRE                     | 70      |
| -   | 1   | 1   | 1   | 1   | 2119740-1   | TAG,IDENTIFICATION                  | 67      |
| -   | 2   | 2   | 2   | 2   | 2168078-1   | SCREW, DRIVE, RH, RoHS, 2 x .188    | 66      |
| -   | 1   | 1   | 1   | 1   | 2168083-2   | SCR, SKT HD CAP, RoHS, M4 X 8.0     | 60      |
| -   | 1   | 1   | 1   | 1   | 5-18022-5   | SCR, HEX HD CAP, M4 X 6.0           | 59      |
| -   | 1   | 1   | 1   | 1   | 1338685-1   | PAWL, FEED                          | 56      |
| -   | 4   | 4   | 4   | 4   | 2168083-3   | SCR, SKT HD CAP, RoHS, M4 X 12.0    | 54      |
| -   | 2   | 2   | 2   | 2   | 1-2168083-0 | SCR, SKT HD CAP, RoHS, M4 X 10      | 53      |
| -   | 1   | 1   | 1   | 1   | 1803382-6   | HOLD DOWN, SPRING LOADED            | 50      |
| -   | 1   | 2   | 1   | 2   | 18023-9     | SCR, SKT HD CAP M4 X 6.0            | 49      |
| -   | -   | 1   | -   | 1   | 2119652-1   | FEED CAM, PRE FEED                  | 48      |
| -   | -   | 1   | -   | 1   | 2119653-1   | FEED CAM, POST FEED                 | 47      |
| -   | 1   | 1   | 1   | 1   | 1803583-9   | APPLICATOR BASIC ASSEMBLY, SF       | 46      |
| -   | 1   | 1   | 1   | 1   | 1803515-1   | RAM ASSEMBLY, SF ATLANTIC           | 44      |
| -   | 1   | 1   | 1   | 1   | 1803602-1   | SCR, BHSC, RoHS (M8 X 25)           | 41      |
| -   | 1   | 1   | 1   | 1   | 1752356-3   | SUPPORT, TERMINAL                   | 34      |
| -   | 2   | 2   | 2   | 2   | 2079383-5   | SCR, BHSC, RoHS (M4 X 20)           | 33      |
| -   | 2   | 2   | 2   | 2   | 2-2844962-4 | SPACER, CYLINDRICAL, STRIP GUIDE    | 30      |
| -   | 1   | 1   | 1   | 1   | 2844992-1   | ASSEMBLY, STRIP GUIDE               | 29      |
| -   | 1   | 1   | 1   | 1   | 1320928-2   | STRIP GUIDE                         | 24      |
| -   | 1   | 1   | 1   | 1   | 2168083-2   | SCR, SKT HD CAP, RoHS, M4 X 8.0     | 21      |
| -   | 2   | 2   | 2   | 2   | 1-18028-2   | WASHER, FLAT, REG M4                | 20      |
| -   | 1   | 1   | 1   | 1   | 2119533-1   | STRIPPER, SIDE FEED                 | 19      |
| -   | 1   | 1   | 1   | 1   | 2119806-1   | INSERT, SHEAR                       | 13      |
| -   | 1   | 1   | 1   | 1   | 3-22280-3   | SPRING, COMPRESSION                 | 12      |
| -   | 1   | 1   | 1   | 1   | 1-356885-4  | STOP, SHEAR                         | 11      |
| -   | 1   | 1   | 1   | 1   | 2119805-1   | SHEAR HOLDER, FRONT                 | 10      |
| -   | 1   | 1   | 1   | 1   | 1803095-1   | FLOATING SHEAR, FRONT               | 9       |
| 1   | 2   | 2   | 1   | 1   | 3-1803058-5 | ANVIL, COMBINATION                  | 8       |
| -   | -   | -   | -   | -   | -           | -                                   | 7       |
| -   | -   | -   | -   | -   | -           | -                                   | 6       |
| -   | 1   | 1   | 1   | 1   | 2119757-6   | DEPRESSOR, SHEAR                    | 5       |
| -   | 1   | 1   | 1   | 1   | 1-238011-7  | BLOCK, CRIMPER SPACER               | 4       |
| 1   | 2   | 2   | 1   | 1   | 5-2119784-1 | CRIMPER, INSULATION O PREMIUM       | 3       |
| -   | 1   | 1   | 1   | 1   | 455888-7    | SPACER, CRIMPER                     | 2       |
| 1   | 2   | 2   | 1   | 1   | 8-1633588-1 | CRIMPER, WIRE                       | 1       |
| -77 | -72 | -71 | -2  | -1  | PART NO     | DESCRIPTION                         | ITEM NO |

|                                                                                                                                               |  |  |  |                                        |         |           |                                              |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|----------------------------------------|---------|-----------|----------------------------------------------|--|
| THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION. |  |  |  | DWN                                    | X.ZHAO  | 25FEB2016 | TE Connectivity<br>Harrisburg, PA 17105-3608 |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                                                                        |  |  |  | CHK                                    | L.ZHANG | 25FEB2016 | NAME                                         |  |
| DIMENSIONS:                                                                                                                                   |  |  |  | APVD                                   | J.GUO   | 25FEB2016 | PRODUCT SPEC                                 |  |
| mm                                                                                                                                            |  |  |  | APPLICATION SPEC                       |         |           |                                              |  |
| 0 PLC ±                                                                                                                                       |  |  |  | WEIGHT                                 |         |           |                                              |  |
| 1 PLC ±                                                                                                                                       |  |  |  | Customer Accessible Production Drawing |         |           |                                              |  |
| 2 PLC ±                                                                                                                                       |  |  |  | SCALE                                  |         |           |                                              |  |
| 3 PLC ±                                                                                                                                       |  |  |  | SHEET                                  |         |           |                                              |  |
| 4 PLC ±                                                                                                                                       |  |  |  | REV                                    |         |           |                                              |  |
| ANGLES                                                                                                                                        |  |  |  | C                                      |         |           |                                              |  |
| FINISH                                                                                                                                        |  |  |  |                                        |         |           |                                              |  |




| LOC |    | DIST |     | REVISIONS   |      |     |      |
|-----|----|------|-----|-------------|------|-----|------|
| A   | 66 | P    | LTR | DESCRIPTION | DATE | DWN | APVD |
|     |    | -    |     | SEE SHEET 1 | -    | -   | -    |
|     |    |      |     |             |      |     |      |
|     |    |      |     |             |      |     |      |


# FEED TYPE MECHANICAL



## PNEUMATIC






### FEED SPRING SETTING POSITION (SHOWN FROM REAR SIDE)




DETAIL A


# CAM POSITIONS



TERMINAL SUPPORT LOCATION



RAM SET-UP



FEED TRACK POSITION  
GUIDE BY INSULATION BARREL


ATLANTIC VERSION  
Shown on sheets 1 of 4 & 2 of 4  
(Pacific version shown on sheets 3 of 4 & 4 of 4)

|             |  |                                        |  |                                        |  |                        |  |                       |  |           |  |
|-------------|--|----------------------------------------|--|----------------------------------------|--|------------------------|--|-----------------------|--|-----------|--|
| DIMENSIONS: |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | DWN X. ZHAO 25FEB2016                  |  | CHK L. ZHANG 25FEB2016 |  | APVD J. GUO 25FEB2016 |  | NAME      |  |
| mm          |  | 0 PLC ±.1                              |  | 1 PLC ±.1                              |  | 2 PLC ±.1              |  | 3 PLC ±.1             |  | 4 PLC ±.1 |  |
| ANGLES      |  | FINISH                                 |  | PRODUCT SPEC                           |  | APPLICATION SPEC       |  | SIZE                  |  | CAGE CODE |  |
| MATERIAL    |  | WEIGHT                                 |  | Customer Accessible Production Drawing |  | SCALE 1:2              |  | SHEET 2 OF 4          |  | REV C     |  |



|                                                                    |          |                          |            |
|--------------------------------------------------------------------|----------|--------------------------|------------|
| 8                                                                  |          | 7                        |            |
| THIS DRAWING IS UNPUBLISHED.                                       |          | RELEASED FOR PUBLICATION |            |
| 20                                                                 |          | 20                       |            |
| COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED. |          |                          |            |
| PART NUMBER                                                        | REVISION | DESCRIPTION              | FEED TYPE  |
| 2-2836229-1                                                        | C        | FINE CRIMP HEIGHT ADJUST | MECHANICAL |
| 2-2836229-2                                                        | C        | FINE CRIMP HEIGHT ADJUST | PNEUMATIC  |
| 7-2836229-7                                                        | A        | CRIMP TOOLING KIT        | -          |

PACIFIC VERSION TERMINATOR  
INTERFACE ADAPTER



| APPLICATOR DATA                      |                |      |
|--------------------------------------|----------------|------|
| CRIMP                                | SIZE           | TYPE |
| WIRE                                 | 1.60 mm [.063] | F    |
| INSUL                                | 1.83 mm [.072] | O    |
| APPLICATOR INSTRUCTIONS<br>408-35042 |                |      |

|                                                         |                   |                                                           |                   |
|---------------------------------------------------------|-------------------|-----------------------------------------------------------|-------------------|
| TERMINAL DATA: SUMITOMO TERMINAL VW CRIMP SPECIFICATION |                   |                                                           |                   |
| TERMINAL NAME: TERMINAL, FEMALE                         |                   |                                                           |                   |
| WIRE STRIP LENGTH<br>3.05-3.81 mm [.120-.150 IN]        |                   | INSULATION DIAMETER RANGE<br>Ø1.40-1.70 mm [.055-.067 IN] |                   |
| TERMINAL APPLICATION SPECIFICATION                      | N .107.773.       | -                                                         | -                 |
| TERMINALS APPLIED                                       |                   |                                                           |                   |
| TE TERMINAL                                             | SUMITOMO TERMINAL | TE TERMINAL                                               | SUMITOMO TERMINAL |
| 2113483-1                                               | 8240-0360         | 2113483-2                                                 | 8240-0358         |

|           |                            |                                |
|-----------|----------------------------|--------------------------------|
| WIRE SIZE | CRIMP HEIGHT mm [INCH]     | CRIMP HEIGHT REFERENCE SETTING |
| 0.50mm2   | 0.96+/-0.03 [.038+/- .001] | 7.6                            |
| 0.35mm2   | 0.94+/-0.03 [.037+/- .001] | 7.8                            |



- RECOMMENDED SPARE PARTS
- REFER TO SUPPLIED INSTRUCTION SHEET FOR CLEANING, LUBRICATION AND STORAGE OF APPLICATOR.
- APPLY PART NUMBER 2-23419-6 LOCTITE TO THREADS OF ITEM 242.
- CRIMP HEIGHT REFERENCE SETTING WAS THE SETTING USED WHEN THE APPLICATOR WAS QUALIFIED AT THE FACTORY. ADJUSTMENT MAY BE NECESSARY WHEN RUNNING APPLICATOR IN THE FIELD.
- UNLESS SPECIFIED OTHERWISE TORQUE VALUES SHALL BE USED PER DOCUMENT, 101-35000.

**\*WARNING**  
ON INSTALLATION, SET WIRE DISC TO CRIMP HEIGHT REFERENCE SETTING FOR LARGEST WIRE SIZE. CRIMP HEIGHT REFERENCE SETTINGS GREATER THAN THE VALUE SHOWN MAY CAUSE DAMAGE TO THE CRIMP TOOLING, REFER TO THE INSTRUCTION SHEET FOR PROPER SETUP AND ADJUSTMENTS.

PACIFIC VERSION  
Shown on sheets 3 of 4 & 4 of 4  
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

| LOC |  | DIST |  | REVISONS |     |             |      |
|-----|--|------|--|----------|-----|-------------|------|
| A   |  | 66   |  | P        | LTR | DESCRIPTION | DATE |
|     |  |      |  |          | -   | SEE SHEET 1 | -    |
|     |  |      |  |          |     |             |      |
|     |  |      |  |          |     |             |      |
|     |  |      |  |          |     |             |      |

|   |   |     |     |             |                                     |     |
|---|---|-----|-----|-------------|-------------------------------------|-----|
|   | - | 1   | 1   | 2119082-4   | CAM, SNAIL, INSULATION ADJUSTMENT   | 244 |
|   | - | 1   | 1   | 2079764-1   | WASHER, WAVE SPRING, CREST-TO-CREST | 243 |
| 3 | - | 1   | 1   | 2119083-1   | RETAINER, INSULATION DIAL           | 242 |
|   | - | 1   | 1   | 7-18023-7   | SCR, SKT HD CAP M3 X 4.0            | 241 |
|   | - | -   | 1   | 2119580-1   | MECHANICAL FEED ASSEMBLY            | 239 |
|   | - | 1   | -   | 2844940-1   | AIR FEED MODULE                     | 238 |
|   | - | REF | REF | 994970-2    | COUNTER, MAGNETIC                   | 164 |
|   | - | 1   | -   | 2119641-2   | FEED CAM, AIR FEED                  | 151 |
|   | - | 1   | 1   | 2168083-8   | SCR, SKT HD CAP, RoHS, M4 X 16      | 144 |
|   | - | 4   | 4   | 2168083-9   | SCR, SKT HD CAP, RoHS, M4 X 20      | 143 |
|   | - | -   | 1   | 2119653-2   | FEED CAM, POST FEED                 | 142 |
|   | - | 1   | 1   | 1-1803583-0 | APPLICATOR BASIC ASSEMBLY, SF       | 141 |
|   | - | 1   | 1   | 1803516-1   | RAM ASSEMBLY, SF PACIFIC            | 140 |
|   | - | 1   | 1   | 2844908-1   | SCREW, LOCKING                      | 99  |
|   | - | 1   | 1   | 2844907-1   | POST, LOCKING                       | 98  |
|   | - | 1   | 1   | 455888-5    | SPACER, CRIMPER                     | 82  |
|   | - | 1   | 1   | 1803607-3   | DOCUMENTATION PACKAGE               | 71  |
|   | - | 1   | 1   | 2119791-9   | DEPRESSOR, WIRE                     | 70  |
|   | - | 1   | 1   | 2119740-1   | TAG, IDENTIFICATION                 | 67  |
|   | - | 2   | 2   | 2168078-1   | SCREW, DRIVE, RH, RoHS, 2 x .188    | 66  |
|   | - | 1   | 1   | 5-18022-5   | SCR, HEX HD CAP, M4 X 6.0           | 59  |
|   | - | 1   | 1   | 1338685-1   | PAWL, FEED                          | 56  |
|   | - | 2   | 2   | 1-2168083-0 | SCR, SKT HD CAP, RoHS, M4 X 10      | 53  |
|   | - | 1   | 1   | 1803382-6   | HOLD DOWN, SPRING LOADED            | 50  |
|   | - | 1   | 2   | 18023-9     | SCR, SKT HD CAP M4 X 6.0            | 49  |
|   | - | -   | 1   | 2119652-1   | FEED CAM, PRE FEED                  | 48  |
|   | - | 1   | 1   | 1803602-1   | SCR, BHSC, RoHS (M8 X 25)           | 41  |
|   | - | 1   | 1   | 1752356-3   | SUPPORT, TERMINAL                   | 34  |
|   | - | 2   | 2   | 2079383-5   | SCR, BHSC, RoHS (M4 X 20)           | 33  |
|   | - | 2   | 2   | 2-2844962-4 | SPACER, CYLINDRICAL, STRIP GUIDE    | 30  |
|   | - | 1   | 1   | 2844992-1   | ASSEMBLY, STRIP GUIDE               | 29  |
|   | - | 1   | 1   | 1320928-2   | STRIP GUIDE                         | 24  |
|   | - | 1   | 1   | 2168083-2   | SCR, SKT HD CAP, RoHS, M4 X 8.0     | 21  |
|   | - | 2   | 2   | 1-18028-2   | WASHER, FLAT, REG M4                | 20  |
|   | - | 1   | 1   | 2119533-1   | STRIPPER, SIDE FEED                 | 19  |
| 1 | - | 1   | 1   | 2119806-1   | INSERT, SHEAR                       | 13  |
|   | - | 1   | 1   | 3-22280-3   | SPRING, COMPRESSION                 | 12  |
|   | - | 1   | 1   | 1-356885-4  | STOP, SHEAR                         | 11  |
| 1 | - | 1   | 1   | 2119805-1   | SHEAR HOLDER, FRONT                 | 10  |
| 1 | - | 1   | 1   | 1803095-1   | FLOATING SHEAR, FRONT               | 9   |
| 1 | 1 | 1   | 1   | 3-1803058-5 | ANVIL, COMBINATION                  | 8   |
|   | - | -   | -   | -           | -                                   | 7   |
|   | - | -   | -   | -           | -                                   | 6   |
|   | - | 1   | 1   | 2119757-6   | DEPRESSOR, SHEAR                    | 5   |
|   | - | 1   | 1   | 1-238011-7  | BLOCK, CRIMPER SPACER               | 4   |
| 1 | 1 | 1   | 1   | 5-2119784-1 | CRIMPER, INSULATION O PREMIUM       | 3   |
|   | - | 1   | 1   | 455888-7    | SPACER, CRIMPER                     | 2   |
| 1 | 1 | 1   | 1   | 8-1633588-1 | CRIMPER, WIRE                       | 1   |


|                                                                                                                                               |  |                                        |  |                                                     |                                     |                                              |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------|--|-----------------------------------------------------|-------------------------------------|----------------------------------------------|--|
| THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION. |  |                                        |  | OWN<br>X. ZHAO<br>CHK<br>L. ZHANG<br>APVD<br>J. GUO | 25FEB2016<br>25FEB2016<br>25FEB2016 | TE Connectivity<br>Harrisburg, PA 17105-3608 |  |
| DIMENSIONS:<br>mm                                                                                                                             |  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |  | PRODUCT SPEC                                        |                                     | NAME<br>Ocean Side Feed Applicator           |  |
| 0 PLC<br>1 PLC<br>2 PLC<br>3 PLC<br>4 PLC                                                                                                     |  | ±<br>±<br>±<br>±<br>±                  |  | APPLICATION SPEC                                    |                                     | SIZE<br>00779                                |  |
| MATERIAL                                                                                                                                      |  | FINISH                                 |  | WEIGHT                                              |                                     | DRAWING NO<br>C=2836229                      |  |
|                                                                                                                                               |  |                                        |  | Customer Accessible Production Drawing              |                                     | RESTRICTED TO                                |  |
|                                                                                                                                               |  |                                        |  | SCALE<br>1:2                                        |                                     | SHEET<br>3 OF 4                              |  |
|                                                                                                                                               |  |                                        |  |                                                     |                                     | REV<br>C                                     |  |

SHEETS 1 & 2 ARE NOT REQUIRED FOR PACIFIC VERSION




| LOC |    | DIST |     | REVISIONS   |      |     |      |
|-----|----|------|-----|-------------|------|-----|------|
| A   | 66 | P    | LTR | DESCRIPTION | DATE | DWN | APVD |
|     |    | -    |     | SEE SHEET 1 | -    | -   | -    |
|     |    |      |     |             |      |     |      |
|     |    |      |     |             |      |     |      |


# FEED TYPE MECHANICAL



## PNEUMATIC






FEED SPRING SETTING POSITION  
(SHOWN FROM REAR SIDE)




DETAIL A


# CAM POSITIONS



TERMINAL SUPPORT LOCATION



RAM SET-UP



FEED TRACK POSITION  
GUIDE BY INSULATION BARREL

PACIFIC VERSION  
Shown on sheets 3 of 4 & 4 of 4  
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

|                                                                                                                                              |  |                                        |                                              |  |
|----------------------------------------------------------------------------------------------------------------------------------------------|--|----------------------------------------|----------------------------------------------|--|
| THIS DRAWING IS UNPUBLISHED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY CHANGES TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST VERSION. |  | DWN<br>X. ZHAO<br>25FEB2016            | TE Connectivity<br>Harrisburg, PA 17105-3608 |  |
| DIMENSIONS:<br>mm                                                                                                                            |  | CHK<br>L. ZHANG<br>25FEB2016           | NAME<br>Ocean Side Feed<br>Applicator        |  |
| TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br>0 PLC ±<br>1 PLC ±<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±<br>FINISH                       |  | APVD<br>J. GUO<br>25FEB2016            | PRODUCT SPEC<br>APPLICATION SPEC             |  |
| MATERIAL                                                                                                                                     |  | SIZE<br>A1                             | CAGE CODE<br>00779                           |  |
|                                                                                                                                              |  | WEIGHT                                 | DRAWING NO<br>2836229                        |  |
|                                                                                                                                              |  | Customer Accessible Production Drawing | RESTRICTED TO                                |  |
|                                                                                                                                              |  | SCALE<br>1:2                           | SHEET<br>4 OF 4                              |  |
|                                                                                                                                              |  |                                        | REV<br>C                                     |  |

SHEETS 1 & 2 ARE NOT REQUIRED FOR PACIFIC VERSION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-2836229-7](#)