



| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
| FT  | 0    | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|     |      |           | A3  | REVISED PER ECO-14-008217 | 02JUN2014 | NK  | MM   |
|     |      |           |     |                           |           |     |      |
|     |      |           |     |                           |           |     |      |
|     |      |           |     |                           |           |     |      |

D





1776138-3 AS SHOWN

- 1 MATERIALS AND FINISH  
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,  
COLOR: BLACK.  
TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE WITHOUT LOSS OF  
CENTERLINE SPACING.
4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF  
UNDERWRITERS LABORATORIES INC., FILE N° E60677.
5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY  
WITH IEC 998-1/998-2-1.
6. UL RATING: 300V, 15A.
- 7 TAPE AND REEL PACKAGING
- 8 PRELIMINARY-NOT FOR PRODUCTION


C

B



|   |   |      |               |                |
|---|---|------|---------------|----------------|
| 8 | 7 | 14.6 | 3             | 1-1776138-4    |
| 8 | 7 | 9.6  | 2             | 1-1776138-3    |
|   |   | 59.6 | 12            | 1-1776138-2    |
|   |   | 54.6 | 11            | 1-1776138-1    |
|   |   | 49.6 | 10            | 1-1776138-0    |
|   |   | 44.6 | 9             | 1776138-9      |
|   |   | 39.6 | 8             | 1776138-8      |
|   |   | 34.6 | 7             | 1776138-7      |
|   |   | 29.6 | 6             | 1776138-6      |
|   |   | 24.6 | 5             | 1776138-5      |
|   |   | 19.6 | 4             | 1776138-4      |
|   |   | 14.6 | 3             | 1776138-3      |
|   |   | 9.6  | 2             | 1776138-2      |
|   |   | A    | NO OF<br>POSN | PART<br>NUMBER |

A



RECOMMENDED PC BOARD LAYOUT

|                                        |  |                                 |                                                                                           |           |               |              |
|----------------------------------------|--|---------------------------------|-------------------------------------------------------------------------------------------|-----------|---------------|--------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. |  | DWN<br>S. WELDON<br>03JUN2005   | <div> TE Connectivity</div>                                                               |           |               |              |
| DIMENSIONS:                            |  | CHK<br>C. RICHARD<br>03JUN2005  |                                                                                           |           |               |              |
| mm                                     |  | APVD<br>C. RICHARD<br>03JUN2005 | NAME<br>TERMINAL BLOCK HEADER ASSEMBLY<br>180 DEGREE, OPEN ENDS, STACKING<br>5.00mm PITCH |           |               |              |
|                                        |  | PRODUCT SPEC<br>108-20166       | SIZE                                                                                      |           | CAGE CODE     |              |
|                                        |  | APPLICATION SPEC<br>114-20079   | DRAWING NO                                                                                |           | RESTRICTED TO |              |
| MATERIAL                               |  | WEIGHT<br>-                     | A200779                                                                                   |           | C-1776138     |              |
|                                        |  | Customer Drawing                |                                                                                           | SCALE 5:1 |               | SHEET 1 OF 1 |
|                                        |  |                                 |                                                                                           |           |               | REV A3       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1776138-2](#)