






LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A2	REVISED PER ECO-12-007711	26APR2012	KH	MS







1. MATERIALS AND FINISH:
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,
COLOR: BLACK.
TERMINAL: COPPER ALLOY, SEE TABLE.
2. SUITABLE FOR 1,6-2, 4mm PC BOARD THICKNESS.
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
5. UL RATING 300V, 15A.
6. TAPE AND REEL PACKAGED.
7. PRELIMINARY PART NUMBER.

6	TIN	16.8	3	2-1776148-3
7	0.76μm AU	26.8	5	1-1776148-3
TIN		61.8	12	1-1776148-2
		56.8	11	1-1776148-1
		51.8	10	1-1776148-0
		46.8	9	1776148-9
		41.8	8	1776148-8
		36.8	7	1776148-7
		31.8	6	1776148-6
		26.8	5	1776148-5
		21.8	4	1776148-4
		16.8	3	1776148-3
		11.8	2	1776148-2
PLATING	DIM L	NO OF POSN	PART NUMBER	



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07JUN2005 CHK S. WELDON C. RICHARD APVD 07JUN2005 C. RICHARD		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL BLOCK HEADER ASSEMBLY, 90 DEGREE, CLOSED ENDS, 5.00mm PITCH	
		0 PLC ± 1 PLC ±0.1 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	
MATERIAL 				SIZE A2	
				CAGE CODE 00779	
				DRAWING NO C=1776148	
				RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 6:1 SHEET 1 OF 1 REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776148-9](#)