

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	W	PRODUCTION ISSUE	18JAN2019	PNT	MT





TABLE OF DIMENSIONS


PART NUMBER	H		P Min b	W $\pm 20\%$ b
	Min a	Max b		
101A011	5.1 [.20]	2.0 [.08]	22.9 [.90]	1.02 [.04]
101A021	7.4 [.29]	3.3 [.13]	25.4 [1.00]	1.27 [.05]
101A031	10.2 [.40]	4.6 [.18]	30.5 [1.20]	1.52 [.06]
101A041	15.2 [.60]	6.4 [.25]	40.6 [1.60]	1.78 [.07]
101A052	20.6 [.81]	9.4 [.37]	61.0 [2.40]	2.03 [.08]
101A062	25.4 [1.00]	11.4 [.45]	68.6 [2.70]	2.29 [.09]
101A073	39.4 [1.55]	18.0 [.71]	91.4 [3.60]	2.54 [.10]
101A083	50.8 [2.00]	22.9 [.90]	101.6 [4.00]	2.79 [.11]
101A094	83.8 [3.30]	38.1 [1.50]	114.3 [4.50]	3.05 [.12]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT - TE Connectivity Ltd.

DIMENSIONS: mm [INCHES]	DWN PRAVEEN N T	18JAN2019	MATERIAL SEE SHEET 2	FINISH -
	CHK N NAGAR	18JAN2019	 TE Connectivity Ltd.	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M TAYLOR	18JAN2019		
	PRODUCT SPEC -		SIZE A4	
	APPLICATION SPEC -		CAGE CODE 00779	DRAWING NO G-101A011-XX-0THRU094-XX-0
	WEIGHT -		RESTRICTED TO -	
0 PLC $\pm -$ 1 PLC ± 0.50 [.10] 2 PLC ± 0.25 [.01] 3 PLC ± 0.13 [.005] 4 PLC $\pm -$ ANGLES $\pm 1^\circ$	CUSTOMER DRAWING		SCALE DNS	SHEET 1 OF 2
		REV W		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATIBILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S1017;S1048;S1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S1017;S1048;S1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A
-25	Elastomer, Fluid Resistant	RW-2070	/42;/86;/225	S1017;S1048;S1206
-100	Polyolefin, Semi-flexible Zerohal	RW-2082	/86;/180	S1048;S1030


ORDERING INFORMATION

Diagram illustrating the breakdown of a part number into its components:

- Base part number: 101A021
- Material dash number (See Compatability Chart): -XX
- Modification number: -XX
- Adhesive slash number (If necessary, see Compatability Chart): /XX
- Color designator: -0

NOTES

1. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Recovered parts may have angularity of 30° - 45°.

DIMENSIONS: mm [INCHES]		DWN PRAVEEN N T 18JAN2019	MATERIAL —		FINISH —	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0,50 [.10] 2 PLC ± 0,25 [.01] 3 PLC ± 0,13 [.005] 4 PLC ± — ANGLES ± 1°		CHK N NAGAR 18JAN2019	 TE Connectivity Ltd.			
		APVD M TAYLOR 18JAN2019				
		PRODUCT SPEC —	NAME CAP, ROUND END —			
		APPLICATION SPEC —				
		WEIGHT	SIZE A4	CAGE CODE 00779	DRAWING NO C- 101A011-XX-0THRU094-XX-0	RESTRICTED TO —
		CUSTOMER DRAWING				SCALE DNS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[101A011-25/86-0](#)