





Technical drawing of a cross-section of a multi-ported pipe. The drawing shows a central pipe with multiple internal ports. Key dimensions include a total width of 4.2, a central port width of 3.45, a port depth of 5 ± 0.1 TYP, and a total length of 12. B. A detail callout '1' points to a specific feature on the right side of the pipe.

REMARKS/Bemerkungen

CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN
PROD.SPEC. 108-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in
Prod. Spec. 108-18049, Punkt 3.3.2

CONTACT CAVITY NO.
Kontaktkammernummerierung

MATING STOP
Tiefenanschlag

AREA FOR TE LOGO ACC. TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36

POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"

KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"

KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten

LOCKING LATCH
Rasthaken

TE PART NO (PN)
TE Bestell Nr. (PN)

DESIGN OF THE HOUSINGS ACC. TO RAST 5 STANDARD
Gehäuseausführung gemäss RAST 5 Vorgabe

GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwannen siehe RAST 5 Vorgabe

PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS. 2500 PIECES PER BOX / 3 POS. 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol. 2500 Stück per Karton / 3pol. 2000 Stück per Karton

DIMENSION A, B C AND D SEE SHEET 2 OF 3

MATERIAL CORRESPONDS TO THE REQUIREMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Glühdrahttest 750° ohne Flamme)


RATIO NUMBER OF THE KEYING VERSION, INKJET PRINTED. SEE SHEET 2
Kodierungskennnummer, mit Tintenstrahldrucker aufgebracht, siehe Blatt 2

PRELIMINARY - NOT RELEASED FOR PRODUCTION

ONLY FOR 9-1241961-7, DIMENSION 3.2 -0.2

DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL

ALLOWED 25±0.2 FOR P/NS X-2364739-X.



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRW Kishor M 18-10-07	 TE Connectivity			
DIMENSIONS:		CNR K.Munz 18-10-07				
mm		APPRO Th. Klenner 18-10-07				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-1804-1	NAME STANDARD TIMER HSG. RAST 5 MARK II			
0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±°		APPLICATION SPEC	Standard Timer Gehäuse RAST 5 Mark II			
FINISH		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4		-	A1	00779	C=1241961	-
		Customer Drawing	SCALE	5:1	SHEET	1 of 4
						REV F4

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

SPECIAL VERSION: UL94 V0 & GWEPT 750°C NF								
2364739-5	5	4	0.5	25	20	PA66 13 17	BLUE	C
2364739-4	4			20	15		BLUE	C
1-2364739-3	3			15	10		BLUE	C
2364739-3				15	10		BLUE	C
1-2364739-2				10	5		BLUE	C
2364739-2	2			10	5		BLUE	C
3-2364739-2		2		10	5		BLUE	C
2-2364739-2				10	5		BLUE	C

SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350								
5-1241961-7	3	6	1	15	10	PA66 13	NATURAL	A
1-1241961-9	3			15	10		NATURAL	A
7-1241961-7	3			15	10		NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
15 2322164-1	4	4	0.5	20	15	PA66 13	NATURAL	1

SPECIAL VERSION: UL94 V2 & GWT 750 NF								
6-2178575-7	3	4	0.5	15	10	PA6 GF15 13	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
15 3-2178412-7	3	6	1	15	10	PA66 13 UL94 V0 & GWT 750 NF	NATURAL	1
15 4-2178412-7	3			15	10		NATURAL	1
15 8-2178412-2	2			10	5		NATURAL	1

UL94 V0 & GWT 750 NF									
15 15	2322917-4	4	4	0.5	20	15	PA66 UL94 V0 & GWT 750 NF	NATURAL	C
	2322917-2	2			10	5		NATURAL	C
	2315717-1	2			10	5		NATURAL	C
	2315717-2	2			10	5		NATURAL	C
	2315717-3	2			10	5		NATURAL	C
	1-2315717-2	2			10	5		NATURAL	1
	2-2315717-2	2			10	5		NATURAL	1
	2315717-4	4			20	15		NATURAL	C
	2315717-5	4			20	15		NATURAL	C
	2315717-6	3			15	10		NATURAL	C
	2315717-7	3			15	10		NATURAL	C
	1-2315717-3	3			15	10		NATURAL	E
	PART NO.				POS	DIM C 12		DIM D 12	DIMA 12

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

2 POSITION VARIANTS

2.00

0-969484-1

2.14

1-969484-1
2315717-2

2.13

2-969484-1

2.12

3-969484-1 OBSOLETE

2.11

4-969484-1

2.10

5-969484-1 OBSOLETE

2.09

6-969484-1

2.07

7-969484-1 OBSOLETE
3-2364739-2

2.06

8-969484-1

2.04

9-969484-1 OBSOLETE

2.03

0-969484-2

2.02

1-969484-2 OBSOLETE

2.08

2-969484-2

2.21

3-969484-2

2.99

4-969484-2
2315717-1

2.20

5-969484-2
2-2364739-2
PA6

2.19

6-969484-2
PA6

2.18

7-969484-2
PA6

2.17

8-969484-2
2315717-3
PA6

2.16

9-969484-2
PA6

2.31

0-969484-3

2.15

1-969484-3 OBSOLETE

2.05

2-969484-3 OBSOLETE

2.30

3-969484-3 OBSOLETE

Ohne/None

4-969484-3

Ohne/None

5-969484-3

Ohne/None

6-969484-3

Ohne/None

7-969484-3 OBSOLETE

5-1241961-2

0-1241961-1

2-1241961-2

3-1241961-2

6-1241961-2
2364739-2

7-1241961-2
2-2315717-2

8-1241961-2
8-2178412-2

9-1241961-2

0-1241961-3
1-2315717-2

3-1241961-3 OBSOLETE

4-1241961-3

5-1241961-3

6-1241961-3

7-1241961-3
1-2364739-2
2178571-2

6-1241983-2

8-1241983-2

5-1241983-3

0-1241983-2

1-1241983-2

2-1241983-2

3-1241961-1

8-1241961-3
2322917-2

4-1955422-3

9-1955506-2

0-1955422-1

PRELIMINARY

3 POSITION VARIANTS

3.00

0-969484-6 OBSOLETE

3.38

1-969484-6 OBSOLETE

3.18

2-969484-6

3.37

3-969484-6

3.35

4-969484-6 OBSOLETE

3.33

5-969484-6 OBSOLETE

3.32

6-969484-6 OBSOLETE

3.20

7-969484-6

3.10

8-969484-6

3.09

9-969484-6

3.08

0-969484-7 OBSOLETE

3.39

1-969484-7
1-1955422-7 PRELIMINARY

3.31

2-969484-7 OBSOLETE

3.40

3-969484-7

3.99

4-969484-7 OBSOLETE

Ohne/NONE

5-969484-7

3.45

6-969484-7 OBSOLETE

3.47

7-969484-7 OBSOLETE

3.65

8-969484-7

3.48

9-969484-7 OBSOLETE

3.66

0-969484-8

Ohne/NONE

1-969484-8 OBSOLETE

Ohne/NONE

2-969484-8

9-1241961-9

3-1241961-8

9-969484-9

4-1241961-8

5-1241961-8

PA6

03-K

PA6

03-F

03-I

5-1955422-7

6-1241961-7
1-1241961-9
0-1955422-6
6-2178575-7
2345753-1

9-1241961-7

0-2315717-6

0-2315717-7

0-1241961-6

2-1241961-7
5-1241961-7
2364739-3
2178571-1

1-1241961-8

2-1241961-8
1-2364739-3

6-1241961-8
7-1241961-7

7-1241961-8

1-1241961-7

9-1241961-8

8-1241961-8
1-2315717-3

2-1241817-3

0-1241961-8

3-1241961-7
3-2178412-7
3-2178413-7

4-1241961-7
4-2178412-7
4-2178413-7

5-1955422-7

6-1241961-7
1-1241961-9
0-1955422-6
6-2178575-7
2345753-1

9-1241961-7

0-2315717-6

0-2315717-7

4 POSITION VARIANTS

4-1241959-4

0-1241959-4
0-1241817-4
2364739-4
2178571-3

2-1241959-4

4-1241959-4

2315717-4

0-1955507-4
PRELIMINARY

0-2315717-5

2-1241817-4

3-1241817-4 OBSOLETE
2322164-1
2322917-4

0-1241959-5

2364739-5

0-1241817-5

2-1241817-5

5 POSITION VARIANTS

5-1241817-3

1-2178571-3

5-1241817-3

5-1241817-3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±0.2
4 PLC ±0.2
ANGLES ±°

MATERIAL
SEE TABLES, SHEETS
PAGE 2 AND 3 OF 4

WEIGHT
-

Customer Drawing

OWN
Kishor M
18-10-07

CHK
K. Muniz
18-10-07

APPROV
T. Klender
18-10-07

PRODUCT SPEC
108-18049

APPLICATION SPEC
-

NAME
STANDARD TIMER HSG. RAST 5 MARK II
Standard Timer Gehäuse RAST 5 Mark II

SIZE
A1

CAGE CODE
00779

DRAWING NO
1241961

RESTRICTED TO
-

SCALE
5:1

SHEET
4

OF
4

REV
E

4

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1241961-8](#)