






Technical drawing of a cross-section of a multi-ribbed structural member. The drawing shows a series of vertical ribs separated by grooves. Dimensions include a top width of 4.2, a top groove width of 3.45, a bottom groove width of 5 ± 0.1 TYP, and a total bottom width of 12 ± 0.1 B. A feature '1' is indicated on the right side of the member.

REMARKS/Bemerkungen

- 1 CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN
PROD.SPEC. 108-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in
Prod. Spec. 108-18049, Punkt 3.3.2
- 2 CONTACT CAVITY NO.
Kontaktkammernummerierung
- 3 MATING STOP
Tiefenanschlag
- 4 AREA FOR TE LOGO ACC. TO SPEC. 202-36
Bereich für TE Logo nach Spec. 202-36
- 5 POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"
- 6 KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"
- 6a KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten
- 7 LOCKING LATCH
Rasthaken
- 8 TE PART NO (PN)
TE Bestell Nr. (PN)
- 9 DESIGN OF THE HOUSINGS ACC. TO RAST 5 STANDARD
Gehäuseausführung gemäss RAST 5 Vorgabe
- 10 GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwanne siehe RAST 5 Vorgabe
- 11 PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS. 2500 PIECES PER BOX / 3 POS. 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol. 2500 Stück per Karton / 3pol. 2000 Stück per Karton
- 12 DIMENSION A, B C AND D SEE SHEET 2 OF 3
- 13 MATERIAL CORRESPONDS TO THE REQUIREMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Gl ühdrahttest 750° ohne Flamme)
- 14 RATIO NUMBER OF THE KEYING VERSION, INKJET PRINTED. SEE SHEET 2
Kodierungsskennnummer, mit Tintenstrahldrucker aufgebracht, siehe Blatt 2
- 15 PRELIMINARY- NOT RELEASED FOR PRODUCTION
- 16 ONLY FOR 9-1241961-7, DIMENSION 3.2 -0.2
- 17 DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL
- 18 ALLOWED 25±0.2 FOR P/NS X-2364739-X.



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG Kishor M 18-10-07 CHK K. Munz 18-10-07 APP'D Th. Klenner 18-10-07	 TE Connectivity	
DIMENSIONS: mm 		NAME STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±°		PRODUCT SPEC 108-1804-9.1 APPLICATION SPEC		
MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4		SIZE A1		WEIGHT -
FINISH -		CASE CODE 00779		DRAWING NO C=1241961
		SCALE 5:1		SHEET 1 OF 4
		REV F4		RESTRICTED TO -

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

SPECIAL VERSION: UL94 V0 & GWEPT 750°C NF								
2364739-5	5	4	0.5	25	20	PA66 13 17	BLUE	C
2364739-4	4			20	15		BLUE	C
1-2364739-3	3			15	10		BLUE	C
2364739-3				15	10		BLUE	C
1-2364739-2				10	5		BLUE	C
2364739-2	2			10	5		BLUE	C
3-2364739-2		2		10	5		BLUE	C
2-2364739-2				10	5		BLUE	C

SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350								
5-1241961-7	3	6	1	15	10	PA66 13	NATURAL	A
1-1241961-9	3			15	10		NATURAL	A
7-1241961-7	3			15	10		NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
15 2322164-1	4	4	0.5	20	15	PA66 13	NATURAL	1

SPECIAL VERSION: UL94 V2 & GWT 750 NF								
6-2178575-7	3	4	0.5	15	10	PA6 GF15 13	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF								
15 3-2178412-7	3	6	1	15	10	PA66 13 UL94 V0 & GWT 750 NF	NATURAL	1
15 4-2178412-7	3			15	10		NATURAL	1
15 8-2178412-2	2			10	5		NATURAL	1

UL94 V0 & GWT 750 NF													
151515	2322917-4	4	4	0.5	20	15	PA66 UL94 V0 & GWT 750 NF	NATURAL	C				
	2322917-2	2			10	5		NATURAL	C				
	2315717-1	2			10	5		NATURAL	C				
	2315717-2	2			10	5		NATURAL	C				
	2315717-3	2			10	5		NATURAL	C				
	1-2315717-2	2			10	5		NATURAL	1				
	2-2315717-2	2			10	5		NATURAL	1				
	2315717-4	4			20	15		NATURAL	C				
	2315717-5	4			20	15		NATURAL	C				
	2315717-6	3			15	10		NATURAL	C				
	2315717-7	3			15	10		NATURAL	C				
	1-2315717-3	3			15	10		NATURAL	E				
	PART NO.				POS	DIM C 12		DIM D 12	DIMA 12	DIM B 12	MATERIAL	COLOUR	REV.

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

2 POSITION VARIANTS

2.00

0-969484-1

2.14

1-969484-1
2315717-2

2.13

2-969484-1

2.12

3-969484-1 OBSOLETE

2.11

4-969484-1

2.10

5-969484-1 OBSOLETE

2.09

6-969484-1

2.07

7-969484-1 OBSOLETE
3-2364739-2

2.06

8-969484-1

2.04

9-969484-1 OBSOLETE

2.03

0-969484-2

2.02

1-969484-2 OBSOLETE

2.08

2-969484-2

2.21

3-969484-2

2.99

4-969484-2
2315717-1

2.20

5-969484-2
2-2364739-2
PA6

2.19

6-969484-2
PA6

2.18

7-969484-2

2.17

8-969484-2
2315717-3
PA6

2.16

9-969484-2

2.31

0-969484-3

2.15

1-969484-3 OBSOLETE

2.05

2-969484-3 OBSOLETE

2.30

3-969484-3 OBSOLETE

Ohne/NONE

4-969484-3

Ohne/NONE

5-969484-3

Ohne/NONE

6-969484-3

Ohne/NONE

7-969484-3 OBSOLETE

Ohne/NONE

5-1241961-2

Ohne/NONE

0-1241961-1

2-1241961-2

3-1241961-2

6-1241961-2
2364739-2

7-1241961-2
2-2315717-2

8-1241961-2

9-1241961-2

0-1241961-3

3-1241961-3 OBSOLETE

4-1241961-3

5-1241961-3

6-1241961-3

7-1241961-3
1-2364739-2
2178571-2

6-1241983-2

8-1241983-2

5-1241983-3

0-1241983-2

1-1241983-2

2-1241983-2

3-1241961-1

8-1241961-3
2322917-2

4-1955422-3

9-1955506-2

0-1955422-1

PRELIMINARY

3 POSITION VARIANTS

3.00

0-969484-6 OBSOLETE

3.38

1-969484-6 OBSOLETE

3.18

2-969484-6

3.37

3-969484-6

3.35

4-969484-6 OBSOLETE

3.33

5-969484-6 OBSOLETE

3.32

6-969484-6 OBSOLETE

3.20

7-969484-6

3.10

8-969484-6

3.09

9-969484-6

3.08

0-969484-7 OBSOLETE

3.39

1-969484-7
1-1955422-7 PRELIMINARY

3.31

2-969484-7 OBSOLETE

3.40

3-969484-7

3.99

4-969484-7 OBSOLETE

Ohne/NONE

5-969484-7

3.45

6-969484-7 OBSOLETE

3.47

7-969484-7 OBSOLETE

3.65

8-969484-7

3.48

9-969484-7 OBSOLETE

3.66

0-969484-8

Ohne/NONE

1-969484-8 OBSOLETE

Ohne/NONE

2-969484-8

3-1241961-9

3-1241961-8

9-969484-9

4-1241961-8

5-1241961-8

PA6

PA6

PA6

PA6

6-1241961-8

7-1241961-8

1-1241961-8

9-1241961-8

8-1241961-8

1-2315717-3

2-1241817-3

0-1241961-8

3-1241961-7

4-1241961-7

5-1955422-7

6-1241961-7
1-1241961-9
0-1955422-6
6-2178575-7
2345753-1

9-1241961-7

0-2315717-6

0-2315717-7

4 POSITION VARIANTS

0-1241959-4

0-1241817-4
2364739-4
2178571-3

2-1241959-4

4-1241959-4

2315717-4

0-1955507-4
PRELIMINARY

0-2315717-5

2-1241817-4

3-1241817-4 OBSOLETE
2322164-1
2322917-4

0-1241959-5

2364739-5

0-1241817-5

2-1241817-5

5 POSITION VARIANTS

1-2178571-3

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN Kishor M 18-10-07

CHK K. Muniz 18-10-07

APVD T. Klender 18-10-07

PRODUCT SPEC 108-18049

APPLICATION SPEC

WEIGHT

Customer Drawing

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES FINISH

MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4

NAME STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II

SIZE A1

CAGE CODE 00779

DRAWING NO. 1241961

RESTRICTED TO

SCALE 5:1

SHEET 4 OF 4

REV E4

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1241961-8](#)