

LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION		DATE	DWN	APVD
A1	-		E2	ECR-21-100675		23FEB2021	KD	FL
			E3	ECR-21-102870		20MAY2021	SM	FL
			E4	ECR-21-103933		14JUN2021	PJ	FL
			E5	ECR-21-115768		06DEC 12021	KD	FL

REMARKS/Bemerkungen

- 1

CAVITY SUITABLE FOR STANDARD TIMER CONTACTS LISTED IN PROD.SPEC. 108-18049, ITEM 3.3.2
Kammer geeignet für Standard Timer Kontakte gelistet in Prod. Spec. 108-18049, Punkt 3.3.2
- 2

CONTACT CAVITY NO.
Kontaktkammernummerierung
- 3

MATING STOP
Tiefenanschlag
- 4

AREA FOR TE LOGO ACC. TO SPEC 202-36
Bereich für TE Logo nach Spec. 202-36
- 5

POLARIZATION RIB POSITION "a" AND/OR "b"
Polarisierungsrippe Position "a" und/oder "b"
- 6

KEYING RIB POSITION "c" AND/OR "d"
Kodierrippe Position "c" und/oder "d"
- 6a

KEYING RIB POSITION "c" AND/OR "d" AT THE END WALLS OF THE HOUSING
Kodierrippe Position "c" und/oder "d" an den Gehäusestirnseiten
- 7

LOCKING LATCH
Rasthaken
- 8

TE PART NO (PN)
TE Bestell Nr. (PN)
- 9

DESIGN OF THE HOUSINGS ACC. TO RAST 5 STANDARD
Gehäuseausführung gemäss RAST 5 Vorgabe
- 10

GENERAL SUITABLE TAB HEADER SEE RAST 5 PERFORMANCE
Generell passende Flachsteckerwannen siehe RAST 5 Vorgabe
- 11

PACKAGING: BULK PACKAGING IN CORRUGATED BOX PN 740580-2
2 POS. 2500 PIECES PER BOX / 3 POS. 2000 PIECES PER BOX
Verpackung: Schüttgut in Versandkarton Pn 740580-2
2pol. 2500 Stück per Karton / 3pol. 2000 Stück per Karton
- 12

DIMENSION A, B C AND D SEE SHEET 2 OF 3
- 13

MATERIAL CORRESPONDS TO THE REQUIRMENT EN 60335
(INCL. GLOW WIRE TEST 750° WITHOUT FLAME)
Material entspricht den Anforderungen der EN 60335
(inkl. Glühdrahttest 750° ohne Flamme)
- 14





RATIO NUMBER OF THE KEYING VERSION,INKJET PRINTED. SEE SHEET 2
Kodierungskennnummer, mit Tintenstrahldrucker aufgebracht , siehe Blatt 2
- 15

PRELIMINARY- NOT RELEASED FOR PRODUCTION
- 16


ONLY FOR 9-1241961-7, DIMENSION 3.2 -0.2
- 17

DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL
- 18

ALLOWED 25±0.2 FOR P/Ns X-2364739-X.




SECTION A-A / Schnitt A-A




SECTION B-B / Schnitt B-B

5 POSITION
STD. TIMER MARK-II HOUSING



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Kishor M	18-10-07	 TE Connectivity		
DIMENSIONS:		CHK K.Munz	18-10-07			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Th. Klenner	18-10-07	NAME		
		PRODUCT SPEC		STANDARD TIMER HSG. RAST 5 MARK II		
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±° FINISH	APPLICATION SPEC		Standard Timer Gehäuse RAST 5 Mark II		
		SIZE		RESTRICTED TO		
MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4		WEIGHT		A 1 00779 ©= 1241961		
Customer Drawing		SCALE 5:1		SHEET 1 of 4 REV E5		

This architectural drawing shows a symmetrical building facade. The central feature is a large entrance with a prominent pediment supported by columns. On either side of the entrance are large, multi-paned windows. The roofline is flat with several small, square ventilation units or skylights. The drawing uses simple lines to represent the building's structure and components.

SPECIAL MATERIAL: UL94 V0								
2345753-1	3	6	1	15	10	PA66	NATURAL	C

SPECIAL MATERIAL									
15	1955507-4	4	6	1	20	15	PA66 UL 94 V0	NATURAL	1
15	9-1955506-2	2			10	5		NATURAL	1

	6-124 1961-7	3	4	0.5	15	10	PA 6 UL94V-2	NATURAL 	1
	4-124 1961-7	3			15	10	PA 6 UL94V-2	NATURAL 	A
	3-124 1961-7	3			15	10	PA 6 UL94V-2	NATURAL 	A
	1-19554 22-7	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
	5-19554 22-7	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
	4-19554 22-3	2			6	1	10	5	PA 66 UNFILLED UL94 V0
	2-124 1817-3	3	4 or 6	0.5 or 1	15	10	PA 66 UL94 V-2	Green	E
	0-19554 22-6	3	4	0.5	15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
	8-124 1961-8	3			15	10	PA 6 UL94V-2	natural 	C
	0-124 1961-8	3			15	10			A
	8-124 1961-3	2			10	5			C
	3-124 1961-1	2			10	5	PA 6 UL94V-2	NATURAL 	C
	0-19554 22-1	2			10	5	PA 66 UNFILLED UL94 V0	NATURAL	A
	PART NO	POS			DIM C	DIM D	DIM A	DIM B	MATERIAL
									

SPECIAL VERSION: UL94 V0 & GW T 750NF								
15	2178571-3	4	4	1	20	15	PA 66, UL94 V-0	NATURAL
	2178571-1	3			15	10	PA 66, UL94 V-0	NATURAL
15	2178571-2	2			10	5	PA 66, UL94 V-0	NATURAL
	1-2178571-3	3			15	10	PA 66, UL94 V-0	NATURAL
	PART NO	POS	DIM C	DIM D	DIM A	DIM B	MATERIAL	COLOUR Farbe
								

SSE SHEET-01												
	0-1241959-5	5	4	0.5	25	20	PA 6 UL94V-2	Natural/natur	B			
	4-1241959-4	4			20	15			A			
	2-1241959-4				20	15						
	0-1241959-4				20	15			B			
OBSOLETE	2-1241817-5	5	4	0.5	25	20	PA 6.6 UL94V-2	Natural/natur Black/schwarz Violet/violett Grey/grau Natural/natur	C			
	0-1241817-5				25	20						
	3-1241817-4				20	15						
	2-1241817-4				20	15						
	0-1241817-4				20	15						
	2-1241983-2	2	4	0.5	10	5	PA 6 UL94V-2	Green/grün Violet/violett TARGET RAL 4001 Yellow/gelb Black/schwarz Blue/blau Red/rot	C			
	1-1241983-2				10	5						
	0-1241983-2				10	5						
	8-1241983-2				10	5						
	5-1241983-3				10	5						
6-1241983-2		10	5									
OBSOLETE	0-1241961-7	3	4	0.5	15	10	PA 6 UL94V-2	Natural/natur	C			
	9-1241961-8				15	10						
	6-1241961-8				15	10						
	5-1241961-8				4 or 6	0.5 or 1				15	10	
	4-1241961-8					15				10		
	7-1241961-8				4	0.5				15	10	
	1-1241961-8				4 or 6	0.5 or 1				15	10	
	3-1241961-8				6	1				15	10	
	2-1241961-8					15				10		
	2-1241961-7				4	0.5				15	10	
	9-1241961-9									15	10	
	0-1241961-6									15	10	
	3-1241961-3									10	5	
	2-1241961-2									10	5	
	5-1241961-2									10	5	
	4-1241961-3									10	5	
	7-1241961-2									10	5	
	7-1241961-3									10	5	
	6-1241961-3									10	5	
	3-1241961-2									10	5	
5-1241961-3	10	5										
6-1241961-2	10	5										
0-1241961-3	10	5										
8-1241961-2	10	5										
9-1241961-2	10	5										
0-1241961-1	10	5										
OBSOLETE	9-969484-9	3	6	1			15	10	PA 6.6 UL94V-2	Yellow/gelb	H	
	2-969484-8						15	10				
	4-969484-8						15	10				
	0-969484-8				4 or 6	0.5 or 1	15	10				
	9-969484-7				4	0.5	15	10				
	8-969484-7					15	10					
	7-969484-7					15	10					
	6-969484-7					15	10					
	5-969484-7				4	0.5	15	10				
	4-969484-7					15	10					
	3-969484-7				4	0.5	15	10				
	2-969484-7					15	10					
	1-969484-7				3	4	0.5	15				10
	0-969484-7					15	10					
	9-969484-6				6	1	15	10				
	8-969484-6						15	10				
	7-969484-6						15	10				
	6-969484-6						15	10				
	5-969484-6						15	10				
	4-969484-6						15	10				
3-969484-6	4	0.5	15	10								
2-969484-6			15	10								
1-969484-6			15	10								
0-969484-6			15	10								
7-969484-3				10			5					
6-969484-3				10			5					
5-969484-3				10			5					
4-969484-3				10			5					
3-969484-3				10			5					
2-969484-3				10			5					
1-969484-3				10			5					
0-969484-3				10			5					
9-969484-2				10			5					
8-969484-2				10			5					
7-969484-2			4	0.5	10	5						
6-969484-2					10	5						
5-969484-2					10	5						
4-969484-2					10	5						
3-969484-2					10	5						
2-969484-2					10	5						
1-969484-2	10	5										
0-969484-2	10	5										
6-969484-1	6	1			10	5						
5-969484-1					10	5						
4-969484-1					10	5						
3-969484-1					10	5						
2-969484-1					10	5						
1-969484-1					10	5						
0-969484-1					10	5						
9-969484-1					4	0.5	10	5				
8-969484-1							10	5				
7-969484-1							10	5				
6-969484-1							10	5				
5-969484-1							10	5				
4-969484-1			10	5								
3-969484-1			10	5								
2-969484-1			10	5								
1-969484-1			10	5								
0-969484-1			10	5								

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

SPECIAL VERSION: UL94 V0 & GWEPT 750°C NF								
2364739-5	5	4	0.5	25	20	PA66 1317	BLUE	C
2364739-4	4			20	15		BLUE	C
1-2364739-3	3			15	10		BLUE	C
2364739-3				15	10		BLUE	C
1-2364739-2		2		10	5		BLUE	C
2364739-2				10	5		BLUE	C
3-2364739-2		2		10	5		BLUE	C
2-2364739-2				10	5		BLUE	C

SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350								
5-1241961-7	3	6	1	15	10	PA6613	NATURAL	A
1-1241961-9	3			15	10		NATURAL	A
7-1241961-7	3			15	10		NATURAL	A


SPECIAL VERSION: UL94 V0 & GWT 750 NF								
152322164-1	4	4	0.5	20	15	PA6613	NATURAL	1

SPECIAL VERSION: UL94 V2 & GWT 750 NF								
6-2178575-7	3	4	0.5	15	10	PA6 GF1513	NATURAL	A


SPECIAL VERSION: UL94 V0 & GWT 750 NF								
153-2178412-7	3	6	1	15	10	PA66 UL94 V0 & GWT 750 NF13	NATURAL	1
154-2178412-7	3			15	10		NATURAL	1
158-2178412-2	2			10	5		NATURAL	1

UL94 V0 & GWT 750 NF								
2322917-4	4	4	0.5	20	15	PA66 UL94 V0 & GWT 750 NF13	NATURAL	C
2322917-2	2			10	5		NATURAL	C
2315717-1	2			10	5		NATURAL	C
2315717-2	2			10	5		NATURAL	C
2315717-3	2	4	0.5	10	5		NATURAL	C
1-2315717-2	2			10	5		NATURAL	E
2-2315717-2	2			10	5		NATURAL	E
2315717-4	4			20	15		NATURAL	C
2315717-5	4			20	15		NATURAL	C
2315717-6	3			15	10		NATURAL	C
2315717-7	3			15	10		NATURAL	C
1-2315717-3	3			15	10		NATURAL	E
PART NO.	POS	DIM C 12	DIM D 12	DIMA 12	DIM B 12	MATERIAL	COLOUR	REV.


2 POSITION VARIANTS





3 POSITION VARIANTS



4 POSITION VARIANTS



5 POSITION VARIANTS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Kishor M	18-10-07	 TE Connectivity	NAME	STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II
		CHK K.Munz	18-10-07			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:				
DIMENSIONS: mm		APVD Th. Klenner	18-10-07			
		0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± ANGLES ±°				
MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4		FINISH - 				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1241959-4](#)