

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16		D	ECR-14-011707	13AUG2014	HZ	RZ


- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.2dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310nm. (SEE TABLE)
- 2

MINIMUM RETURN LOSS: 55dB (1310nm)
- 3

TEST DATA PROVIDED WITH EACH ASSEMBLY.
- 4

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.



A

B

B

A

FIBER PATH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.W.DAVIS	01NOV05	TE Connectivity	
		CHK J.DUNCAN	01NOV05		
DIMENSIONS: METERS [INCHES]		APVD F.McCORKEL	01NOV05	NAME CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE, 2 FIBER BREAKOUT, SEALED LC DUPLEX (ODVA), BOTH ENDS	
		PRODUCT SPEC		SIZE A2	CAGE CODE 00779
		APPLICATION SPEC		DRAWING NO C-1828936	RESTRICTED TO
MATERIAL		WEIGHT		SCALE NTS	
FINISH		CUSTOMER DRAWING		SHEET 1 of 2	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1828936-7](#)