

D

C

B

A

D





C

B

A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		C	REVISED	22JUL2009	DH	JE
			C1	REVISED PER ECO-10-001873	18FEB2010	DH	JE
			D	REVISED PER ECO-11-009841	5-12-11	BM	WA



- NOTES:
- UNLESS OTHERWISE SPECIFIED
- 1 MATERIAL: 6063 ALUMINUM.
 - 2 FINISH: ELECTROLESS NICKEL 0.76-2.54 MICROMETERS THICK. RoHS COMPLIANT.
 - 3 0.2mm MAX BURR.
 - 4 VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
 - 5 MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
 - 6 RoHS COMPLIANT AND CERTIFIED.

2	1829904-3
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	E.TAO	6-26-06	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		CHK	-	-	HEAT SINK SFP DWDM 6.5mm TALL	
mm		APVD	-	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	-	-		
0 PLC ±.2		APPLICATION SPEC	-	-		
1 PLC ±.10		WEIGHT	-	-	SIZE	CAGE CODE
2 PLC ±.08		CUSTOMER DRAWING		A200779	DRAWING NO	RESTRICTED TO
3 PLC ±.08					1829904	-
4 PLC ±0.0001						
ANGLES ±5						
FINISH						
1						
2						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1829904-2](#)