

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		C	REVISED	22JUL2009	DH	JE
			C1	REVISED PER ECO-10-001873	19FEB2010	DH	JE
			C2	REVISED PER ECO-10-014519	21MAY2010	MB	MB

D

D

C


C

B


B

A

A



- NOTES:
- UNLESS OTHERWISE SPECIFIED
- 1 MATERIAL: 6063 ALUMIMUM.
 - 2 FINISH: ELECTROLESS NICKEL 0.76-2.54 MICROMETERS THICK. RoHS COMPLIANT.
 - 3. 0,2mm MAX BURR.
 - 4. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
 - 5 MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
 - 6. RoHS COMPLIANT AND CERTIFIED.
 - 7 FINISH: HARD ANODIC COATING PER MIL-A-8625 TYPE III, 40.64 MICROMETERS MINIMUM THICK.



7	1829905-4
2	1829905-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN E.TAO 6-26-06	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK V.KHEIL 7-13-06	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm .2$ 1 PLC $\pm .10$ 2 PLC $\pm .08$ 3 PLC ± 0.0001 4 PLC $\pm .5$ ANGLES ± 5 FINISH		APVD -	PRODUCT SPEC -	
MATERIAL 1		APPLICATION SPEC -	SCALE 4:1	
2		WEIGHT -	SHEET 1	
		CUSTOMER DRAWING	REV C2	
		SIZE A2	CAGE CODE 00779	RESTRICTED TO -
		DRAWING NO C-1829905		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1829905-2](#)