





A 4x4 grid with numbers 1-6 and various symbols. The grid is as follows:


b	-	4	-	d
a	-	4	-	c
b	-	3	-	d
a	-	3	-	c
b	-	2	-	d
a	-	2	-	c
b	-	1	-	d
a	-	1	-	c

Additional symbols and connections:

- Triangle 9 is connected to the top-right corner of the grid.
- Triangle 6 is connected to the top-right corner of the grid.
- Triangle 2 is connected to the top-right corner of the grid.
- Triangle 3 is connected to the bottom-left corner of the grid.
- Triangle 4 is connected to the bottom-right corner of the grid.
- A shaded square is located at the top-right corner of the grid.
- A square with an 'X' is located at the top-right corner of the grid.




PAY ATTENTION !
DIFFERENT LOCKING LATCHES



4805 (3/11)

SPECIAL VERSIONS
SEE SHEET 3 OF 3



SW AGED KEYING RIB
Abgeschr ägte Kodierrippe

		7-1241965-2	2	02-M	10	5	NATURE/natur	UL94 V-0	B	
		0-1241980-8	8	-	40	35	NATURE/natur	UL94 V-0	-	
		5-964702-3	9	-	45	40	NATURE/natur	UL94 V-2	C	
		0-964702-3		-			NATURE/natur			
		0-964702-2		-			BLACK/schwarz			
		280-964702-1		-			NATURE/natur			
	3-1241817-4	0-964983-6	6	06-A	30	25	WHITE/weiß	UL94 V-2	B	
		3-964983-4	4	04-G	20	15	GREY/grau			
		2-964983-4	4	04-F	20	15	ORANGE/orange			
	2-1241817-3	2-964983-3	3	03-K	15	10	GREEN/grün			
		283-964983-2	2	02-M	10	5	VIOLET/violett (lila)	UL94 V-2	B	
		2-964983-2	2	02-G	10	5	BLUE/blau			
	3-969484-2	0-964983-2	2	02-D	10	5	BLACK/schwarz			
		1-1241965-1	11	11-B	55	50	NATURE/natur			
		280-1241965-9	9	09-D	45	40	NATURE/natur	UL94 V-2	B	
		0-1241965-8	8	08-D	40	35	NATURE/natur			
		1-1241965-7	7		35	30	NATURE/natur			
		0-1241965-7	7		35	30	NATURE/natur			
		2-1241965-6	6	06-D	30	25	NATURE/natur			
		2-1241965-5	5	05-B	25	20	NATURE/natur			
		0-1241965-5	5		25	20	NATURE/natur			
		6-1241965-4	4		20	15	NATURAL			
		0-1241965-4	4	04-C	20	15	NATURE/natur			
		9-1241965-2	2		10	5	NATURE/natur			
		5-1241965-2	2	02-B	10	5	BLACK/schwarz			
		4-1241965-2	2	02-I	10	5	RED/rot			
		3-1241965-2	2	02-G	10	5	BLUE/blau			
		0-1241965-2	2	02-A	10	5	NATURE/natur			
		1-928247-1	11	11-B	55	50	YELLOW/gelb			
		282-928247-0	10	-	50	45	GREY/grau			
		281-928247-0	10	-	50	45	BROWN/braun			
		2-928247-9	9	09-D	45	40	BLUE/blau	UL94 V-2	B	964703-3
		0-928247-8	8	08-D	40	35	BLUE/blau			
		6-928247-7	7	-	35	30	GREEN/grün			
		4-928247-7	7	-	35	30	NATURE/natur			
		3-928247-7	7	-	35	30	NATURE/natur	UL94 V-0	A	
		0-928247-7	7	07-C	35	30	GREY/grau			
		2-928247-6	6	06-D	30	25	BLUE/blau			
		0-1703150-6	6	06-C	30	25	GREY/grau			
		0-928247-6	6	06-C	30	25	GREY/grau	UL94 V-2	B	
		6-928247-5	5	-	25	20	NATURE/natur			
		5-928247-5	5	-	25	20	GREEN/grün			
		3-928247-5	5	05-D	25	20	BLUE/blau			
		2-1703150-5	5	05-B	25	20	BLACK/schwarz	UL94 V-2	B	
		2-928247-5	5	05-B	25	20	BLACK/schwarz			
		9-928247-4	4	-	20	15	NATURE/natur			
		5-928247-4	4	04-B	20	15	BLACK/schwarz			
		4-928247-4	4	04-A	20	15	NATURE/natur	UL94 V-0	A	
		283-928247-4	4	04-G	20	15	VIOLET/violett (lila)			
		2-928247-4	4	04-F	20	15	WHITE/weiß			
		0-928247-4	4	04-C	20	15	GREY/grau			
		5-928247-3	3	-	15	10	NATURE/natur	UL94 V-2	B	
NATURE	1-969484-7	4-928247-3	3	03-H	15	10	BROWN/brau			
NATURE	1-969484-8	3-928247-3	3	03-D	15	10	BLUE/blau			
NATURE	3-969484-7	2-928247-3	3	03-G	15	10	VIOLET/violett (lila)			
		0-928247-3	3	-	15	10	YELLOW/gelb	UL94 V-2	B	
		9-928247-2	2	-	10	5	NATURE/natur			
		8-928247-2	2	02-C	10	5	GREY/grau			
NATURE	0-969484-3	7-928247-2	2	02-P	10	5	PURPLED/purpurrot			
		6-928247-2	2	02-A	10	5	NATURE/natur	UL94 V-2	B	
		5-928247-2	2	02-E	10	5	GREEN/grün			
		4-928247-2	2	02-K	10	5	YELLOW GREEN/gelbgrün			
		3-928247-2	2	02-I	10	5	ORANGE/orange			
		282-928247-2	2	02-O	10	5	PINK/rosa	UL94 V-2	B	
		0-928247-2	2	02-B	10	5	BLACK/schwarz			
		PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH Rasthaken	MATED WITH Gegenstecker
COLOUR	SUPERSEDED BY PN:	Bestell-Nr.	Pol.	Rast 5	Maß A	Maß B	Farbe			
TABLE/TABELLE										

KEYING RIB te Kodierrippe	THIS DRAWING IS A CONTROLLED DOCUMENT. DWN K. Munz 18JUL2017 CHK Th. Klenner 07-NOV-06 APPV PRODUCT SPEC 108-18049 APPLICATION SPEC	DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 ±0.1 ±0.03 ±0.001 ±0.0001		WEIGHT -	SIZE A1	CAGE CODE 00779	DRAWING NO C=1241965	RESTRICTED TO -
				MATERIAL SEE TABLES						
		FINISH -								



		TE Connectivity	
2-12 POS. STANDARD TIMER HSG WITH EXTERIOR LOCKING			
SCALE 5:1		SHEET 2 of 4	
Customer Drawing		REV B5	

LOC	DIST	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1			

-  ONLY FOR 2322912-3. TOLERANCE IS +0.1/-0.15
-  ONLY FOR 2322912-6. 1-2364737-1. TOLERANCE IS -0.30
-  CANDIDATE PRELIMINARY P/N. NOT YET OFFICIAL. ONLY FOR DISCUSSION. NOT YET RELEASED FOR PRODUCTION.
-  DOUBLE SOURCE RESIN: ALTERNATIVE RESIN UNDER APPROVAL.

	5-1241965-5	5	05-B	25	20	NATURAL	UL94-V0 & GW EPT 750 no flame △4 △3	E	△2 △1
	1-2364737-1	11	11-B	55	50	BLUE	UL94-V0 & GW EPT 750 no flame △4 △3	B	△2 △1
△4 △3	2364737-9	9	-	45	40	BLUE		C	△2 △1
	2364737-5	5	-	25	20	BLUE		B	△2 △1
	1-2364737-2	2	02-B	10	5	BLUE		B	△2 △1
	2364737-2	2	02-A	10	5	BLUE		B	△2 △1
	2322912-8	8	08-D	40	35	BLUE	PA66 UL94 V0 GW T 750	B	△2 △1
	2322912-6	6	06-D	30	25	BLUE		B	△2 △1
	2322912-3	3	-	15	10	YELLOW		B	△2 △1
△4	2-2322912-2	2	02-A	10	5	NATURE		B	△2 △1
	1-2322912-2	2	02-G	10	5	BLUE		B	△2 △1
	2322912-2	2	02-C	10	5	GREY		B	△2 △1
	5-1241965-7	7	07-C	35	30	NATURAL	PA66 UL94 V0 GW T 750 CT1350	E	△2 △1
△4	4-1241965-7	7	-	35	30	NATURAL		E	△2 △1
	5-1241965-5	5	05-B	25	20	NATURAL		E	△2 △1
	5-1241965-4	4	-	20	15	NATURAL		E	△2 △1
△4	4-1241965-4	4	-	20	15	NATURAL		E	△2 △1
	3-1241965-4	4	-	20	15	NATURAL		E	△2 △1
	2-1241965-4	4	-	20	15	NATURAL		E	△2 △1
	1-1241965-4	4	04-C	20	15	NATURAL		E	△2 △1
	8-1241965-2	2	02-C	10	5	NATURAL		E	△2 △1
	2-1241965-2	2	-	10	5	NATURAL		E	△2 △1
	PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
SPECIAL VERSION: UL94 V0 & GW T 750									

KEYING PLAN SEE SHEET 2 OF 4

2345754-1	2	02-C	10	5	NATURAL	PA66 UL94 V0	E	 
PART NO.	POS.	RAST 5	DIM A	DIM B	COLOUR	MATERIAL	LOCKING LATCH	MATED WITH
SPECIAL VERSION: UL94 V0								


THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN: Kishor M 18JUL2017
CHK: K. Munz 07-NOV-06
APVD: Th. Klenner 07-NOV-06

 TE Connectivity

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -



MATERIAL SEE TABLES -

NAME

PRODUCT SPEC 108-18049

APPLICATION SPEC -

WEIGHT -

Customer Drawing

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

1241965

-

SCALE

5:1

SHEET

3




OF

4


BY

B54


SPECIAL VERSIONS
9 POS STD. TIMER HSG. WITH TANGLING PROTECTION









ONLY FOR 0-964702-2




SPECIAL VERSION
8 POS SPECIAL STD. TIMER HSG.



SWAGED KEYING RIB



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN Kishor M 18JUL2017		 TE Connectivity							
DIMENSIONS:			CHK K. Munz 07-NOV-06									
mm			TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		NAME							
			APVD Th. Klenner 07-NOV-06		2-12 POS. STANDARD TIMER HSG WITH EXTERIOR LOCKING							
			PRODUCT SPEC									
			108-18049									
			APPLICATION SPEC									
MATERIAL SEE TABLES			WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
			-		A1		00779		©=1241965	-		
			Customer Drawing		SCALE		5:1		SHEET	4 of 4	REV	B54

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1241965-6](#)