

D

C

B

A





D

C

B

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		BB	ECR-15-016499	16NOV2015	KR	TN



NOTES:

- POWER RATING: 200W
- INSULATION RESISTANCE: DC 500V - 20 M Ohms Min
- VOLTAGE RESISTABILITY: AC 2500V 1 MINUTE
- UP TO 9R1 RIBBED 10R UPWARD SMOOTH.
- TUBE BORE AND SIDE FACES SHOULD BE FREE OF PAINT
- PARTS SHALL BE BLANK, SMOOTH, FREE OF BURRS AND ALL OTHER FOREIGN MATERIAL
- FOR FURTHER INFORMATION SEE DATASHEET FOR TE SERIES HIGH POWER WIRE WOUND RESISTOR
- FOR SPECIFIC PART NUMBER, RESISTANCE VALUE AND TOLERANCE PLEASE REFER TO SMART PART SEARCH

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRASAD K 26SEP2011	 TE Connectivity				
DIMENSIONS: mm		CHK J.CATCHPOLE 26SEP2011					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.CATCHPOLE 26SEP2011	NAME HIGH POWER WIRE WOUND RESISTOR TE 200W SERIES				
 0 PLC ±0.5 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±0.5° FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -					
MATERIAL -		SIZE A2		CAGE CODE 00779	DRAWING NO C=1879447	RESTRICTED TO -	
		Customer Drawing			SCALE 1:1	SHEET 1 OF 1	REV BB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1879447-0](#)