

4

3

2

1

© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	DIMENSION CHANGE	ECO-21-004260	10-JUN-21	XR.L K.T

TE

0 Z T - S S - 1 1 2 D M 1

cULus

TV-8/120V~

CEC

A

16A 240V~

C:MADE IN CHINA

OEG

1 CHARACTER(A TO Z)
FOR LINE IDENTIFIER

LOT NO.

20.4

H

H

4.1

0.6

0.3

0.3

0.6

1.85

20

5.0

2.3

7.5

12.8

29.2

PART A

PART B

NOTES:

1.TERMINAL DIMENSION IS NOT INCLUDING SOLDER TIP.

2.LOT NO. SYSTEM AS FOLLOWING:

0 8 2 5
WEEK
YEAR

3.GENERAL TOLERANCE AS FOLLOW:

TOLERANCE	
0~0.99mm	±0.1
1mm~2.99mm	±0.2
3mm MIN.	±0.3

4.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKNESS AND DIAMETER.
+0.5mm FOR LENGTH.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 13MAY2009

CHK LIU,DAVEY

BANGHUA,YU

APVD SUNNY,ZHANG

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

OZT-D/LM1 CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1461254-2

SCALE 4:1

SHEET 1 OF 2

REV H

4

3

2

1

C

TE Connectivity. All Rights Reserved.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	G		16-DEC-14		

107-79006

SUPERCED BY 1461392-8	9-1419145-2	OZT-SH-112LM1	OZT-SH-112LM1	12V	32
ACTIVE	2-1419124-7	OZT-SH-124LM1	OZT-SH-124LM1	24V	31
SUPERCED BY 3-1440002-8	3-1419124-4	OZT-SS-148LM1	OZT-SS-148LM1	48V	30
OBSOLETE	3-1419124-3	OZT-SS-124LM1	OZT-SS-124LM1	24V	29
OBSOLETE	3-1419124-1	OZT-SS-112LM1	OZT-SS-112LM1	12V	28
ACTIVE	1-1461392-2	OZT-SH-148LM1	OZT-SH-148LM1	48V	27
ACTIVE	1-1461392-1	OZT-SH-148DM1	OZT-SH-148DM1	48V	26
ACTIVE	1-1461392-0	OZT-SH-124LM1	OZT-SH-124LM1	24V	25
ACTIVE	1461392-9	OZT-SH-124DM1	OZT-SH-124DM1	24V	24
ACTIVE	1461392-8	OZT-SH-112LM1	OZT-SH-112LM1	12V	23
ACTIVE	1461392-7	OZT-SH-112DM1	OZT-SH-112DM1	12V	22
ACTIVE	1461392-6	OZT-SH-109LM1	OZT-SH-109LM1	9V	21
ACTIVE	1461392-5	OZT-SH-109DM1	OZT-SH-109DM1	9V	20
ACTIVE	1461392-4	OZT-SH-106LM1	OZT-SH-106LM1	6V	19
ACTIVE	1461392-3	OZT-SH-106DM1	OZT-SH-106DM1	6V	18
ACTIVE	1461392-2	OZT-SH-105LM1	OZT-SH-105LM1	5V	17
ACTIVE	1461392-1	OZT-SH-105DM1	OZT-SH-105DM1	5V	16
ACTIVE	1-1461254-0	OZT-SS-148DM1	OZT-SS-148DM1	48V	15
ACTIVE	1461254-9	OZT-SS-124DM1	OZT-SS-124DM1	24V	14
ACTIVE	1461254-8	OZT-SS-109LM1	OZT-SS-109LM1	9V	13
ACTIVE	1461254-7	OZT-SS-109DM1	OZT-SS-109DM1	9V	12
ACTIVE	1461254-6	OZT-SS-106LM1	OZT-SS-106LM1	6V	11
ACTIVE	1461254-5	OZT-SS-106DM1	OZT-SS-106DM1	6V	10
ACTIVE	1461254-4	OZT-SS-105LM1	OZT-SS-105LM1	5V	9
ACTIVE	1461254-3	OZT-SS-105DM1	OZT-SS-105DM1	5V	8
ACTIVE	1461254-2	OZT-SS-112DM1	OZT-SS-112DM1	12V	7
ACTIVE	1461254-1	OZT-SS-103DM1	OZT-SS-103DM1	3V	6
ACTIVE	3-1440002-8	OZT-SS-148LM1	OZT-SS-148LM1	48V	5
ACTIVE	3-1440002-7	OZT-SS-124LM1	OZT-SS-124LM1	24V	4
ACTIVE	3-1440002-6	OZT-SS-112LM1	OZT-SS-112LM1	12V	3
SUPERCED BY 1-1461392-0	3-1440002-5	OZT-SH-124LM1	OZT-SH-124LM1	24V	2
SUPERCED BY 1461392-8	3-1440002-4	OZT-SH-112LM1	OZT-SH-112LM1	12V	1

PACKING SPEC.	PART STATUS	TE PART NO	DESCRIPTION	PART A	PART B	ITEM
---------------	-------------	------------	-------------	--------	--------	------

CIRCUIT DIAGRAM(2/1)
(BOTTOM VIEW)DRILLING DIAGRAM
(BOTTOM VIEW)

		UV RESIN	UV SEAL	16
		EPOXY RESIN	SEAL	15
		Cu ALLOY	HINGE SPRING	14
		PBT	CASE	13
		MW79	MAGNETIC WIRE	12
UL94V-0		PET	BASE	11
UL94HB		PBT	BOBBIN	10
	SOLDER DIP	Cu ALLOY	COIL TERMINAL	9
UL94V-0		PPS	CARD	8
		Ag ALLOY	MOVABLE CONTACT	7
		Ag ALLOY	STATIONARY CONTACT	6
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	5
	SOLDER DIP	Cu ALLOY	NO-TERMINAL	4
	Ni PLATED	STEEL	CORE	3
	Ni PLATED	STEEL	ARMATURE	2
	Ni PLATED	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

RELAY TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LIU, DAVEY 13MAY2009	
DIMENSIONS: mm		CHK BANGHUA, YU	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SUNNY, ZHANG	
0 PLC ±		NAME	
1 PLC ±		PRODUCT SPEC	
2 PLC ±		APPLICATION SPEC	
3 PLC ±		WEIGHT	
4 PLC ±		SIZE	
ANGLES ±		CAGE CODE	
FINISH		DRAWING NO	
MATERIAL		RESTRICTED TO	
		A3 00779 C=1461254-2	
CUSTOMER DRAWING		SCALE 4:1 SHEET 2 of 2 REV H	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1461392-8](#)