

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		BB	INITIAL RELEASE	19NOV2015	KR	TN

D

C

B



A

D



C

B


A



- NOTES:
1. RATED POWER: 1200W
 2. TEMPERATURE COEFFICIENT OF RESISTANCE: < ±400ppm/°C
 3. INSULATION RESISTANCE DC 500V - 20 M Ohms MIN.
 4. FAULT CONDITION: 11kW FOR 3 SECONDS
 5. FOR FURTHER INFORMATION SEE DATASHEET FOR TE SERIES HIGH POWER WIRE WOUND RESISTOR
 6. FOR SPECIFIC PART NUMBER, RESISTANCE VALUE AND TOLERANCE PLEASE REFER TO SMART PART SEARCH



RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 16NOV2015	 TE Connectivity					
DIMENSIONS: mm		CHK ALLAN P 16NOV2015						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.5 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±0.5° FINISH	APVD TONY N 16NOV2015	NAME HIGH POWER WIRE WOUND RESISTOR TE 1200 SERIES					
		PRODUCT SPEC -						
		MATERIAL -	-	APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=1879454	RESTRICTED TO -
				WEIGHT -	SCALE 1:2		SHEET 1 OF 1	REV BB
Customer Drawing								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1879454-8](#)