





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HB	—		B	CHANGE RAW MATERIAL OF CARD ECO-19-012552	14-AUG-19	TOD	K.T
			B1	REMOVED SEMKO LOGO ECN-21-112550	14-AUG-21	G.R	K.T



- NOTES:
- ① 1. LOT NO. SYSTEM AS FOLLOWING:

WEEK
YEAR
 - ② 2.TERMINAL DIMENSIONS BEFORE SOLDER DIP
 - ③ 3.FOR THE TIN-PLATING OF THE PINS: +0.1mm FOR WIDTH, THICKNESS AND DIAMETER
+0.5mm FOR LENGTH

DRILLING DIAGRAM
BOTTOM VIEW (2/1)



CONNECTION DIAGRAM
BOTTOM VIEW (2/1)





Diagram dimension	Tolerance
max. 1mm	±0.1mm
1 - 3mm	±0.2mm
min. 3mm	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.OKAKO	 TE Connectivity											
		CHK H.SASAKI												
DIMENSIONS: mm		APVD A.NAGAI	NAME SDT-DMR											
		PRODUCT SPEC —												
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		APPLICATION SPEC —	SIZE			CAGE CODE		DRAWING NO		RESTRICTED TO				
		WEIGHT —	A3		00779		C-1461267		—					
MATERIAL —		FINISH —	CUSTOMER DRAWING						SCALE 4:1		SHEET 1 of 2		REV B1	

LOC	DIST	REVISIONS					
HB	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—


SDT-S-118DMR	1461267-3	108-79782	18V	SDT-S-118DMR	STANDARD	h
SDT-S-148DMR	1461023-2	108-79440	48V	SDT-S-148DMR	STANDARD	g
SDT-S-124DMR	1419126-1	108-79439	24V	SDT-S-124DMR	STANDARD	f
SDT-S-112DMR	9-1419125-7	108-79438	12V	SDT-S-112DMR	STANDARD	e
SDT-S-109DMR	8-1419125-9	108-79437	9V	SDT-S-109DMR	STANDARD	d
SDT-S-106DMR	1461267-2	108-79436	6V	SDT-S-106DMR	STANDARD	c
SDT-S-105DMR	8-1419125-0	108-79435	5V	SDT-S-105DMR	STANDARD	b
SDT-S-103DMR	1461267-1	108-79434	3V	SDT-S-103DMR	STANDARD	a
TYPE NAME	PART NO	PRODUCT SPEC	PART B	PART A	DESCRIPTION	No

RELAY TYPE

		EPOXY RESIN	SEAL (BASE & TERMINAL)	15
		EPOXY RESIN	SEAL (BASE & YOKE)	14
		3UEW	MAGNETIC WIRE	13
94V-0		P.B.T	CASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		PPS ⑧	CARD	9
		AgSn0	MOVABLE CONTACT	8
		AgSn0	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	NO.TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

DWN
K.OKAKO

CHK
H.SASAKI

APVD
A.NAGAI

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
—

TE Connectivity

SDT-DMR

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1461267

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2 OF 2

REV
B1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1419126-1](#)