





LOC		DIST		REVISIONS					
GP	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			C	REV PER EC 09-028503			30DEC09	RG	DO




SCALE 5:1

- 1 MATERIAL: BRASS  
2 MATERIAL: HIGH CONDUCTIVITY COPPER ALLOY  
3 FINISH: CONTACT MATING AREA .38µm MIN Au;  
CRIMP AREA 2.03µm MIN. Sn;  
UNDERPLATE OVERALL 1.27µm MIN. Ni  
4 FINISH: CONTACT MATING AREA 1.27µm MIN Au;  
CRIMP AREA 2.03µm MIN. Sn;  
UNDERPLATE OVERALL 1.27µm MIN Ni  
5 CONTACT SHOWN W/O CARRIER, OR HIDDEN LINES, FOR CLARITY  
6 CUT OFF TO BE .13 MAX  
7 INSULATION DIAMETER : 2.0-3.1 mm  
8 WIRE DIAMETER: 16-20 AWG  
10 THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.  
11 FINISH: ENTIRE CONTACT 1.27µm MIN Au;  
UNDERPLATE OVERALL 1.27µm MIN Ni

SCALE 12:1



SECTION A-A  
SCALE 20:1



SECTION B-B  
SCALE 20:1

			11.4	1-1489128-6
			9.8	1-1489128-5
			11.4	1-1489128-4
			9.8	1-1489128-3
	-		11.4	1-1489128-0
	-		9.8	1489128-9
	-		11.4	1489128-8
	-		9.8	1489128-7
	-		11.4	1489128-3
	-		9.8	1489128-2
MATERIAL	LOOSE PIECE	FINISH	DIM "A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AL FRANTUM CHK -	15 MAY 02		Tyco Electronics Corporation Middletown, Pa 17057
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		NAME	
DIMENSIONS: mm	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-1998		MINI POWER DRAWER	
		APPLICATION SPEC 114-13067		CRIMP PLUG CONTACT	
MATERIAL 1 2	FINISH 3 4	WEIGHT -	SIZE A1	CAGE CODE 00779	DRAWING NO 1489128
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1489128-5](#)