

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-15-009282	05AUG2015	KG	DW

SET SCREW, M4x6
MAT'L: STAINLESS STEEL

EXTENSION
MAT'L: SEE TABLE
FINISH: SEE TABLE

CRIMP SUPPORT
MAT'L: NICKEL-SILVER ALLOY

CRIMP SUPPORT
MAT'L: NICKEL-SILVER ALLOY

CONDUCTIVE BLACK ZINC-NICKEL
ON ALUMINUM ALLOY

	4 x 3mm	2-1918934-8
	6.7mm	2-1918934-7
	6.0mm	2-1918934-6
	5.5mm	2-1918934-5
	5.0mm	2-1918934-4
	4.2mm	2-1918934-3
	3.2mm	2-1918934-2
DESCRIPTION	MAXIMUM CABLE DIAMETER	PART NUMBER

SUPERSEDED BY:
2-1918934-8
SUPERSEDED BY:
2-1918934-7
SUPERSEDED BY:
2-1918934-6
SUPERSEDED BY:
2-1918934-5
SUPERSEDED BY:
2-1918934-4
SUPERSEDED BY:
2-1918934-3
SUPERSEDED BY:
2-1918934-2

CONDUCTIVE OLIVE DRAB ZINC
ON ALUMINUM ALLOY


NICKEL ALUMINUM BRONZE ALLOY

HARD ANODIZE FINISH
ON ALUMINUM ALLOY

	4 x 3mm	2-1918934-1
	6.7mm	2-1918934-0
	6.0mm	1-1918934-9
	5.5mm	1-1918934-8
	5.0mm	1-1918934-7
	4.2mm	1-1918934-6
	3.2mm	1-1918934-5
	4 x 3mm	1-1918934-4
	6.7mm	1-1918934-3
	6.0mm	1-1918934-2
	5.5mm	1-1918934-1
	5.0mm	1-1918934-0
	4.2mm	1918934-9
	3.2mm	1918934-8
	4 x 3mm	1918934-7
	6.7mm	1918934-6
	6.0mm	1918934-5
	5.5mm	1918934-4
	5.0mm	1918934-3
	4.2mm	1918934-2
	3.2mm	1918934-1
DESCRIPTION	MAXIMUM CABLE DIAMETER	PART NUMBER

I. PACKAGED LOOSE PIECE.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±
MATERIAL AS LISTED	FINISH AS LISTED
-	-

DWN K. GLATFELTER 31OCT2006	CHK D. WERTMAN 04JUN2008	APVD D. WERTMAN 04JUN2008
PRODUCT SPEC		
-		
APPLICATION SPEC		
-		
WEIGHT		
-		
Customer Drawing		

 TE Connectivity			
NAME CABLE ADAPTER KIT, STD BULKHEAD, PRO BEAM JR.			
-			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1918934	-
SCALE		SHEET	REV
2:1		1 OF 1	A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1918934-7](#)