





REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
B12	ECR-21-105046		28JUN2021	SM
B13	ECR-21-105810		05JUL2021	SM
B14	ECR-21-107712		27JUL2021	SM
B15	ECR-21-114094		22SEP2021	SM




- 12 STRIPE IN YELLOW COLOR WHERE SHOWN PRESENT ON THE PARTS PRODUCED IN TE COLLEGNO ONLY
- 14 PNs WITHOUT THE INTERNAL WALL NEED ASSISTANT GUIDE DURING THE APPLICATION SUCH AS RAST TAB HEADER
- 13 PRELIMINARY PART NOT RELEASED FOR PRODUCTION
- 12 CAVITY NO.
- 11 KEYING, BETWEEN POSITION
- 10 COLOR MARKING IN THIS AREA.
- 9 SLOT FOR KEYING BETWEEN POSITION
- 8 COLOR STRIP ON COVER OF HOUSING. NOT THE COLOR OF HOUSING
- 7 TE LOGO
- 6 INCLUSIVE COPPER CLOADING
- 5 PCB PREFERABLY CHAMPFERED
- 4 WIRE RANGE: 0.22-0.35mm² SEE APPLICATION SPEC. 114-18467-1
- 3 IEC60695-2-11 / IEC60335-1 GLOWWIRE TEST 750 °C WITHOUT FLAME


- 1 KEYING RIBS; CUTTING WITH TERMINATION MACHINE POSSIBLE



PCB LAYOUT- SOLDERING SIDE



SECTION B-B



2	SEE TABLE	CONTACT	CuSn
1		HOUSING	PA 13
SL NO	PN	DESCRIPTION	MATERIAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Winter Wang 22-Sep-21	TE Connectivity	
DIMENSIONS: mm		CHK Daniel Zhong 15-Mar-17		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Riccardo Robore 15-Mar-17	NAME DUOPUG MARK II SIDE LOCKING	
0 PLC ±0.2		PRODUCT SPEC	SIZE A1	
1 PLC ±0.2		APPLICATION SPEC	CAGE CODE	
2 PLC ±0.2		114-18467-1	DRAWING NO	
3 PLC ±0.2		WEIGHT	RESTRICTED TO	
4 PLC ±0.2		FINISH	C=2306286	
MATERIAL		CUSTOMER DRAWING	SCALE 8:1	
			SHEET 1 OF 2	
			REV B15	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1534415-2](#)