



1471-9 (1/15)

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By - ALL RIGHTS RESERVED.		



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

D	[.012]	[.33]	A	12	6.5[.256]	1-2	29	0.10[.004]	--	9-192047-0	OBSOLETE
	[.012]	[.33]	A	12	6.5[.256]	3-2	29	0.10[.004]	--	8-192047-9	
	[.012]	[.13]	A	12	2.54[.100]	17-2	12	0.10[.004]	--	8-192047-8	
	[.014]	[.38]	A	12	7.9[.313]	3-2	35	0.10[.004]	--	8-192047-7	OBSOLETE
	[.012]	[.06]	A	12	1.0[.040]	5-2	6	0.10[.004]	--	8-192047-6	
	[.023]	--	C	12	--	2	35	0.10[.004]	--	8-192047-5	
	[.023]	--	C	12	--	2	--	0.10[.004]	--	8-192047-4	
	[.012]	[.33]	A	12	6.5[.256]	6-2	29	0.10[.004]	--	8-192047-3	
	[.012]	[.57]	A	12	11.9[.471]	6-2	55	0.10[.004]	--	8-192047-2	
	[.014]	[.09]	A	12	1.57[.062]	UNPL	6	0.10[.004]	--	8-192047-1	OBSOLETE
[.014]	[.09]	A	12	1.57[.062]	3-2	6	0.10[.004]	--	8-192047-0	OBSOLETE	
[.025]	--	C	12	--	UNPL	23	0.10[.004]	--	7-192047-9	OBSOLETE	
C	[.012]	[.43]	A	12	10.1[.400]	UNPL	45	0.10[.004]	--	7-192047-8	OBSOLETE
	[.012]	[.40]	A	12	8.7[.342]	UNPL	39	0.10[.004]	--	7-192047-7	
	[.012]	[.36]	A	12	7.2[.284]	UNPL	32	0.10[.004]	--	7-192047-6	
	[.012]	[.29]	A	12	6.5[.256]	UNPL	29	0.10[.004]	--	7-192047-5	
	[.012]	[.28]	A	12	6.1[.241]	UNPL	28	0.10[.004]	--	7-192047-4	
	[.012]	[.26]	A	12	5.7[.226]	UNPL	26	0.10[.004]	--	7-192047-3	
	[.012]	[.25]	A	12	5.3[.210]	UNPL	24	0.10[.004]	--	7-192047-2	OBSOLETE
	[.012]	[.23]	A	12	4.8[.188]	UNPL	22	0.10[.004]	--	7-192047-1	
	[.012]	[.20]	A	12	4.3[.168]	UNPL	19	0.10[.004]	--	7-192047-0	
	[.023]	--	C	12	--	UNPL	--	0.10[.004]	--	6-192047-9	
[.012]	[.06]	A	12	1.0[.040]	4-7	6	0.10[.004]	--	6-192047-8	OBSOLETE	
B	NO DATA									6-192047-7	
	NO DATA									6-192047-6	
	NO DATA									6-192047-5	
	NO DATA									6-192047-4	
	[.012]	[.43]	A	12	1.0[.040]	4-2	45	0.10[.004]	06085	6-192047-3	
									06800	6-192047-2	OBSOLETE
	SUPERSEDED BY 193811-1								06801	6-192047-1	SUPERSEDED
	SUPERSEDED BY 192047-7								06078	6-192047-0	SUPERSEDED
	NO DATA								06054	5-192047-9	OBSOLETE
	NO DATA								06053	5-192047-8	OBSOLETE
[.012]	[.52]	A	12	12.7[.500]	UNPL	55	0.10[.004]	06057	5-192047-7	OBSOLETE	
[.012]	[.43]	A	12	10.1[.400]	3-2	45	0.10[.004]	06020	5-192047-6		
[.012]	[.40]	A	12	8.7[.342]	3-2	39	0.10[.004]	06019	5-192047-5	OBSOLETE	
[.012]	[.36]	A	12	7.2[.284]	3-2	32	0.10[.004]	06018	5-192047-4	OBSOLETE	
[.012]	[.35]	A	12	6.9[.272]	6-2	31	0.10[.004]	06046	5-192047-3		
[.012]	[.35]	A	12	6.9[.272]	UNPL	31	0.10[.004]	06077	5-192047-2	OBSOLETE	
[.012]	[.33]	A	12	6.5[.256]	4-2	29	0.10[.004]	06040	5-192047-1		
LH		FREE DIA (REF)	STYLE	MAT'L (NOTE)	MATING PIN Ø REF	PLATING	NUM LOUV	MATL THK	REF	PART NUMBER	



STYLE A

(FEMALE)



STYLE C
(STRIP)

- 15 CUT TO LENGTH OF 25mm.
- 16 OBSOLETE PART NUMBER.
- 17 FINISH: GOLD PLATE 30 MIN THICK MIN.
- 18 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RA JAYNE 06-11-92 CHK RA JAYNE 06-11-92		 TE Connectivity Ltd.				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME			
		0 PLC ± —		PRODUCT SPEC				
		1 PLC ± —		—				
		2 PLC ± .02		APPLICATION SPEC				
		3 PLC ± .010		—				
		4 PLC ± —		SIZE				
		ANGLES ± —		CAGE CODE				
MATERIAL		FINISH		DRAWING NO				
SEE TABLE		SEE TABLE		RESTRICTED TO				
				A2 00779 C-192047				
				—				
CUSTOMER DRAWING				SCALE 20:1		SHEET 2 of 2		
				REV		P		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-192047-1](#)