








THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	2016
© COPYRIGHT 2016	TE Connectivity Germany GmbH	ALL RIGHTS RESERVED.	

LOC	DIS1	REVISIONS					
A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D21	ECR-20-100619		05NOV2020	W	FL
		D22	ECR-21-108728		16AUG2021	SM	FL
		D23	ECR-21-114072		22SEP2021	SM	FL
		D24	ECR-21-115341		28SEP2021	SM	FL



KEYING PLAN (VIEW Z)
Kodierschema (Ansicht Z)



- | | |
|----|---|
| 16 | KEYING BETWEEN POSITIONS |
| 15 | UL94 V0 AND GLOW WIRE TEST 750 °C WITHOUT FLAME |
| 14 | PRELIMINARY PART NOT RELEASED FOR PRODUCTION |
| 13 | OBSOLETE |
| 12 | TE LOGO |

- X...CAVITY LOADED WITH CONTACT
 0...CAVITY WITHOUT CONTACT
 X...Kammer mit Kontakt
 0...Kammer ohne Kontakt
- GLOW WIRE TEST 750 °C WITHOUT FLAME
 Gluehdrahttest 750°C ohne Flamme
- INCLUSIVE COPPER CLADDING:
 Inclusive Kupferkaschierung:
- PCB PREFERABLY CHAMFERED.
 Leiterplatte vorzugsweise angefasst.
- SLOT FOR SIDE KEYING.     .
 Schlitz fuer Seitenkodierung.
- COLOUR MARKING ON TOP OF HOUSING OPTIONAL ON TERMINATION MACHINE
 Farbmarkierung auf Gehäuseoberseite optional an Verarbeitungsmaschine
- MATING PART: PCB (WITH FRAMES ACC. RAST 2.5 E.G. PN 964 575/576)
 TABHEADER PN 1 534 787/788
 5 Passender Gegenstecker:Leiterplatten (mit Rahmen nach RAST 2.5 z.B. 964 575/576)
 Tabwannen Nr. 1 534 787/788
- SIDE KEYING, ON LAST CAVITY
 Seitenkodierung, an letzter Kammer
- SIDE KEYING, on CAVITY 1
 Seitenkodierung, an Kammer 1
- WIRE RANGE: 0.35-0.75 mm²
 Drahtgrößenbereich: 0.35-0.75 mm²
- KEYING RIBS; CUTTING WITH TERMINATION MACHINE POSSIBLE
 Koddierippe; Schneiden auf der Verarbeitungsmaschine möglich

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 130CT2016 H.Karabiyik CHK 24 JAN2002 B. Schnaube APVD 24 JAN2002 T. Klenner		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 0^\circ$		NAME AMP DUOPLUG POWER FEMALE CONNECTOR (Standard Version) -	
		PRODUCT SPEC 108-18780 APPLICATION SPEC 114-18458		SIZE A 1	
MATERIAL -		FINISH -		CAGE CODE 00779	
WEIGHT -		DRAWING NO C=1534415		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1 SHEET 1 OF 2 REV 024	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

GWEPT 750°C NO FLAME + UL94-V2																		
X	X	X	X	X	X	X	X	X	X	NATURE	10	45	49.9	3/4	-	-	2-1534415-0	
X	X	X	X	X	X	X	X	X	X	NATURE	10	45	49.9		-	-	1-1534415-0	
	X	X	X	X	X	X	X	X	X	NATURE	9	40	44.9		-	-	0-1534415-9	
		X	X	X	X	X	X	X	X	NATURE	8	35	39.9		-	-	0-1534415-8	
			X	X	X	X	X	X	X	NATURE	7	30	34.9		-	-	0-1534415-7	
				X	X	X	X	X	X	NATURE	6	25	29.9		-	-	0-1534415-6	
					X	X	X	X	X	NATURE	5	20	24.9		-	-	0-1534415-5	
						X	X	X	X	NATURE	4	15	19.9		-	X	3-1534415-4	
						X	X	X	X	NATURE	4	15	19.9	3/4	X	X	2-1534415-4	
						X	X	X	X	NATURE	4	15	19.9	2/3	X	X	1-1534415-4	
						X	X	X	X	NATURE	4	15	19.9		-	-	0-1534415-4	
							X	X	X	RED	3	10	14.9		X		8-1534415-3	
							X	X	X	GREEN	3	10	14.9			X	7-1534415-3	
							X	X	X	NATURE	3	10	14.9	1/2		X	6-1534415-3	
							X	0	X	NATURE	3	10	14.9		-	-	4-1534415-3	
							X	X	X		3	10	14.9		X	X	3-1534415-3 13	
							X	X	X	NATURE	3	10	14.9		X	-	2-1534415-3	
							X	X	X	NATURE	3	10	14.9		-	X	1-1534415-3	
							X	X	X	NATURE	3	10	14.9		-	-	0-1534415-3	
								X	X	BROWN	2	5	9.9		-	-	4-1534415-2 6	
								X	X	NATURE	2	5	9.9		X	X	3-1534415-2	
								X	X	NATURE	2	5	9.9		X	-	2-1534415-2	
								X	X	NATURE	2	5	9.9		-	X	1-1534415-2	
								X	X	NATURE	2	5	9.9		-	-	0-1534415-2	
10	9	8	7	6	5	4	3	2	1	6	POS. Polzahl	DIM A	DIM B	16	4	3	PN Bestell-Nr.	
CAVITY LOADED 11										COLOR				KEYING 16	KEYING 4	KEYING 3		
2		SEE TABLE siehe Tabelle		KONTAKT		CuNiSi		TINNED										
1				Federleistengehaeuse		PA 6 6		NATUR/Natur										
POS.		PN Bestell-Nr.		DESCRIPTION Beschreibung		MATERIAL		COLOUR/FINISH Farbe/Oberflaeche										

GWEPT 750°C NO FLAME + UL94-V0 																		
X	X	X	X	X	X	X	X	X	X	NATURE	10	40	49.9	3/4	-	-	2-2328644-0 	
X	X	X	X	X	X	X	X	X	X	NATURE	10	40	49.9	-	-	-	1-2328644-0 	
	X	X	X	X	X	X	X	X	X	NATURE	9	40	44.9	-	-	-	-	
			0	0	X	X	X	X	X	NATURE	7	30	34.9	-	-	-	1-2328644-7 	
			X	X	X	X	X	X	X	NATURE	7	30	34.9	-	-	-	2328644-7 	
					X	X	X	X	X	NATURE	5	20	24.9	-	-	-	2328644-5 	
							X	X	X	NATURE	3	10	14.9	-	-	X	2328644-3 	
							X	X	X	NATURE	3	10	14.9	-	X	-	5-1534415-3	
								X	X	NATURE	2	5	9.9	-	-	-	-	
10	9	8	7	6	5	4	3	2	1									
CAVITY LOADED 										COLOR 	POS.	DIM A	DIM B	KEYING 	KEYING 	KEYING 	TE P/N	
2		SEE TABLE siehe Tabelle		CONTACT			CuNiSi			TINNED								
1																		
				Federleistengehaeuse			PA 66			NATUR/Natur								
POS.		TE P/N		DESCRIPTION			MATERIAL			COLOUR/FINISH								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1534415-7](#)