


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00	C		REVISED PER ECO-13-002771	26FEB2013	KH
		D		REVISED PER ECO-19-009248	09JUL2019	AP

D




C

B

A



RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE SHOWN



△ MATERIAL:
CONTACT AND SHIELD: PHOS BRONZE
HOUSING AND CHICKLET: LCP, UL 94V-0, COLOR: BLACK

△ FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS
OF TE PRODUCT SPECIFICATION 108-2303; BASED ON
TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY
LEVEL III APPLICATIONS IN CONTROLLED
ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5µm MIN MATTE TIN OVER 1.27µm MIN NICKEL.
SHIELD 1.27µm MIN NICKEL.

△ CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND
STANDARD IN APPROXIMATE AREA SHOWN.

△ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.

△ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED
LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1,
NOVEMBER 1995.

△ REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.

△ ALL GROUNDS IN ODD NUMBERED COLUMNS ARE COMMONED.
ALL GROUNDS IN EVEN NUMBERED COLUMNS, EXCEPT FOR ROW A
ARE COMMONED.

△ SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA.

1934360-1

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. J. MAGARO 16AUG2007	TE Connectivity	
DIMENSIONS:		CHK W. DAVIS 16AUG2007		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. PATTERSON 12OCT2007	NAME RIGHT ANGLE HEADER ASSEMBLY, DOUBLE WALL, 3 PAIR, 8 COLUMN, Z-PACK TinMan	
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC APPLICATION SPEC	SIZE A100779	
MATERIAL : △	FINISH : △	WEIGHT -	RESTRICTED TO C=1934360	
CUSTOMER DRAWING		SCALE 6:1	SHEET 1	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1934360-1](#)