






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z	REVISED PER ECO-21-006957	25JUN2021	RK	MZ




STRIP



LOOSE-PIECE




SECTION A-A



SECTION B-B

WIRE RANGE : 0.12-0.20 mm<sup>2</sup> (26-24 AWG)  
INSUL. RANGE : 0.9 -1.4 mm (.035-.055)



NOTES	MATERIAL	THICKNESS	AREA
	TIN	2,0 μm	ALL OVER
	NICKEL GOLD TIN	.76 μm 1.01 μm	ALL OVER CONTACT AREA BARREL
	NICKEL GOLD TIN	1.27 μm .76 μm 1.01 μm	ALL OVER CONTACT AREA BARREL
	NICKEL GOLD	1,2 μm	ALL OVER CONTACT AREA ALL OVER
	NICKEL SILVER TIN	2,5 μm	ALL OVER CONTACT AREA BARREL
	SILVER	0,5 μm	ALL OVER
	SILVER	2,5 μm	ALL OVER
	NICKEL TIN	1,27 μm 1,27 μm	ALL OVER ALL OVER

- NOTES :
- UL RECOGNIZED UNDER E28476 VOL VI SEC I
  - FOR CRIMP DETAILS SEE SPEC. 114-19000
  - MEETS PRODUCT SPECIFICATION 108-10042
  - OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
  - OBSOLETE
  - OMISSION OF 6 CONTACTS MAX PER REEL OF 5000PCS

LUBRICATED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH
MATERIAL	REFER TABLE
REFER TABLE	REFER TABLE

DWN	L.V.D.HEIJDEN	19.08.87
CHK	P.V.D.HAGEN	20.08.87
APVD	L.V.SOEST	20.08.87
PRODUCT SPEC	108-10042	
APPLICATION SPEC	114-19000	
WEIGHT		
CUSTOMER DRAWING		

TE Connectivity				
NAME TYPE III+, SIZE 16, SOCKET ASS'Y, 26-24 AWG, 0.9-1.4mm DIA INSULATION				
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	00779	C-163091	-	
SCALE		SHEET	REV	
-		1 OF 1	Z	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-163092-0](#)