




2		1				
LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	C	PLATING INFORMATION ADDED		16 JUL 2019	RK	PS

D



SCALE 2:1
-4 AS SHOWN

5	SEE FIG	46.50	9	2-1986711-6
		126.50	25	2-1986711-5
		121.50	24	2-1986711-4
		116.50	23	2-1986711-3
		111.50	22	2-1986711-2
		106.50	21	2-1986711-1
		101.50	20	2-1986711-0
		96.50	19	1-1986711-9
		91.50	18	1-1986711-8
		86.50	17	1-1986711-7
		81.50	16	1-1986711-6
		76.50	15	1-1986711-5
		71.50	14	1-1986711-4
		66.50	13	1-1986711-3
		61.50	12	1-1986711-2
		56.50	11	1-1986711-1
		51.50	10	1-1986711-0
		46.50	9	1986711-9
		41.50	8	1986711-8
		36.50	7	1986711-7
		31.50	6	1986711-6
		26.50	5	1986711-5
		21.50	4	1986711-4
		16.50	3	1986711-3
		11.50	2	1986711-2
		"L"	POLE	PART NO

1. MATERIAL:
HOUSING - PA66 , UL94 V0
CLAMPING SPRING - STAINLESS STEEL
PIN - COPPER ALLOY - BRIGHT TIN PLATED
2. MECHANICAL:
MIN. PC BOARD HOLES DIAMETER : 1.2 mm
MAX. PC BOARD THICKNESS : 2.4 mm
WIRE STRIPPING LENGTH : 11.5 mm
3. ELECTRICAL:
WIRE RANGE : 12-30 AWG
RATED VOLTAGE : 300V
RATED CURRENT : 16A
CONTACT RESISTANCE : <15 m Ohm
INSULATION RESISTANCE : >1000 M Ohm (500V DC)



4. OPERATING TEMPERATURE RANGE : -40°C TO +105°C

5 PRELIMINARY PART

C

B


A




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 08AUG2011 RAGHAVENDRA	TE Connectivity			
DIMENSIONS: mm		CHK 08AUG2011 SARVER MICHAEL				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 08AUG2011 SARVER MICHAEL	NAME SPRING TYPE. SIDE WIRE ENTRY TERMINAL BLOCK SIDE STACKABLE STRAIGHT 02 - 25 POLES PITCH 5.00mm			
0 PLC ± 1 PLC ±0.5 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -				
MATERIAL SEE NOTES		SEE NOTES	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986711	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 2	REV C

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	2011
© COPYRIGHT 2011	-	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
FT	0		-	SEE SHEET 1	-	-



2-1986711-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 08AUG2011	TE TE Connectivity				
DIMENSIONS: mm		CHK SARVER MICHAEL 08AUG2011					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±1°	APVD SARVER MICHAEL 08AUG2011	NAME SPRING TYPE. SIDE WIRE ENTRY TERMINAL BLOCK SIDE STACKABLE STRAIGHT 02 - 25 POLES PITCH 5.00mm				
		PRODUCT SPEC -					
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL SEE NOTES		FINISH SEE NOTES	WEIGHT -	A3	00779	C-1986711	-
CUSTOMER DRAWING			SCALE 4:1	SHEET 2	OF 2	REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1986711-0](#)