

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

LOC

GP

DIST

00

REVISONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|----|-----|---------------------------|---------|-----|------|
| D1 | | REVISED PER ECO-11-004835 | 11MAR11 | RK | HMR |

BEFORE TERMINATION

14.15
[.557]

AFTER TERMINATION

12.10 MAX
[.476]

POSITION #1 INDICATOR
(ON FAR SIDE)

1.27
[.050]

1.00
[.040]

2.54
[.100]

2.54
[.100]

6.05
[.238]

0.89
[.035]

0.81
[.032]

30°

7.62 MIN
[.300]

A±0.05
[.002]

2.54±0.05
[.100±.002]

2.54±0.05
[.100±.002]

3.81 MIN (FOR CONNECTORS W/O
[.150] CENTER POLARIZER)

5.08 MIN (FOR CONNECTORS W/
[.200] CENTER POLARIZER)

0.64±0.03 SQUARE POST
[.025±.001]

MAX HEIGHT 6.40
[.252]

POST LAYOUT

ELECTRICAL PROPERTIES

| | |
|--------------------------|-------------------------------------|
| CURRENT RATING | 1 AMP |
| INSULATION RESISTANCE | >1 x 10 ⁹ OHMS @ 500 VDC |
| DWV | >500 VRMS AT SEA LEVEL |
| ENVIRONMENTAL PROPERTIES | |
| TEMPERATURE RATING | -55°C TO 125°C |

1. 20 POSITION CONNECTOR ASSEMBLY SHOWN.

△ MOLDED PARTS: THERMOPLASTIC, UL94V-0 RATED, COLOR BLUE.
CONTACTS: BERYLLIUM COPPER.

△ CONTACTS: 0.00076[.000030] MIN GOLD ON MATING AREA,
0.00254-0.00508[.000100-.000200] TIN OR GOLD FLASH ON TERMINATION END,
ALL OVER 0.00127[.000050] MIN NICKEL ON ENTIRE CONTACT.

△ POLARIZER FEATURE DOES NOT EXIST ON POSITION #1 END
FOR 14 POSITION ASSEMBLIES AND SMALLER.

△ POLARIZER FEATURE DOES NOT EXIST ON THIS END FOR
4 & 6 POSITION ASSEMBLIES.

6. FOR TERMINATION OF 26 OR 28 AWG STRANDED OR SOLID
PVC INSULATED FLAT RIBBON CABLE. SEE TYCO ELECTRONICS DRAWINGS
57034 (26 AWG) OR 57040 (28 AWG) FOR DETAILS.

△ STRAIN RELIEF PACKAGED SEPARATELY AND SHIPPED WITH
ASSEMBLY.

14.10±0.20
[.555±.008]

16.59
[.653]

14.14
[.557]

△ STRAIN RELIEF
(SEE TABLE)

BASE OF CONNECTOR

| | | | | | | | | | |
|----------|---------------|------------------|------------|--------------|--------------|--------------|---------------------|-----------------------------|-------------|
| | YES | YES | 3.80[.150] | 85.78[3.377] | 80.01[3.150] | 78.74[3.100] | 64 | 622-6441LF | 3-1658527-2 |
| | NO | YES | 3.80[.150] | 85.78[3.377] | 80.01[3.150] | 78.74[3.100] | 64 | 622-6430LF | 3-1658527-1 |
| OBSOLETE | YES | YES | 3.80[.150] | 80.70[3.177] | 74.93[2.950] | 73.66[2.900] | 60 | 622-6041LF | 3-1658527-0 |
| OBSOLETE | NO | YES | 3.80[.150] | 80.70[3.177] | 74.93[2.950] | 73.66[2.900] | 60 | 622-6030LF | 2-1658527-9 |
| OBSOLETE | NO | YES | 3.80[.150] | 75.62[2.977] | 69.85[2.750] | 68.58[2.700] | 56 | 622-5630LF | 1-1658527-8 |
| | YES | YES | 3.80[.150] | 68.00[2.677] | 62.23[2.450] | 60.95[2.400] | 50 | 622-5041LF | 1-1658527-5 |
| | NO | YES | 3.80[.150] | 68.00[2.677] | 62.23[2.450] | 60.95[2.400] | 50 | 622-5030LF | 1-1658527-4 |
| OBSOLETE | NO | NO | - | 60.38[2.377] | 54.61[2.150] | 53.34[2.100] | 44 | 622-4400LF | 1-1658527-7 |
| | YES | YES | 3.80[.150] | 55.30[2.177] | 49.53[1.950] | 48.26[1.900] | 40 | 622-4041LF | 1-1658527-3 |
| | NO | YES | 3.80[.150] | 55.30[2.177] | 49.53[1.950] | 48.26[1.900] | 40 | 622-4030LF | 1-1658527-2 |
| | YES | YES | 3.80[.150] | 47.68[1.877] | 41.91[1.650] | 40.64[1.600] | 34 | 622-3441LF | 2-1658527-8 |
| | NO | YES | 3.80[.150] | 47.68[1.877] | 41.91[1.650] | 40.64[1.600] | 34 | 622-3430LF | 1-1658527-1 |
| | YES | YES | 3.80[.150] | 42.60[1.677] | 36.83[1.450] | 35.56[1.400] | 30 | 622-3041LF | 2-1658527-7 |
| | NO | YES | 3.80[.150] | 42.60[1.677] | 36.83[1.450] | 35.56[1.400] | 30 | 622-3030LF | 2-1658527-6 |
| | YES | YES | 3.80[.150] | 37.52[1.477] | 31.75[1.250] | 30.48[1.200] | 26 | 622-2641LF | 1-1658527-0 |
| | NO | YES | 3.80[.150] | 37.52[1.477] | 31.75[1.250] | 30.48[1.200] | 26 | 622-2630LF | 1658527-9 |
| | YES | YES | 3.80[.150] | 34.98[1.377] | 29.21[1.150] | 27.94[1.100] | 24 | 622-2441LF | 2-1658527-5 |
| OBSOLETE | NO | YES | 3.80[.150] | 34.98[1.377] | 29.21[1.150] | 27.94[1.100] | 24 | 622-2430LF | 2-1658527-4 |
| | YES | YES | 3.80[.150] | 29.90[1.177] | 24.13[.950] | 22.86[.900] | 20 | 622-2041LF | 1658527-8 |
| | NO | YES | 3.80[.150] | 29.90[1.177] | 24.13[.950] | 22.86[.900] | 20 | 622-2030LF | 2-1658527-3 |
| | YES | YES | 3.80[.150] | 24.82[.977] | 19.05[.750] | 17.78[.700] | 16 | 622-1641LF | 1658527-7 |
| | NO | YES | 3.80[.150] | 24.82[.977] | 19.05[.750] | 17.78[.700] | 16 | 622-1630LF | 1658527-6 |
| | YES | YES | 3.80[.150] | 22.28[.877] | 16.51[.650] | 15.24[.600] | 14 | 622-1441LF | 2-1658527-2 |
| | NO | YES | 3.80[.150] | 22.28[.877] | 16.51[.650] | 15.24[.600] | 14 | 622-1430LF | 1658527-5 |
| OBSOLETE | YES | YES | 3.80[.150] | 19.74[.777] | 13.97[.550] | 12.70[.500] | 12 | 622-1241LF | 2-1658527-1 |
| | NO | YES | 3.80[.150] | 19.74[.777] | 13.97[.550] | 12.70[.500] | 12 | 622-1230LF | 2-1658527-0 |
| | YES | YES | 3.20[.126] | 17.20[.677] | 11.43[.450] | 10.16[.400] | 10 | 622-1041LF | 1658527-4 |
| | NO | YES | 3.20[.126] | 17.20[.677] | 11.43[.450] | 10.16[.400] | 10 | 622-1030LF | 1658527-3 |
| OBSOLETE | NO | NO | - | 14.66[.577] | 8.89[.350] | 7.62[.300] | 8 | 622-0800LF | 1-1658527-6 |
| | YES | YES | 1.90[.075] | 12.12[.477] | 6.35[.250] | 5.08[.200] | 6 | 622-0641LF | 1-1658527-9 |
| | NO | YES | 1.90[.075] | 12.12[.477] | 6.35[.250] | 5.08[.200] | 6 | 622-0630LF | 1658527-2 |
| OBSOLETE | NO | YES | 1.90[.075] | 9.58[.377] | 3.81[.150] | 2.54[.100] | 4 | 622-0430LF | 1658527-1 |
| | STRAIN RELIEF | CENTER POLARIZER | D | C | B | A | NUMBER OF POSITIONS | T&B PART NUMBER (REFERENCE) | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.13[.005]

4 PLC ± -

ANGLES ± -

MATERIAL

FINISH

DWN J. GERACE 17SEP04

CHK C. ROHDE 17SEP04

APVD M. WALMSLEY 17SEP04

NAME

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

CONNECTOR ASSEMBLY, FEMALE SOCKET TRANSITION, 622 SERIES

1658527

SCALE 10:1 SHEET 1 OF 1 REV D1

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[622-2041LF](#) [622-1230LF](#)