










F1 1-1718645-3	A	4pos. MCON 1.2 - LL Connector, Sealed	F	1	MCON 1.2 - CPA	PA46-GF15	RED	5
				1	4pos. MCON 1.2 - Seal	MVQ	NATURE	4
				1	4pos. MCON 1.2 - Retainer	PA66-GF15	VIOLET	3
				1	4pos. MCON 1.2 - Protec. Cover	PA6-GF15	YELLOW	2
				1	4pos. MCON 1.2 - Rec. Housing	PA66-GF30	BLACK	1
F2 2-1718645-1	B	4pos. MCON 1.2 - LL Connector, Sealed	F2 F	1	MCON 1.2 - CPA	PA46-GF15	GREY	5
				1	4pos. MCON 1.2 - Seal	MVQ	NATURE	4
				1	4pos. MCON 1.2 - Retainer	PA66-GF15	VIOLET	3
				1	4pos. MCON 1.2 - Protec. Cover	PA6-GF15	BLACK	2
				1	4pos. MCON 1.2 - Rec. Housing	PA66-GF30	NATURE	1
F3 1-1718645-1	A	4pos. MCON 1.2 - LL Connector, Sealed	F3 F	1	MCON 1.2 - CPA	PA46-GF15	GREY	5
				1	4pos. MCON 1.2 - Seal	MVQ	NATURE	4
				1	4pos. MCON 1.2 - Retainer	PA66-GF15	VIOLET	3
				1	4pos. MCON 1.2 - Protec. Cover	PA6-GF15	BLACK	2
				1	4pos. MCON 1.2 - Rec. Housing	PA66-GF30	BLACK	1
TE-ORDER-NO. 10	COD	DEFINITION	REV	QTY	DEFINITION	MATERIAL	SURFACE/COLOUR	ITEM




CPA IN END POSITION



RETAINER IN END POSITION



CODINGS
M 2:1



NOTES:

- 1 MAX. WIRE SIZE RANGE 1.0 mm² FLR PERMITTED FOR CAVITY-Ø 3.55MM
QUANTITY SEE WIRE HARNESS DRAWING
FOR PERMISSIBLE CURRENT CARRYING CAPACITY OF THE SINGLE CONTACT
SEE PRODUCT SPECIFICATION NO. 108-18782
- 2 AREA FOR PRINT
- 3 USABLE CONTACTS MCON 1.2 LL
SEE TE-NO. 1452674, SINGLE WIRE SEAL-VERSION
- 4 ACCORDING TO INTERFACE DRAWING 114-18679-3
- 5 SUPPLIER-MARK
- 6 SPACE OF ACTIVITY
- 7 SUPPLY CONDITION: CPA IN PRELOCKED POSITION
- 8 SUPPLY CONDITION: RETAINER IN PRELOCKED POSITION
- 9 WARPAGE PERMITTED TO MAX. -0.5mm
- 10 TE ORDER-NO.
- 11 ASSEMBLY LINE SEGMENT IDENTIFICATION
- 12 DATE CODE (DDYY)
- 13 DIVERGENT MARKING FOR PARTS FROM CHINESE AND U.S. PRODUCTION
- 1-...-1 AS SHOWN

3D VIEW

1:1

1:1

TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-140@CENTRIC TO NOMINAL DIMENSION. EDITION 1982-11 SHALL APPLY. Freimaßtoleranzen nach DIN 16901-140@. Es gilt die Ausgabe 1982-11.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±, 1 PLC ±, 2 PLC ±, 3 PLC ±, 4 PLC ±, ANGLES FINISH ±0°

DWN G. Roth 16FEB2005

CHK A. Schroebel 16FEB2005

APVD J. Woller

PRODUCT SPEC 108-18969

APPLICATION SPEC 116-18861

WEIGHT 5 g

CUSTOMER DRAWING

NAME 4pos. MCON 1.2 - LL Connector, Sealed

SIZE A1

CAGE CODE 00779

DRAWING NO. ©=1718645

RESTRICTED TO

SCALE 5:1

SHEET 1 OF 1

REV F3

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1718645-1](#)