

4

3

2


1

LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REVISED PER ECN-22-134141	17JAN2022	AK	SZ

- NOTE:
- MATERIAL:
HOUSING: THERMOPLASTIC HIGH TEMPERATURE, UL 94V-0, COLOR: SEE PART TABLE.
CONTACT: PHOSPHOR BRONZE, THICKNESS=0.25mm.
SHELL: PHOSPHOR BRONZE, THICKNESS=0.30mm.
REAR SHELL: STAINLESS, THICKNESS=0.30mm.
 - FINISH:
CONTACT: GOLD FLASH OVER 30u" MIN. PALLADIUM-NICKEL PLATED ON CONTACT AREA, GOLD FLASH ON CONTACT AREA, 100u" MIN. MATTE-TIN PLATED ON SOLDER TAILS, 50u" MIN. NICKEL UNDERPLATED ALL OVER.
SHELL: 30u"~ 90u" NICKEL PLATED OVER ALL.
 - PANEL THICKNESS OF 2.67mm MAXIMUM IF RECEPTACLE CONNECTOR IS MOUNTED BEHIND A PANEL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.
 PLEASE REMOVE POST HOLE ON PCB.
 NO EMBOSSED ON TOP SURFACE OF SHELL.
 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

D




D



RECOMMENDED PCB LAYOUT

C

C



W/O 	REEL	 W/O		WHITE 	2-1734346-8
				BLACK 	2-1734346-7
				WHITE 	2-1734346-6
				BLACK	2-1734346-5
		W/		WHITE 	2-1734346-4
				BLACK	2-1734346-3
				WHITE 	2-1734346-2
				BLACK	2-1734346-1
W/ 	REEL	 W/O		WHITE 	1-1734346-8
				BLACK	1-1734346-7
				WHITE 	1-1734346-6
				BLACK	1-1734346-5
		W/		WHITE 	1-1734346-4
				BLACK	1-1734346-3
				WHITE	1-1734346-2
				BLACK	1-1734346-1
	TRAY	 W/O		WHITE 	1-1734346-8
				BLACK 	1-1734346-7
				WHITE 	1-1734346-6
				BLACK 	1-1734346-5
		W/		WHITE	1734346-4
				BLACK	1734346-3
				WHITE 	1-1734346-2
				BLACK	1734346-1
REAR SHELL	PACKAGE	POST	FINISH	HSG'S COLOR	PART NUMBER

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION


DATE

DWN

APVD


SEE SHEET 1.

TRAY




TRAY

TOTAL:100 PCS




TRAY




USE THE TAPE TO FIX THE TRAY

8 PLC


VIEW A




INNER BOX(16 TRAY)



INNER BOX(16 TRAY)



OUTER BOX



CARTON


32TRAY/ CARTON

TOTAL:3200 PCS

GROSS WEIGHT: 16.5 KGS.

NET WEIGHT: 15.5 KGS

VIEW A



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

USB CONNECTOR, SERIES B, 4 POSITIONS,
R/A, SMT TYPE, WITH REAR SHELL

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779C=1734346

SCALE

SHEET


2 OF 3

REV

D

DIMENSIONS:

MM



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

MATERIAL

FINISH

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.



COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.



PLASTIC REEL






W

COVER





CARRIER

 ϕA


8 LAYER



OUT BOX PACKAGE DIAGRAM DRAWING



PACKING VIEW



SECTION A-A

NOTE:

- MATERIAL:
EMBOSSED CARRIER :PS .
COVER TAPE :PET.
SHIPPING CARTON : CORRUGATED FIBERBOARD.
- DIMENSION:
REEL : W=32, $\phi A=330$ mm.
SHIPPING CARTON : L=348, W=348, H=340mm.
- QUANTITY:
PRIMARY PACKING : 200 PCS/REEL.
SECONDARY PACKING : 8 REEL/CARTON(1,600PCS).
- WEIGHT:
NET WEIGHT : 9.5kg.
GROSS WEIGHT : 10.5kg.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

USB CONNECTOR, SERIES B, 4 POSITIONS,
R/A, SMT TYPE, WITH REAR SHELL

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779C=1734346

SCALE

SHEET

3 of 3

REV

D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1734346-3](#)