

1. THIS PLUG CONNECTOR KIT CONSIST OF THE FOLLOWING ITEMS, WHICH ARE ALSO AVAILABLE SEPARATELY.

- 1738254-1 PLUG SHELL ASSEMBLY
- 1738203-1 JACKNUT KIT, A-F (ASSEMBLED PER TABLE)
- 1738186-1 INSERT ASSEMBLY, ARR 40P, KEY A, INSTALLED
- 1-1954122-5; SIZE 22 PIN CONTACT, RT ANGLE; QTY = 10; INSTALLED (ROW D)
- 1-1954122-6; SIZE 22 PIN CONTACT, RT ANGLE; QTY = 10; INSTALLED (ROW C)
- 1-1954122-7; SIZE 22 PIN CONTACT, RT ANGLE; QTY = 10; INSTALLED (ROW B)
- 1-1954122-8; SIZE 22 PIN CONTACT, RT ANGLE; QTY = 10; INSTALLED (ROW A)
- 1954332-1 INSERT ASSEMBLY, ARR 13PI, KEY B, INSTALLED
- 2000591-6; SIZE 12 PIN CONTACT, RT ANGLE; QTY = 2; INSTALLED
- 1996787-2; SIZE 16 PIN CONTACT, RT ANGLE; QTY = 4; INSTALLED
- 1-1954186-2; SIZE 20 PIN CONTACT, RT ANGLE LONG LEG; QTY = 4; INSTALLED
- 1-1954186-0; SIZE 20 PIN CONTACT, RT ANGLE SHORT LEG; QTY = 2; INSTALLED
- 1738712-4 SIZE 5 PIN CONTACT, RT ANGLE; QTY = 1; INSTALLED
- 1738211-1 DUST COVER; QTY = 2; INSTALLED

SHELL ASSEMBLY MAT'L:
SHELL: ALUMINUM ALLOY 6061 T651 PER AMS-QQ-A-250
INSERT RETENTION CLIP: COPPER ALLOY PER ASTM B194
PROTECTIVE COVER: ANTI-STATIC THERMOPLASTIC ELASTOMER PER ASTM D5593.

INSERT ASSEMBLY MAT'L:
FRONT & REAR INSULATORS: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
INTERFACIAL SEAL & GROMMET: FLUROSILICONE ELASTOMER PER MIL-R-25988 B
EXCEPT 4.6.6.1
ALIGNMENT BOARDS: HIGH-TEMP THERMOPLASTIC

CONTACT MAT'L: COPPER ALLOY

SHELL: ELECTROLYTIC NICKEL PER SAE AMS QQ-N-290 OVER ELECTROLESS NICKEL PER SAE AMS-2404, CLASS 3.

CONTACT FINISH: 1.27µm MIN GOLD PER ASTM B488 OVER 2.54µm MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT

TE LOGO, TE PART NO, DATE CODE - YEAR & WEEK (YY - WW) MARKED IN THIS AREA

4-40 SCREWS ARE REQUIRED FOR PANEL MOUNTING (NOT INCLUDED).
SCREW HEAD DIAMETER: 6mm MAX
RECOMMENDED TORQUE: 1.1 N-m [10 lb_in] MIN

4-40 THREADED HOLES ARE SELF-LOCKING, HAVING THE SPIRALOCK® THREAD FORM.
SPIRALOCK® IS A REGISTERED TRADEMARK OF SPIRALOCK CORPORATION.




7. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.

8. POLARIZATION FEATURE TO PREVENT FRONT PANEL MOUNTING.

9. PITCH FOR SIDE-BY-SIDE MOUNTING: 19.50mm MIN.

10. DUST COVERS INSTALLED BEFORE SHIPPING.

11. JACKNUT KIT (IF NOT ASSEMBLED) PACKAGED SEPARATELY AND SHIPPED WITH CONNECTOR.



WITH CONTACTS (INSTALLED) WITH JACK NUT (INSTALLED IN "E")	1996725-3
WITH CONTACTS (INSTALLED) WITH JACK NUT (INSTALLED IN "B")	1996725-2
WITH CONTACTS (INSTALLED) WITH JACK NUT A-F (NOT INSTALLED)	1996725-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS CHK K. HOGAN APVD K. HOGAN	7-27-09 7-27-09 7-27-09	NAME	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC	
MATERIAL		FINISH		WEIGHT	
2		3		A100779C=1996725	
CUSTOMER DRAWING		SCALE		SHEET 1 OF 1	
		2:1		REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1996725-3](#)