





P	LTR	DESCRIPTION	DATE	DWN	APVD
	P7	REVISED PER ECO-11005140	30MAR11	RK	HMR
	P8	REVISED PER ECR-21-101990	19APR2021	SS	EW




TIPICA CAVITA' PER TERMINALE TE AMP
(TYPICAL CAVITY FOR TE AMP CONTACT


SCALE 1:1



- | | |
|---|--|
|  | PA 6.6 UNFILLED, UL 94-V2. |
|  | PA 6 UNFILLED, GLOW WIRE TEST AT 750°C |
|  | NON ANCORA RILASCIATO IN PRODUZIONE
(NOT YET RELEASED FOR PRODUCTION) |
|  | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI |
| 5 | INTERNAL FLASH INSIDE CAVITY (THIN AND FLEXIBLE
THAT DO NOT COME OFF) ACCEPTABLE UP TO 0.15 mm.
EXTERNAL FLASH ACCEPTABLE UP TO 0.4 mm |

4		NATURALE (NATURAL)	2	2-180941-0	P
		NATURALE (NATURAL)		1-180941-0	O
4		ARANCIONE (ORANGE)	1	0-180941-9	O
		VIOLA (VIOLET)		0-180941-8	O
		MARRONE (BROWN)		0-180941-6	P
		NERO (BLACK)		0-180941-5	P
4		GIALLO (YELLOW)		0-180941-4	O
		BLU (BLUE)		0-180941-3	O
		VERDE (GREEN)		0-180941-2	O
		ROSSO (RED)		0-180941-1	P
		NATURALE (NATURAL)		0-180941-0	P
	NOTE	COLORE (COLOUR)		MATERIALE (MATERIAL)	P / N



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. YAALI		24JUL2002		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK C. TARTARI		NAME	
mm		0 PLC ±-		APVD -		FASTIN-FASTON CONN. 6.3 MM	
		1 PLC ±0.3		PRODUCT SPEC		SR. REC HSG 3 WAY	
		2 PLC ±-		108-20020		-	
		3 PLC ±-		APPLICATION SPEC			
		4 PLC ±-		-			
ANGLES ±2°				SIZE		CAGE CODE	DRAWING NO
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
SEE TABLE		-		2.3 g		A300779	
material_2		finish_spec_2		CUSTOMER DRAWING		C-180941	
						SCALE	SHEET
						3:1	OF
							REV
							P8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[180941](#)