


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		A	REVISED PER ECO-09-012256	22MAY2009	HMR	SM
			A1	ECO-19-006909	03MAY2019	AP	WS

- 1 PHOSPHOR BRONZE, 0.2 THK REF.
- 2 0.000381 MIN THK GOLD STRIPE IN CONTACT AREA,0.00127 MIN BRIGHT TIN PLATE IN CRIMP AREA,0.00127 MIN NICKEL PLATE ALL OVER.
- 3 0.000762 MIN THK GOLD STRIPE IN CONTACT AREA,0.00127 MIN BRIGHT TIN PLATE IN CRIMP AREA,0.00127 MIN NICKEL PLATE ALL OVER.
4. WIRE RANGE : 22 - 18 AWG
5. INSULATION RANGE : Ø1.50 - 2.79
- 6 0.0381 MIN THK BRIGHT TIN PLATE, LUBRICATED
- 7 TYCO ELECTRONICS LOGO LOCATED APPROXIMATELY AS SHOWN.

3	2008625-3
2	2008625-2
6	2008625-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN R BROWN 03APR2008	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK M McCARTHY 03APR2008	NAME CONTACT, RECEPTACLE, CRIMP SNAP-IN MICRO MATE-N-LOK(TM) 22-18 AWG	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±1° FINISH		APVD C JONES 28MAY2008	PRODUCT SPEC 108-1836	
MATERIAL			APPLICATION SPEC 114-13000	
SEE NOTES			WEIGHT -	
			CUSTOMER DRAWING	
			SIZE A200779	CAGE CODE C-2008625
			DRAWING NO -	RESTRICTED TO -
			SCALE 10:1	SHEET 1 OF 1
			REV A1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2008625-1](#)