





1. APPLICABLE CABLE: RECOMMENDED AWG30~26 X 8C
MAX AWG22 X4C
OVERALL DIAMETER 6.7MAX.

2. DATE CODE IS DESCRIBED ON THE BUNDLED CUSTOMER DRAWING.

3. THE PRODUCT OF THIS DRAWING NO. IS PACKED INDIVIDUALLY
IN PACKAGE OF EXCLUSIVE USE.

4 PROP 65 WARNING LABEL: SEE SHEET 2



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECR-19-000401	10JAN2019	PP	PP
	D2	ECR-19-007308	08MAY2019	SS	PP
	D3	NOTE 4 ADDED (PROP 65 WARNING)	25AUG2020	SS	JDB
	D4	ADD NEW PART VARIANT 3-2013595-1	02SEP2020	SS	JDB

PRELIMINARY					D4	ADD NEW PART VARIANT 3-2013595-1	02SEP2020	SS	JDB
4	4	4	4	4	CROSS-LINKED POLYOLEFIN	HEAT SHRINKABLE TUBE		9	
					ELECTROLYSIS COPPER FOIL, ACRYLIC ADHESIVE MATERIAL	COPPER FOIL TAPE		8	
-		-	-	-	POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	BOTTOM COVER	YELLOW	7	
-	-		-	-	POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	BOTTOM COVER	GREY		
	-	-			POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	BOTTOM COVER	BLACK		
-		-	-	-	POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	TOP COVER	YELLOW	6	
-	-		-	-	POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	TOP COVER	GREY		
	-	-			POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	TOP COVER	BLACK		
-		-		-	POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	LOCK EJECTOR	WHITE PRINT	5	
	-		-		POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	LOCK EJECTOR	BLACK		
					STEEL/UNDER:Cu PLATING,TOP:Ni PLATING	BOTTOM SHELL		4	
					STEEL/UNDER:Cu PLATING,TOP:Ni PLATING	TOP SHELL		3	
2	2	2	2	2	POLYESTER OF GLASS FILLED THERMO PLASTIC(UL94V-0)	PLUG HSG COVER		2	
	-	-	-	-	CONTACT:COPPER ALLOY UNDER ALL SURFACE:Ni PLATING 1.27±°µmMIN TOP CONTACT AREA:Au PLATING:0.76µmMIN SOLDERING AREA:Au FLASH HSG:POLY-AMID OF GLASS FILLED THERMO PLASTIC(UL94V-0)	PLUG HSG SUB ASSY		1	
-					CONTACT:COPPER ALLOY UNDER ALL SURFACE:Ni PLATING 1.27±*µmMIN TOP CONTACT AREA:Au PLATING:0.5µmMIN SOLDERING AREA:Au FLASH HSG:POLY-AMID OF GLASS FILLED THERMO PLASTIC(UL94V-0)				
3-2013595-1	2013595-4	2013595-3	2013595-2	2013595-1					
REQ'D/ASSY					MATERIAL / FINISH	PART NAME	COLOR	ITEM NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT

DWN 12NOV2007

TE TE Connectivity

NAME	INDUSTRIAL MINI I/O PLUG CONNECTOR KIT D-SHAPE TYPE I
------	---

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2013595	

CUSTOMER DRAWING	SCALE 5:2	SHEET 1 OF 2	REV D4
------------------	-----------	--------------	--------

NOTES: CONTINUATION FROM SHEET 1:

4 PROP 65 WARNING LABEL:

- THE WARNING LABEL ON THE PRODUCT OR LOWEST LEVEL PACKAGING.
- CHEMICAL NAME: ANTIMONY TRIOXIDE




WARNING: This product can expose you to chemicals including ANTIMONY TRIOXIDE which is known to the state of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
±0.3

0-PLC ±

1-PLC ±0.5

2-PLC ±0.13

3-PLC ±0.013

4-PLC ±0.0001

ANGLES ±

FINISH
SEE TABLE

DWN
S. INOMATA
12NOV2007

CHK
I. HASEGAWA
12NOV2007

APVD
I. HASEGAWA
12NOV2007

PRODUCT SPEC
108-78405

APPLICATION SPEC
114-5431

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
INDUSTRIAL MINI I/O
PLUG CONNECTOR KIT
D-SHAPE TYPE I

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2013595

RESTRICTED TO

SCALE
5:2

SHEET
2 OF 2

REV
D4

1470-19 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2013595-1](#)