


P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL CREATED	23SEP2019	CL	RS



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

- NOTES:
- MATERIAL AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702
 - CONNECTOR N-TYPE INTERFACE FOLLOW IEC61169-16
 - PRODUCT RATING:
TEMPERATURE: -40°C TO +85°C
CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
FREQUENCY RANGE: DC TO 18GHz
DURABILITY: NO LESS THAN 500TIMES
BEND RADIUS: 20MM MIN (STATIC)
50MM MIN(REPEATED)
 - CABLE ASSEMBLY TO BE 100% SI TESTED
VSWR: 1.3:1 MAX @ DC~18GHz
INSERT LOSS: REFER TO TABLE
MECHANICAL PHASE STABILITY: <±5°
MECHANICAL AMPLITUDE STABILITY: <±0.1dB
 - CONNECTOR NEED COVER WITH CAP,PACKAGE FOLLOW TEC-107-115

1-2016657-5	1500±15	2.08dB@6GHz	3.96dB@18GHz
1-2016657-0	1000±15	1.52dB@6GHz	2.94dB@18GHz
2016657-6	600±10	1.07dB@6GHz	1.94dB@18GHz
PART NUMBER	LENGTH	INSERTION LOSS(MAX)	

PC	1	LABEL	4
MR	AR	HEAT SHRINK TUBE	3
MR	AR	COAX CABLE,SOLID SPCCS 0.94MM,PTFE TAPE INSULATION, SPC TAPE OUTER CONDUCTOR 3.15MM,FEP JACKET,50OHM,BLUE	2
PC	2	PC N-TYPE,MALE,STRAIGHT	1
UNIT	Q'TY	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 20AUG2019 Cedar Liu		
		CHK 28AUG2019 Roger Song		
DIMENSIONS: mm		APVD Roger Song	NAME RF CA, N M TO N M, WITHOUT ARMOR 18GHz	
		PRODUCT SPEC	SIZE A3	
		APPLICATION SPEC	CAGE CODE 00779	
		WEIGHT	DRAWING NO C-2016657	
MATERIAL TBD		FINISH -	RESTRICTED TO	
		finish_spec_2	SCALE 1:3	
		CUSTOMER DRAWING	SHEET 1 OF 1	
			REV 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2016657-0](#)