








POS.	DIM. A
2*6	39.70
2*5	33.70
2*4	27.70
2*3	21.70



- 1 MATERIAL:
LEVEL 1: PBT,STANDARD TEMPERATURE 105°C
KEY A:NATURAL; KEY B:PURPLE; KEY C:BLUE; KEY D:YELLOW
- LEVEL 2: PA66,HIGH TEMPERATURE 150°C
KEY A:LIGHT GREY; KEY B:RED; KEY C:BLACK; KEY D:NATURAL


- 2 MATERIAL MARK:
LEVEL 1:PBT,LEVEL 2:HDT
3. APPLICABLE CONTACT P/N
RECEPTACLE CONTACT:1971237/1971779/81/83/85/87-*, 2238066-*
4. MATING CONN, P/N
CAP HSG: *-1971774/5-
TPA (LOCKING PLATE): *-1971778-*

- 5 GLOW WIRE COMPLIANT IN ACCORDANCE WITH IEC 60335-1. THIS IS BASED ON THE PRODUCT MEETING A GWEPT 850° C TEST AND RESIN GWIT GREATER THAN OR EQUAL TO 775° C.


LOC		DIST		REVISIONS				
-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			E	REVISED PER ECR-21-100678	08APR2021	SS	VS	
			F	REVISED PER ECR-20-100915	28APR2021	JP	VS	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TOMMY WU		09JUL2012		 TE Connectivity	
		CHK	HAPYE WU		09JUL2012			
		APVD	YUHONG MAO		09JUL2012			
		PRODUCT SPEC						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:					NAME	
mm		108-106118						
		APPLICATION SPEC						
		114-106118						
MATERIAL		WEIGHT					SIZE	
		-					CAGE CODE	
		Customer Drawing					DRAWING NO	
							RESTRICTED TO	
							A100779C=1971776	
							SCALE	
							4:1	
							SHEET	
							1 OF 2	
							REV	
							F	


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	-	-	SEE SHEET 1	-	-	-




2*5 POSITIONS




KEYING FOR 2*5 POS.




2*4 POSITIONS



KEYING FOR 2*4 POS.




2*3 POSITIONS




KEYING FOR 2*3 POS.

2*6	LEVEL 1	KEY A	1-1971776-6
		KEY B	2-1971776-6
		KEY C	3-1971776-6
		KEY D	4-1971776-6
	LEVEL 2	KEY A	5-1971776-6
		KEY B	6-1971776-6
		KEY C	7-1971776-6
		KEY D	8-1971776-6
2*5	LEVEL 1	KEY A	1-1971776-5
		KEY B	2-1971776-5
		KEY C	3-1971776-5
		KEY D	4-1971776-5
	LEVEL 2	KEY A	5-1971776-5
		KEY B	6-1971776-5
		KEY C	7-1971776-5
		KEY D	8-1971776-5
POS.	MATERIAL	KEY	P/N

2*4	LEVEL 1	KEY A	1-1971776-4
		KEY B	2-1971776-4
		KEY C	3-1971776-4
		KEY D	4-1971776-4
	LEVEL 2	KEY A	5-1971776-4
		KEY B	6-1971776-4
		KEY C	7-1971776-4
		KEY D	8-1971776-4
2*3	LEVEL 1	KEY A	1-1971776-3
		KEY B	2-1971776-3
		KEY C	3-1971776-3
		KEY D	4-1971776-3
	LEVEL 2	KEY A	5-1971776-3
		KEY B	6-1971776-3
		KEY C	7-1971776-3
		KEY D	8-1971776-3
POS.	MATERIAL	KEY	P/N



2*6 POSITIONS



KEYING FOR 2*6 POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY WU	09JUL2012	 TE Connectivity	
		CHK HAPYE WU	09JUL2012		
		APVD YUZHONG MAO	09JUL2012		
		PRODUCT SPEC			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm				PLUG HOUSING, DOUBLE ROW POWER TRIPLE LOCK	
		0 PLC ±		108-106118	
		1 PLC ±0.35		APPLICATION SPEC	
		2 PLC ±0.25		114-106118	
		3 PLC ±		WEIGHT	
		4 PLC ±		Customer Drawing	
ANGLES ±				SIZE	
FINISH				CAGE CODE	
MATERIAL				DRAWING NO	
				RESTRICTED TO	
				A1 00779 ©=1971776	
				SCALE 4:1	
				SHEET 2 OF 2	
				REV F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1971776-6](#)