


NOTES

1. All dimensions are in $\frac{\text{inches}}{\text{millimeters}}$


2. Dimensions appearing in table are as follows:

- a - As Supplied
- b - After Unrestricted Recovery

3. COATING (ADHESIVE):
AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETER WILL BE REDUCED BY .06 [1.5] MAX.



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

ORDERING INFORMATION

Base part number 202K1XX -X -20 /XXX -0

Material dash number (See Compatibility Chart)

Modification number

Adhesive slash number

Color Designator

TABLE OF DIMENSIONS

PART NUMBER	H		J		P	R	S	T	U&V	JO	HW	JW	X	Y
	Min	Max	Min	Max	±10%	±10%	±10%	±10%	±10%	±10%	±20%	±20%	±20%	±20%
202K153-X-20	a	b	a	b	b	b	b	b	b	b	b	b	b	b
	1.42 [36,0]	0.88 [22,4]	1.42 [36,0]	0.33 [8,4]	3.15 [80,0]	1.65 [42,0]	0.12 [3,0]	0.04 [1,0]	0.79 [20,0]	0.77 [19,5]	0.08 [2,0]	0.04 [1,1]	1.26 [32,0]	1.18 [30,0]
202K163-X-20	a	b	a	b	b	b	b	b	b	b	b	b	b	b
	1.69 [43,0]	1.11 [28,2]	1.69 [43,0]	0.39 [9,9]	3.90 [99,0]	2.40 [61,0]	0.12 [3,0]	0.07 [1,7]	0.79 [20,0]	0.83 [21,0]	0.09 [2,2]	0.05 [1,2]	2.05 [52,0]	1.18 [30,0]

Raychem Molded Parts CUSTOMER DRAWING

If this document is printed it becomes uncontrolled. Check for the latest revision

COMPATABILITY CHART

MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S. NO.	COATING DESCRIPTION
-3	POLYOLEFIN, SEMI RIGID (RT-301)	RT-301	/42; /86	S-1017; S-1048	ADHESIVE
-4	POLYOLEFIN, FLEXIBLE (RT-1304)	RT-1304	/42; /86	S-1017; S-1048	ADHESIVE
-25	Elastomer, Fluid Resistant	RT-1325	/225	S-1048	ADHESIVE
-100	POLYOLEFIN, SEMI-FLEXIBLE ZEROHAL	RT-1323	/184; /86	S-1030; S-1048	ADHESIVE

THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCO ELECTRONICS CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO ELECTRONICS CORPORATION IS PROHIBITED.				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC AND INCHES ARE IN BRACKETS. DECIMAL TOLERANCES XXX ± 0.13 (.005) XX ± 0.25 (.01) X ± 0.50 (.10) ANGLE TOLERANCE .X ± 1 DEG.	DRAWN M. Mazariagos 12/04/12	APPROVED S. Gravano 12/04/12	 TE Connectivity	
	RPN _____	TITLE Boot, Straight, With Lip		
	CAD FILE: 202K1XX-X-20_CD			
TYCO ELECTRONICS RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANY TIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION. © 2012 Tyco Electronics Corporation. All rights reserved.	THIRD ANGLE PROJECTION 	SIZE B	CODE IDENT. NO. 06090	DWG. NO. 202K1XX-X-20
		DO NOT SCALE THIS DRAWING		SHEET 1 OF 1



TE Connectivity

Boot, Straight, With Lip

SIZE B CODE IDENT. NO. 06090 DWG. NO. 202K1XX-X-20

DO NOT SCALE THIS DRAWING SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CZ2454-000](#)