






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A	REVISED PER ECO-15-003242	23MAR2015	AP	DD



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



UNGUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: KIRAN HOLAL CHK: D.DIXON APVD: D.DIXON	08NOV2012 08NOV2012 08NOV2012	TE Connectivity	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		IMPACT, 2 PAIR, 10 COLUMN, HEADER	
mm	0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ±	PRODUCT SPEC		UNGUIDED, OPEN END WALL	
	ANGLES ±	APPLICATION SPEC		SIGNAL MODULE, 0.46 PTH	
MATERIAL	FINISH SEE TABLE	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A1	00779	C=2057426	-
Customer Drawing		SCALE	6:1	SHEET 1 OF 2	REV A

8	7	6	5	4	3	2	1
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		20			
© COPYRIGHT 20		BY -		ALL RIGHTS RESERVED.			

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	-	-	SEE SHEET 1	-	-	-

	5.5	2057426-6
	4.9	2057426-5
	4.5	2057426-4
	5.5	2057426-3
	4.9	2057426-2
	4.5	2057426-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN -	27APR2011	 TE Connectivity			
DIMENSIONS:		CHK J. EABY	27APR2011	NAME IMPACT, 2 PAIR, 10 COLUMN, HEADER UNGUIDED, OPEN END WALL SIGNAL MODULE, 0.46 PTH			
	mm	APVD J. EABY	27APR2011				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		0 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ±		APPLICATION SPEC			
		ANGLES FINISH SEE TABLE		SIZE CAGE CODE DRAWING NO			
MATERIAL -		WEIGHT -		A1 00779 C=2057426		RESTRICTED TO -	
Customer Drawing		SCALE 5:1		SHEET 2 OF 2			
				REV A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2057426-3](#)