

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	PRODUCTION ISSUE	18JAN2019	PNT	MT





TABLE OF DIMENSIONS

PART NUMBER	H		J			P	R	S	T	JO	W
	Min	Max	Min	Min	Max	±10%	Ref	Ref	Ref	±10%	±20%
	a	b	-3,-4 a	-12 a	b	b	b	b	b	b	b
202D121-X-60	23.3 [.92]	10.5 [.41]	23.3 [.92]	12.4 [.49]	5.6 [.22]	38.1 [1.50]	21.1 [.83]	3.0 [.12]	1.0 [.04]	10.2 [.40]	1.78 [.07]
202D132-X-60	28.4 [1.12]	14.3 [.56]	28.4 [1.12]	14.7 [.58]	6.6 [.26]	54.9 [2.16]	27.7 [1.09]	3.0 [.12]	1.0 [.04]	16.5 [.65]	1.78 [.07]
202D142-X-60	31.0 [1.22]	17.8 [.70]	31.0 [1.22]	16.0 [.63]	7.2 [.28]	66.8 [2.63]	35.3 [1.39]	3.0 [.12]	1.0 [.04]	17.8 [.70]	2.03 [.08]
202D153-X-60	36.0 [1.42]	22.4 [.88]	36.0 [1.42]	18.5 [.73]	8.4 [.33]	80.0 [3.15]	41.4 [1.63]	3.0 [.12]	1.0 [.04]	20.8 [.82]	2.03 [.08]
202D163-X-60	42.7 [1.68]	28.2 [1.11]	42.7 [1.68]	22.0 [.87]	9.9 [.39]	103.6 [4.08]	56.4 [2.22]	3.0 [.12]	1.65 [.065]	24.6 [.97]	2.29 [.09]
202D174-X-60	51.8 [2.04]	35.1 [1.38]	51.8 [2.04]	35.3 [1.39]	15.8 [.62]	130.3 [5.13]	64.5 [2.54]	3.0 [.12]	1.65 [.065]	39.6 [1.56]	3.3 [.13]
202D185-X-60	66.0 [2.60]	44.5 [1.75]	66.0 [2.60]	45.7 [1.80]	20.4 [.80]	165.1 [6.50]	84.1 [3.31]	3.0 [.12]	2.0 [.08]	48.3 [1.90]	4.06 [.16]
202D196-X-60	81.7 [3.22]	57.6 [2.27]	81.7 [3.22]	57.1 [2.25]	25.4 [1.00]	177.8 [7.00]	95.3 [3.75]	3.0 [.12]	2.0 [.08]	47.8 [1.88]	4.06 [.16]

DIMENSIONS:  
mm [INCHES]

DWN 18JAN2019

PRAVEEN N T

MATERIAL

SEE SHEET 2

FINISH

-

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

CHK 18JAN2019

N NAGAR

APVD 18JAN2019

M TAYLOR

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

NAME

BOOT, STRAIGHT,  
WITH LIP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-202D1XX-XX-60-0

-

CUSTOMER DRAWING

SCALE


DNS

SHEET

1 OF 2

REV

C



THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

TE Connectivity Ltd.

Copyright

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-3	Polyolefin, Semi-rigid	RT-301	/42;/86;/180	S-1017;S-1048;S-1030
-4	Polyolefin, Flexible	RT-1304	/42;/86;/180	S-1017;S-1048;S-1030
-12	Fluoroelastomer, Flexible	RT-1312	N/A	N/A

## ORDERING INFORMATION

The diagram illustrates the structure of a 10-digit part number. It is divided into five segments, each with a label and a corresponding example:

- Base part number**: 202D1XX
- Material dash number (See Compatibility Chart)**: -XX
- Modification number**: -XX
- Adhesive slash number (If necessary, see Compatibility Chart)**: /XX
- Color Designator**: -0



Horizontal lines connect the labels to their respective segments in the example number. Vertical lines separate the segments. The example number is shown as 202D1XX-XX-XX/XX-0.

NOTES:

1. Dimensions appearing in table are as follows:
  - a - As Supplied
  - b - After Unrestricted Recovery
2. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.
3. Parts shall have color stripe 3.05[.12] wide x 360° around outside surface approx. as shown and must meet requirements set forth in MS3109. colors shall be as follows:

Dash No.	Color
-3	White
-4	Red
-12	Yellow

4. Parts to have only one lip because of core change.

DIMENSIONS: mm [INCHES]		DWN PRAVEEN N T 18JAN2019	MATERIAL —		FINISH —		
TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		CHK N NAGAR 18JAN2019	<div>TE Connectivity Ltd.</div>				
		APVD M TAYLOR 18JAN2019					
		PRODUCT SPEC —	NAME  BOOT, STRAIGHT, WITH LIP				
		APPLICATION SPEC —					
		WEIGHT —	SIZE A4	CAGE CODE 00779	DRAWING NO C-202D1XX-XX-60-0	RESTRICTED TO —	
		CUSTOMER DRAWING			SCALE DNS	SHEET 2 OF 2	REV C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202D132-4-60/42-0-CS5077](#)