

| PART<br>NUMBER | H              |                | J              |                |               | P<br>±10%<br>b  | JO<br>±10%<br>b | R<br>Ref<br>b | S<br>Ref<br>b | T<br>Ref<br>b  | U<br>±10%<br>b | HW<br>±20%<br>b | JW<br>±20%<br>b |
|----------------|----------------|----------------|----------------|----------------|---------------|-----------------|-----------------|---------------|---------------|----------------|----------------|-----------------|-----------------|
|                | Min            | Max            | Min            | Min            | Max           |                 |                 |               |               |                |                |                 |                 |
|                | a              | b              | -3,-4,-25<br>a | -12,-100<br>a  | b             |                 |                 |               |               |                |                |                 |                 |
| 202D211        | 22.4<br>[.88]  | 11.4<br>[.45]  | 22.4<br>[.88]  | 14.0<br>[.55]  | 6.4<br>[.25]  | 105.9<br>[4.17] | 86.4<br>[3.40]  | 11.7<br>[.46] | 3.0<br>[.12]  | 1.0<br>[.04]   | 14.2<br>[.56]  | 1.52<br>[.06]   | 1.14<br>[.045]  |
| 202D221        | 25.7<br>[1.01] | 15.0<br>[.59]  | 25.7<br>[1.01] | 16.0<br>[.63]  | 7.4<br>[.29]  | 121.2<br>[4.77] | 98.6<br>[3.88]  | 12.2<br>[.48] | 3.0<br>[.12]  | 1.0<br>[.04]   | 15.0<br>[.59]  | 1.52<br>[.06]   | 1.14<br>[.045]  |
| 202D232        | 29.5<br>[1.16] | 18.8<br>[.74]  | 29.5<br>[1.16] | 18.3<br>[.72]  | 8.4<br>[.33]  | 138.7<br>[5.46] | 112.8<br>[4.44] | 12.2<br>[.48] | 3.0<br>[.12]  | 1.0<br>[.04]   | 15.5<br>[.61]  | 1.78<br>[.07]   | 1.14<br>[.045]  |
| 202D242        | 34.0<br>[1.34] | 22.9<br>[.90]  | 34.0<br>[1.34] | 21.3<br>[.84]  | 9.7<br>[.38]  | 159.5<br>[5.28] | 130.8<br>[5.15] | 12.2<br>[.48] | 3.0<br>[.12]  | 1.0<br>[.04]   | 15.7<br>[.62]  | 1.78<br>[.07]   | 1.14<br>[.045]  |
| 202D253        | 37.3<br>[1.47] | 29.5<br>[1.16] | 37.3<br>[1.47] | 23.1<br>[.91]  | 10.4<br>[.41] | 177.8<br>[7.00] | 142.2<br>[5.60] | 14.0<br>[.55] | 3.0<br>[.12]  | 1.65<br>[.065] | 18.0<br>[.71]  | 2.0<br>[.08]    | 1.14<br>[.045]  |
| 202D263        | 43.7<br>[1.72] | 34.0<br>[1.34] | 43.7<br>[1.72] | 27.2<br>[1.07] | 12.2<br>[.48] | 203.2<br>[8.00] | 163.1<br>[6.42] | 15.2<br>[.60] | 3.0<br>[.12]  | 1.65<br>[.065] | 19.8<br>[.78]  | 2.0<br>[.08]    | 1.14<br>[.045]  |
| 202D274        | 50.0<br>[1.97] | 41.2<br>[1.62] | 50.0<br>[1.97] | 31.5<br>[1.24] | 14.2<br>[.56] | 203.2<br>[8.00] | 157.7<br>[6.21] | 15.2<br>[.60] | 3.0<br>[.12]  | 1.65<br>[.065] | 20.8<br>[.82]  | 2.3<br>[.09]    | 1.40<br>[.055]  |
| 202D285        | 62.7<br>[2.47] | 47.0<br>[1.85] | 62.7<br>[2.47] | 39.1<br>[1.54] | 17.5<br>[.69] | 203.2<br>[8.00] | 153.2<br>[6.03] | 16.0<br>[.63] | 3.0<br>[.12]  | 2.0<br>[.08]   | 23.4<br>[.92]  | 2.5<br>[.10]    | 1.40<br>[.055]  |
| 202D296        | 69.3<br>[2.73] | 59.7<br>[2.35] | 69.3<br>[2.73] | 43.2<br>[1.70] | 19.6<br>[.77] | 203.2<br>[8.00] | 143.3<br>[5.64] | 16.0<br>[.63] | 3.0<br>[.12]  | 2.0<br>[.08]   | 23.6<br>[.93]  | 2.5<br>[.10]    | 1.40<br>[.055]  |
| 202D299        | 81.8<br>[3.22] | 67.1<br>[2.64] | 81.8<br>[3.22] | 51.1<br>[2.01] | 22.9<br>[.90] | 203.2<br>[8.00] | 138.4<br>[5.45] | 16.0<br>[.63] | 3.0<br>[.12]  | 2.0<br>[.08]   | 31.2<br>[1.23] | 2.5<br>[.10]    | 1.40<br>[.055]  |

1469-35 (1/15)

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-------------|------|-----|------|
|   | -   | SEE SHEET 1 | -    | -   | -    |

COMPATIBILITY CHART

| MATERIAL DASH NO. | MATERIAL DESCRIPTION              | RT SPEC | COATING SLASH NUMBER | COATING S NUMBER  |
|-------------------|-----------------------------------|---------|----------------------|-------------------|
| -3                | Polyolefin, Semi-rigid            | RT-301  | /42;/86;/180         | S1017;S1048;S1030 |
| -4                | Polyolefin, Flexible              | RT-1304 | /42;/86;/180         | S1017;S1048;S1030 |
| -12               | Fluoroelastomer,Flexible          | RT-1312 | N/A                  | N/A               |
| -25               | Elastomer, Fluid Resistant        | RW-2070 | /42;/86;/225         | S1017;S1048;S1206 |
| -100              | Polyolefin, Semi-flexible ZEROHAL | RW-2082 | /86;/180             | S1048,S1030       |

ORDERING INFORMATION

202D211 -XX -XX /XX -0

BASE PART NUMBER \_\_\_\_\_

MATERIAL DASH NUMBER \_\_\_\_\_  
(SEE COMPATABILITY CHART)

MODIFICATION NUMBER \_\_\_\_\_

ADHESIVE SLASH NUMBER \_\_\_\_\_  
(IF NECESSARY, SEE COMPATABILITY CHART)

COLOR DESIGNATOR \_\_\_\_\_

NOTES:

- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
  - a - AS SUPPLIED
  - b - AFTER UNRESTRICTED RECOVERY
- COATING IS OPTIONAL. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY 1.5mm[.06] MAX.
- MOLDING PORTS ARE OPTIONAL. WHEN -00 MODIFICATION NUMBER IS SPEDIFIED MOLDIG PORTS WILL BE LOCATED AS SHOWN.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT - TE Connectivity Ltd.

|                                                                                                      |                                |                                                                                                           |                    |                                           |                    |
|------------------------------------------------------------------------------------------------------|--------------------------------|-----------------------------------------------------------------------------------------------------------|--------------------|-------------------------------------------|--------------------|
| DIMENSIONS:<br>mm [INCHES]                                                                           | DWN<br>M MAZARIEGOS 03/15/2021 | MATERIAL<br>-                                                                                             | FINISH<br>-        |                                           |                    |
|                                                                                                      | CHK<br>M TAYLOR 03/16/2021     |  TE Connectivity Ltd. |                    |                                           |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                               | APVD<br>L RODRIGUEZ 03/16/2021 |                                                                                                           |                    |                                           |                    |
| 0 PLC ± -<br>1 PLC ± 0.50[.1]<br>2 PLC ± 0.25[.01]<br>3 PLC ± 0.13[.005]<br>4 PLC ± -<br>ANGLES ± 1° | PRODUCT SPEC<br>-              | NAME<br>BOOT, STRAIGHT,<br>WITH LIP                                                                       |                    |                                           |                    |
|                                                                                                      | APPLICATION SPEC<br>-          |                                                                                                           |                    |                                           |                    |
|                                                                                                      | WEIGHT                         | SIZE<br>A4                                                                                                | CAGE CODE<br>00779 | DRAWING NO<br>C= 202D211-XX-0THRU299-XX-0 | RESTRICTED TO<br>- |
|                                                                                                      | CUSTOMER DRAWING               |                                                                                                           | SCALE<br>DNS       | SHEET<br>2 OF 2                           | REV<br>P1          |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202D253-3/42-0](#)