







LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	OWN	APVD	
			B	REVISED PER ECO-11-025276	05JAN2012	KH	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. K. SHOBER 31JAN2011		 TE Connectivity	
DIMENSIONS:		CHK J. EABY 31JAN2011			
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	IMPACT, 2 PAIR, 16 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH
		0 PLC ±.05 2 PLC ±.025 2 PLC ±.013 0 PLC ±.010	APVD J. EABY 31JAN2011		
MATERIAL		FINISH SEE TABLE		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO A100779C-2057741
				WEIGHT	
		CUSTOMER DRAWING		SCALE 6:1	SHEET 1 OF 2 REV B

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057741-6
	4.9	2057741-5
	4.5	2057741-4
	5.5	2057741-3
	4.9	2057741-2
	4.5	2057741-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 31 JAN 2011	 TE Connectivity			
DIMENSIONS:		CHK J. EABY 31 JAN 2011				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 31 JAN 2011	NAME	IMPACT, 2 PAIR, 16 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH		
	0 PLC ±	±	PRODUCT SPEC			
	1 PLC ±	±0.25				
	2 PLC ±	±0.13				
	3 PLC ±	±		APPLICATION SPEC		
MATERIAL	4 PLC ±	±	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	ANGLES	±	WEIGHT	-	-	-
-	FINISH	±	A100779C		2057741	-
-	SEE TABLE		CUSTOMER DRAWING			
			SCALE	5:1	SHEET	2 OF 2
			REV B			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2057741-1](#)