

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	ECR-20-010112	28JUN2020	CL	SZ
	C3	ECR-21-103575(NEW PN)	18MAY2021	JZ	WKH
	C4	ECR-21-111621(NEW PN)	28AUG2021	JZ	WKH
	C5	ECR-22-134829	13APR2022	JZ	WKH

1. PARTS AND PROCESSES RoHS COMPLIANT PER TE CONNECTIVITY
STANDARD TEC-138-702.
2. 100% OPEN AND SHORT MISWIRE TEST.
3. PRODUCT RATING:
CHARACTERISTIC IMPEDANCE: 50 OHMS Normal
FREQUENCY RANGE: DC TO 9GHz
4. UMCC GEN1 CAN MATE WITH I-PEX MHFI SERIES AND HIROSE U.FL SERIE

CONNECTOR 0° FROM OTHER END



90±2	UMCC GEN1 PLUG	BLACK	1.13MM LOW LOSS	1-2118651-4
150±3	UMCC GEN1 PLUG	BLACK	1.13 MM	1-2118651-3
80±2	UMCC GEN1 PLUG	BLACK	1.13 MM	1-2118651-2
509±5	UMCC GEN1 PLUG	BLACK	1.13 MM	1-2118651-1
60±2	UMCC GEN1 PLUG	BLACK	1.13 MM	1-2118651-0
250±5	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-9
200±3	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-8
90±2	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-7
90±2	UMCC GEN1 PLUG	GRAY	1.13 MM	2118651-6
70±2	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-5
40±2	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-4
75±2	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-3
30±2	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-2
140±3	UMCC GEN1 PLUG	BLACK	1.13 MM	2118651-1
A	CONNECTOR 2	COLOR-CABLE	1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SCHOLZ 01APR2016	TE Connectivity CABLE ASSEMBLY, COAX 1.13 MM DOUBLE ENDED, UMCC GEN1 PLUG				
DIMENSIONS: mm		CHK J. SCHOLZ 01APR2016					
		APVD J. MOORE 01APR2016					
		PRODUCT SPEC 108-2231					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	NAME	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ±-		WEIGHT	-	A3	00779	C-2118651	-
1 PLC ±-		CUSTOMER DRAWING					
2 PLC ±-		SCALE 8:1					
3 PLC ±-		SHEET 1 OF 1					
4 PLC ±-		REV C5					
ANGLES ±-							
FINISH							
-							
-							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2118651-1](#)