





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16		C	ECR-14-011637	14AUG2014	HZ	RZ

- 1

MAXIMUM CONNECTOR INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 3.5dB/km AT 850nm. MEASURE AGAINST A REFERENCE LEAD
2. TEST DATA PROVIDED WITH EACH ASSEMBLY.
3. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	LG EBY	23MAR09	 TE Connectivity															
			CHK	J.DUNCAN	23MAR09																
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D. BAECHTLE	23MAR09	NAME														
METERS [INCHES]				PRODUCT SPEC																	
		0 PLC ± -		—		CABLE ASSEMBLY, FIBER OPTIC, 50/125, OM3, 2 FIBER BREAKOUT CABLE, SEALED CIRCULAR LC DUPLEX (ODVA), BOTH ENDS															
		1 PLC ± -		—																	
		2 PLC ± -		APPLICATION SPEC		SIZE			CAGE CODE			DRAWING NO			RESTRICTED TO						
		3 PLC ± -		—																	
		4 PLC ± -		—		A2			00779			C-2064915			—						
		ANGLES ± -		—																	
MATERIAL		FINISH		WEIGHT																	
—		—		—																	
CUSTOMER DRAWING										SCALE		NTS		SHEET		1 of 2		REV		C	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOCCE

DIST16

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1.38	250.0±2.50	[9842.5±98.4]	8-2064915-2
0.85	100.0±1.00	[3937.0±39.4]	8-2064915-1
1.03	152.40±1.50	[6000.0±60.0]	8-2064915-0
0.77	76.00±0.76	[2992.1±29.9]	7-2064915-6
0.76	75.00±0.75	[2953.0±30.0]	7-2064915-5
0.71	61.00±0.61	[2400.0±24.0]	6-2064915-1
0.68	50.00±0.50	[1969.0±20.0]	5-2064915-0
0.64	40.00±0.40	[1574.80±15.75]	4-2064915-0
0.64	39.00±0.35	[1535.43±13.78]	3-2064915-9
0.63	38.00±0.35	[1496.06±13.78]	3-2064915-8
0.63	37.00±0.35	[1456.69±13.78]	3-2064915-7
0.63	36.00±0.35	[1417.32±13.78]	3-2064915-6
0.62	35.00±0.35	[1377.95±13.78]	3-2064915-5
0.62	34.00±0.30	[1338.58±11.81]	3-2064915-4
0.62	33.00±0.30	[1299.21±11.81]	3-2064915-3
0.61	32.00±0.30	[1259.84±11.81]	3-2064915-2
0.61	31.00±0.30	[1220.47±11.81]	3-2064915-1
0.61	30.00±0.30	[1181.10±11.81]	3-2064915-0
0.60	29.00±0.30	[1141.73±11.81]	2-2064915-9
0.60	28.00±0.30	[1102.36±11.81]	2-2064915-8
0.59	27.00±0.30	[1062.99±11.81]	2-2064915-7
0.59	26.00±0.30	[1023.62±11.81]	2-2064915-6
0.59	25.00±0.30	[984.25±11.81]	2-2064915-5
0.58	24.00±0.30	[944.88±11.81]	2-2064915-4
0.58	23.00±0.30	[905.51±11.81]	2-2064915-3
0.58	22.00±0.30	[866.14±11.81]	2-2064915-2
0.57	21.00±0.30	[826.77±11.81]	2-2064915-1
0.57	20.00±0.30	[787.40±11.81]	2-2064915-0
0.57	19.00±0.30	[748.03±11.81]	1-2064915-9
0.56	18.00±0.30	[708.66±11.81]	1-2064915-8
0.56	17.00±0.30	[669.29±11.81]	1-2064915-7
0.56	16.00±0.30	[629.92±11.81]	1-2064915-6
0.55	15.00±0.15	[590.55±5.91]	1-2064915-5
0.55	14.00±0.15	[551.18±5.91]	1-2064915-4
0.55	13.00±0.15	[511.81±5.91]	1-2064915-3
0.54	12.00±0.15	[472.44±5.91]	1-2064915-2
0.54	11.00±0.15	[433.07±5.91]	1-2064915-1
0.54	10.00±0.15	[393.70±5.91]	1-2064915-0
0.53	9.00±0.15	[354.33±5.91]	2064915-9
0.53	8.00±0.15	[314.96±5.91]	2064915-8
0.52	7.00±0.08	[275.59±3.15]	2064915-7
0.52	6.00±0.08	[236.22±3.15]	2064915-6
0.52	5.00±0.08	[196.85±3.15]	2064915-5
0.51	4.00±0.08	[157.48±3.15]	2064915-4
0.51	3.00±0.05	[118.11±1.97]	2064915-3
0.51	2.00±0.05	[78.74±1.97]	2064915-2
0.50	1.00±0.05	[39.37±1.97]	2064915-1
MAX IL (dB)	L METERS [INCHES]		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
METERS [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL -

FINISH -

DWN LG EBY 23MAR09

CHK J.DUNCAN 23MAR09

APVD D. BAECHTLE 23MAR09

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
CABLE ASSEMBLY, FIBER OPTIC,
50/125, OM3, 2 FIBER BREAKOUT CABLE,
SEALED CIRCULAR LC DUPLEX (ODVA), BOTH ENDS

SIZEA2

CAGE CODE00779

DRAWING NOC=2064915

RESTRICTED TO -

SCALENTS

SHEET2 of 2

REVC

1471-9 (3/11)

2064915

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2064915-0](#)